

CD8a Monoclonal Antibody (53-6.7), Biotin, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Fruit fly, Hamster, Mouse, Human
Host/Isotype	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), Biotin, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	53-6.7
Conjugate	Biotin
Form	Liquid
Concentration	0.5 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_466346

Applications	Tested Dilution	Publications
Western Blot (WB)	-	2 Publications
Immunohistochemistry (IHC)	-	12 Publications
Immunohistochemistry (Frozen) (IHC (F))	Assay-Dependent	-
Immunocytochemistry (ICC/IF)	-	6 Publications
Flow Cytometry (Flow)	0.5 µg/test	141 Publications
Immunoprecipitation (IP)	-	1 Publication
Functional Assay (FN)	-	3 Publications
Miscellaneous PubMed (Misc)	-	8 Publications

Product Specific Information

Description: The 53-6.7 monoclonal antibody reacts with the mouse CD8a molecule. CD8a is an approximately 32-34 kDa cell surface receptor expressed either as a heterodimer with the CD8 beta chain (CD8 alpha beta) or as a homodimer (CD8 alpha alpha). A majority of thymocytes and a subpopulation of mature alpha beta TCR T cells express CD8 alpha beta while gamma delta TCR T cells, a subpopulation of intestinal intraepithelial lymphocytes (IELs) and dendritic cells express CD8 alpha alpha. CD8 binds to MHC class I and through its association with protein tyrosine kinase p56lck plays a role in T cell development and activation of mature T cells.


Applications Reported: The 53-6.7 antibody has been reported for use in flow cytometric analysis and immunohistochemistry.

Applications Tested: The 53-6.7 antibody has been tested by flow cytometric analysis of mouse thymocytes and splenocytes. This can be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It

is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD8a Monoclonal Antibody (53-6.7), Biotin, eBioscience™



CD8a Antibody (13-0081-82) in Flow
Staining of C57BL/6 splenocytes with 0.25 µg of Rat IgG2a K Isotype Control Biotin (Product # 13-4321-82) (open histogram) or 0.25 µg of Anti-Mouse CD8a Biotin (filled histogram) followed by Streptavidin PE (Product # 12-4317-87). Total viable cells were used for analysis.

[View more figures on thermofisher.com](#)

Western Blot (2)

eLife	Year 2019
Hemozoin produced by mammals confers heme tolerance. "Published figure using CD8a monoclonal antibody (Product # 13-0081-82) in Western Blot" Authors: Pek RH,Yuan X,Rietzschel N,Zhang J,Jackson L,Nishibori E,Ribeiro A,Simmons W,Jagadeesh J,Sugimoto H, Alam MZ,Garrett L,Haldar M,Ralle M,Phillips JD,Bodine DM,Hamza I	
Cardiovascular research	Year 2013
Genetic deletion of chemokine receptor Ccr7 exacerbates atherogenesis in ApoE-deficient mice. "Published figure using CD8a monoclonal antibody (Product # 13-0081-82) in Flow Cytometry" Authors: Wan W,Lionakis MS,Liu Q,Roff� E,Murphy PM	

Immunohistochemistry (12)

Scientific reports	Year 2022
Therapeutic potential of highly functional codon-optimized microtrophin for muscle-specific expression. "Published figure using CD8a monoclonal antibody (Product # 13-0081-82) in Immunohistochemistry" Authors: Starikova AV,Skopenkova VV,Polikarpova AV,Reshetov DA,Vassilieva SG,Velyaev OA,Shmidt AA,Savchenko IM,Soldatov VO,Egorova TV,Bardina MV	
Cancers	Year 2020
TIAM2S Mediates Serotonin Homeostasis and Provokes a Pro-Inflammatory Immune Microenvironment Permissive for Colorectal Tumorigenesis. "Published figure using CD8a monoclonal antibody (Product # 13-0081-82) in Immunohistochemistry" Authors: Chan YL,Lai WC,Chen JS,Tseng JT,Chuang PC,Jou J,Lee CT,Sun HS	

View more IHC references on thermofisher.com

More applications with references on thermofisher.com

- ICC/IF (6)
- Flow (141)
- IP (1)
- FN (3)
- Misc (8)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.