

CD3 Monoclonal Antibody (17A2), FITC, eBioscience™

Product Details

Size	100 µg
Species Reactivity	Mouse
Published Species	Fungi, Rat, Bacteria, Mouse
Host/Isotype	Rat / IgG2b, kappa
Recommended Isotype Control	Rat IgG2b kappa Isotype Control (eB149/10H5), FITC, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	17A2
Conjugate	FITC
Excitation/Emission Max	498/517 nm
Form	Liquid
Concentration	0.5 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2572431

Applications	Tested Dilution	Publications
Western Blot (WB)	-	1 Publication
Immunohistochemistry (IHC)	-	13 Publications
Immunohistochemistry (Paraffin) (IHC (P))	-	1 Publication
Immunohistochemistry (Frozen) (IHC (F))	10 µg/mL	2 Publications
Immunocytochemistry (ICC/IF)	10 µg/mL	5 Publications
Flow Cytometry (Flow)	0.25 µg/test	113 Publications
T-Cell Activation (TCA)	-	1 Publication

Product Specific Information

Description: The 17A2 monoclonal antibody reacts with the mouse CD3 complex. CD3 subunits gamma, delta and epsilon are required for proper assembly, trafficking and surface expression of the TCR complex. CD3 is expressed by thymocytes in a developmentally regulated manner and by all mature T cells. Binding of 17A2 to CD3 initiates the intracellular biochemical pathway resulting in cellular activation and proliferation.

Applications Reported: This 17A2 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This 17A2 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.25 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. This 17A2 antibody has been tested by immunohistochemistry on frozen mouse spleen and can be used at less than or equal to 10 µg

/mL. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.


Excitation: 488 nm; Emission: 520 nm; Laser: Blue Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD3 Monoclonal Antibody (17A2), FITC, eBioscience™


CD3 Antibody (11-0032-82) in Flow

Staining of C57Bl/6 splenocytes with Anti-Human/Mouse CD45R (B220) PE (Product # 12-0452-82) and 0.125 µg of Rat IgG2b K Isotype Control FITC (Product # 11-4031-82) (left) or 0.125 µg of Anti-Mouse CD3 FITC (right). Total viable cells were used for analysis.



CD3 Antibody (11-0032-82) in IHC (F)

Immunohistochemistry of frozen mouse spleen stained with 10 µg/mL Anti-Mouse CD3 FITC and costained with 10 µg/mL Anti-Human/Mouse CD45R (B220) eFluor® 660. Nuclei are stained with DAPI.



[View more figures on thermofisher.com](#)

Western Blot (1)

<p>The Journal of clinical investigation</p> <p>Targeted delivery of immune therapeutics to lymph nodes prolongs cardiac allograft survival.</p> <p>"Published figure using CD3 monoclonal antibody (Product # 11-0032-82) in Western Blot"</p> <p>Authors: Bahmani B,Uehara M,Jiang L,Ordikhani F,Banouni N,Ichimura T,Solhjoui Z,Furtmüller GJ,Brandacher G, Alvarez D,von Andrian UH,Uchimura K,Xu Q,Vohra I,Yilmam OA,Haik Y,Azzi J,Kasinath V,Bromberg JS,McGrath MM, Abdi R</p>	<p>Year</p> <p>2018</p>
--	-------------------------

Immunohistochemistry (13)

<p>PLoS biology</p> <p>The activity of the aryl hydrocarbon receptor in T cells tunes the gut microenvironment to sustain autoimmunity and neuroinflammation.</p> <p>"Published figure using CD3 monoclonal antibody (Product # 11-0032-82) in Immunohistochemistry"</p> <p>Authors: Merchak AR,Cahill HJ,Brown LC,Brown RM,Rivet-Noor C,Beiter RM,Slogar ER,Olgun DG,Gaultier A</p>	<p>Year</p> <p>2023</p>
<p>Frontiers in immunology</p> <p>A single-cell atlas reveals the heterogeneity of meningeal immunity in a mouse model of Methyl CpG binding protein 2 deficiency.</p> <p>"Published figure using CD3 monoclonal antibody (Product # 11-0032-82) in Immunohistochemistry"</p> <p>Authors: Li H,Hu M,Huang Z,Wang Y,Xu Y,Deng J,Zhu M,Feng W,Xu X</p>	<p>Year</p> <p>2023</p>

[View more IHC references on thermofisher.com](#)

Immunohistochemistry (Paraffin) (1)

<p>Clinical and translational medicine</p> <p>Functional inhibition of lactate dehydrogenase suppresses pancreatic adenocarcinoma progression.</p> <p>"Published figure using CD3 monoclonal antibody (Product # 11-0032-82) in Immunohistochemistry (Paraffin)"</p> <p>Authors: Cheng CS,Tan HY,Wang N,Chen L,Meng Z,Chen Z,Feng Y</p>	<p>Year</p> <p>2021</p>
--	-------------------------

More applications with references on thermofisher.com

- IHC (F) (2)
- ICC/IF (5)
- Flow (113)
- TCA (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.