

CD27 Monoclonal Antibody (LG.7F9), eBioscience

Product Details	
Size	100 µg
Species Reactivity	Human, Mouse, Rat
Published Species	Mouse, Human
Host/Isotype	Armenian hamster / IgG
Class	Monoclonal
Type	Antibody
Clone	LG.7F9
Conjugate	Unconjugated
Form	Liquid
Concentration	0.5 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage Conditions	4° C
RRID	AB_467183

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	1 Publication
Flow Cytometry (Flow)	0.5 µg/test	32 Publications
Immunoprecipitation (IP)	Assay-Dependent	-
Neutralization (Neu)	Assay-Dependent	-
Functional Assay (FN)	Assay-Dependent	-
Miscellaneous PubMed (Misc)	-	1 Publication

Product Specific Information

Description: The LG.7F9 monoclonal antibody reacts with mouse CD27, a lymphocyte-specific member of the TNFR superfamily. CD27 is expressed by virtually all mature T cells and by a subpopulation of B cells, mainly memory B cells. In mouse, CD27 has been found on nearly all thymocytes excluding a population of CD46-CD8- precursors. CD27 binds to CD70 and, through this interaction, plays an important role in T cell-B cell interaction. It has been reported that triggering CD27 plays an important role in the maturation of CD4+ and CD8+ effector cells. LG.7F9 cross-reacts with human and rat CD27.

Applications Reported: The LG.7F9 antibody has been reported for use in flow cytometric analysis, and immunoprecipitation. Use of mild detergent lysates is recommended when performing immunoprecipitation with this mAb. LG.7F9 has also been reported in blocking of ligand binding. (Please use Functional Grade purified LG.7F9, cat. 16-0271, in functional assays.).


Applications Tested: The LG.7F9 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Purity: Greater than 90%, as determined by SDS-PAGE.

Aggregation: Less than 10%, as determined by HPLC.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD27 Monoclonal Antibody (LG.7F9), eBioscience



CD27 Antibody (14-0271-82) in Flow

Staining of mouse splenocytes with 0.25 µg Hamster IgG Isotype Control Purified (Product # 14-4888-81) (open histogram) or 0.25 µg Anti-CD27 Purified (filled histogram) followed by Anti-Armenian Hamster IgG FITC (Product # 11-4111). Total viable cells were used for analysis.

[View more figures on thermofisher.com](http://thermofisher.com)

34 References

Immunohistochemistry (1)

Cell reports

Iterative Single-Cell Analyses Define the Transcriptome of the First Functional Hematopoietic Stem Cells.

Authors: Vink CS, Calero-Nieto FJ, Wang X, Maglitto A, Mariani SA, Jawaid W, Göttgens B, Dzierzak E

Species
Mouse

Dilution
1:100

Year
2020

Flow Cytometry (32)

Journal of leukocyte biology

NK cells regulate CXCR2+ neutrophil recruitment during acute lung injury.

"14027182 was used in flow cytometry to elucidate the role of Tbet in acute lung injury"

Authors: Hoegl S, Ehrentraut H, Brodsky KS, Victorino F, Golden-Mason L, Eltzschig HK, McNamee EN

Species
Mouse

Dilution
Not Cited

Year
2017

Journal of immunological methods

In vivo expression of signaling proteins in reconstituted NK cells.

"14-0271 was used in Flow cytometry/Cell sorting to develop a novel technique to generate NK cells in vivo, all of which express a gene of interest."

Authors: Orr SJ, Quigley L, McVicar DW

Species
Mouse

Dilution
Not Cited

Year
2009

[View more Flow references on thermofisher.com](#)

Miscellaneous PubMed (1)

Journal of immunology (Baltimore, Md. : 1950)

Characterization of murine CD70, the ligand of the TNF receptor family member CD27.

Authors: Tesselaar K, Gravestien LA, van Schijndel GM, Borst J, van Lier RA

Species
Not Applicable

Dilution
Not Cited

Year
1997

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.