

CD36 Monoclonal Antibody (eBioNL07 (NL07)), eBioscience™

Product Details	
Size	100 µg
Species	Human
Expression System	Mouse / IgM
Class	Monoclonal
Type	Antibody
Clone	eBioNL07 (NL07)
Conjugate	Unconjugated
Form	Liquid
Concentration	0.5 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage Conditions	4° C
RRID	AB_467217

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.5 µg/test	2 Publications
ChIP assay (ChIP)	-	1 Publication
Immunofluorescence (IF)	-	1 Publication
Immunohistochemistry (IHC)	-	1 Publication

Product Specific Information

Description: The monoclonal antibody eBioNL07 recognizes human CD36, which is a member of the class B scavenger receptor family. CD36 was originally identified as a platelet-membrane glycoprotein also called glycoprotein IV and a receptor for thrombospondin-1 (TSP-1) and extracellular matrix proteins. Binding to TSP-1 is in the CLESH (CD36 LIMP-II Emp sequence homology) domain of CD36. CD36 expression is broad and includes microvascular (but not large vessel) endothelium, adipocytes, skeletal muscle, dendritic cells, epithelia of the retina, breast, and intestine, smooth muscle cells, and hematopoietic cells, including erythroid precursors, platelets, monocytes/macrophages, DCs and megakaryocytes. Expression on platelets is absent on Nak^a negative donors. Unlike other scavenger receptor, CD36 binds LDL that has been exposed to "minimally" oxidizing conditions. CD36 is also a fatty acid translocase (FAT) necessary for the transport of long-chain fatty acids (LCFAs) and therefore may play a role in atherosclerosis.

Applications Reported: This eBioNL07 (NL07) antibody has been reported for use in flow cytometric analysis.


Applications Tested: This eBioNL07 (NL07) antibody has been tested by flow cytometric analysis of human peripheral blood cells. This can be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Purity: Greater than 90%, as determined by SDS-PAGE.

Aggregation: Less than 10%, as determined by HPLC.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD36 Monoclonal Antibody (eBioNL07 (NL07)), eBioscience™



CD36 Antibody (14-0369-82) in Flow

Staining of normal human peripheral blood cells with 0.25 µg of Mouse IgM Isotype Control Purified (Product # 14-4752-82) (open histogram) or 0.25 µg of Anti-Human CD36 Purified (filled histogram) followed by Anti-Mouse IgM PE (Product # 12-5890-82). Cells in the monocyte gate were used for analysis.

[View more figures on thermofisher.com](http://thermofisher.com)

5 References

Flow Cytometry (2)

The Journal of investigative dermatology

Spatial and Single-Cell Transcriptional Profiling Identifies Functionally Distinct Human Dermal Fibroblast Subpopulations.

"Published figure using CD36 monoclonal antibody (Product # 14-0369-82) in Flow Cytometry"

Authors: Philippeos C, Telerman SB, Oulès B, Pisco AO, Shaw TJ, Elgueta R, Lombardi G, Driskell RR, Soldin M, Lynch MD, Watt FM

Species
Not Applicable

Dilution
Not Cited

Year
2018

Scientific reports

IRGM1 regulates oxidized LDL uptake by macrophage via actin-dependent receptor internalization during atherosclerosis.

"Published figure using CD36 monoclonal antibody (Product # 14-0369-82) in Flow Cytometry"

Authors: Xia F, Li R, Wang C, Yang S, Tian L, Dong H, Pei C, He S, Jiang P, Cheng H, Fang S, Li H, Xu H

Species
Not Applicable

Dilution
Not Cited

Year
2013

Immunofluorescence (1)

The Journal of investigative dermatology

Spatial and Single-Cell Transcriptional Profiling Identifies Functionally Distinct Human Dermal Fibroblast Subpopulations.

"Published figure using CD36 monoclonal antibody (Product # 14-0369-82) in Flow Cytometry"

Authors: Philippeos C, Telerman SB, Oulès B, Pisco AO, Shaw TJ, Elgueta R, Lombardi G, Driskell RR, Soldin M, Lynch MD, Watt FM

Species
Not Applicable

Dilution
Not Cited

Year
2018

ChIP assay (1)

Oncogene

Terminal differentiation and loss of tumorigenicity of human cancers via pluripotency-based reprogramming.

"Published figure using CD36 monoclonal antibody (Product # 14-0369-82) in Immunohistochemistry"

Authors: Zhang X, Cruz FD, Terry M, Remotti F, Matushansky I

Species
Not Applicable

Dilution
Not Cited

Year
2013

More applications with references on thermofisher.com

IHC (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.