

CD34 Monoclonal Antibody (RAM34), FITC, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Rat, Mouse
Host/Isotype	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), FITC, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	RAM34
Conjugate	FITC
Form	Liquid
Concentration	0.5 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_465021

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	3 Publications
Immunohistochemistry (Frozen) (IHC (F))	-	2 Publications
Immunocytochemistry (ICC/IF)	-	3 Publications
Flow Cytometry (Flow)	1 µg/test	136 Publications
Functional Assay (FN)	-	1 Publication

Product Specific Information

Description: The RAM34 monoclonal antibody reacts with mouse CD34, also known as mucosialin. It has been reported that the RAM34 antibody can be used to detect CD34+Sca-1+c-Kit+ cells. CD34 is a highly glycosylated (approximately 90-120 kDa) member of the sialomucin family and is expressed by capillary endothelial cells, bone marrow stroma, and a small subpopulation of mouse bone marrow cells. RAM34 has been used to purify mouse hematopoietic stem cells (HSC) to near homogeneity. CD34 expressed on endothelial cells is a ligand for CD62L and plays a role in adhesion. Simultaneous staining of mouse bone marrow cells with a cocktail of antibodies to lineage markers (CD3, CD11b, Ly6G, TER-119 and CD45R/B220) reveals a subset of cells that stain with the RAM34 antibody and express undetectable to low levels of the indicated lineage markers.

Applications Reported: This RAM34 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This RAM34 antibody has been tested by flow cytometric analysis of mouse bone marrow cells. This can be used at less than or equal to 1 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended

that the antibody be carefully titrated for optimal performance in the assay of interest.


Note: When staining with the RAM34 antibody an incubation time of 90 minutes is recommended to obtain the optimal signal to noise ratio.

For more detailed information on staining with RAM34, please refer to Ema et al., listed under References.

Excitation: 488 nm; Emission: 520 nm; Laser: Blue Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD34 Monoclonal Antibody (RAM34), FITC, eBioscience™



CD34 Antibody (11-0341-82) in Flow

Staining of C57Bl/6 bone marrow cells with Anti-Mouse Hematopoietic Lineage Biotin Panel (Product # 88-7774-75) followed by Streptavidin PE (Product # 12-4317-87) and 0.5 µg of Rat IgG2a K Isotype Control FITC (Product # 11-4321-42) (left) or 0.5 µg of Anti-Mouse CD34 FITC (right). Total viable cells were used for analysis.

Immunohistochemistry (3)

Frontiers in endocrinology

Transcriptional Analysis of Sepsis-Induced Activation and Damage of the Adrenal Endothelial Microvascular Cells.

"11-0341-82 was used in Immunohistochemistry to characterize transcriptomic alterations in isolated mouse adrenal microvascular endothelial cells induced by systemic administration of bacterial LPS."

Authors: Chen LS, Singh SP, Müller G, Bornstein SR, Kanczkowski W

Species
Mouse

Dilution
1:50

Year
2020

Cell transplantation

A Novel CXCR4 Antagonist CX549 Induces Neuroprotection in Stroke Brain.

"11-0341 was used in Flow cytometry/Cell sorting to characterise the neuroprotective and neurotrophic effect of a novel C-X-C chemokine receptor type 4 antagonist, CX549."

Authors: Wu KJ, Yu SJ, Shia KS, Wu CH, Song JS, Kuan HH, Yeh KC, Chen CT, Bae E, Wang Y

Species
Mouse

Dilution
1:100

Year
2017

[View more IHC references on thermofisher.com](#)

Immunohistochemistry (Frozen) (2)

The Journal of biological chemistry

The CB(2) cannabinoid receptor controls myeloid progenitor trafficking: involvement in the pathogenesis of an animal model of multiple sclerosis.

Authors: Palazuelos J, Davoust N, Julien B, Hatterer E, Aguado T, Mechoulam R, Benito C, Romero J, Silva A, Guzmán M, Nataf S, Galve-Roperh I

Species
Not Applicable

Dilution
Not Cited

Year
2008

Development, growth & differentiation

Hair cycle-dependent changes of alkaline phosphatase activity in the mesenchyme and epithelium in mouse vibrissal follicles.

Authors: Iida M, Ihara S, Matsuzaki T

Species
Not Applicable

Dilution
Not Cited

Year
2007

More applications with references on thermofisher.com

ICC/IF (3)

Flow (136)

FN (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.