

IL-6 Monoclonal Antibody (MQ2-13A5), eBioscience™

Product Details

Size	50 µg
Species Reactivity	Human
Published Species	Mouse, Human
Host/Isotype	Rat / IgG1, kappa
Class	Monoclonal
Type	Antibody
Clone	MQ2-13A5
Conjugate	Unconjugated
Form	Liquid
Concentration	0.5 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C
RRID	AB_468426

Applications	Tested Dilution	Publications
Immunocytochemistry (ICC/IF)	-	1 Publication
Flow Cytometry (Flow)	-	5 Publications
ELISA (ELISA)	2-8 µg/mL	8 Publications
Neutralization (Neu)	-	2 Publications
Inhibition Assays (IA)	-	1 Publication
T-Cell Activation (TCA)	-	1 Publication
Miscellaneous PubMed (Misc)	-	1 Publication

Product Specific Information

Description: The MQ2-13A5 antibody reacts with human interleukin-6 (IL-6), a 21-28 kDa cytokine secreted by a variety of cell types.

Applications Reported: The MQ2-13A5 antibody has been reported for use in capture of human IL-6 by ELISA, intracellular staining for flow cytometric analysis, and for neutralizing IL-6 bioactivity.

Applications Tested: The MQ2-13A5 antibody has been tested as the capture antibody in a sandwich ELISA for analysis of human Interleukin-6 (IL-6) in combination with the biotin MQ2-39C3 (13-7068) antibody for detection and recombinant human IL-6 (14-8069) as the standard. A suitable range of concentrations of this antibody for ELISA capture is 2-8 µg/mL. A standard curve consisting of doubling dilutions of the recombinant standard over the range of 1000 pg/mL - 8 pg/mL should be included in each ELISA plate.

Purity: Greater than 90%, as determined by SDS-PAGE.

Aggregation: Less than 10%, as determined by HPLC.

Filtration: 0.2 µm post-manufacturing filtered.

19 References

Immunocytochemistry (1)

Stem cells (Dayton, Ohio)

Mesenchymal Stromal Cell-Derived Interleukin-6 Promotes Epithelial-Mesenchymal Transition and Acquisition of Epithelial Stem-Like Cell Properties in Ameloblastoma Epithelial Cells.

"Published figure using IL-6 monoclonal antibody (Product # 14-7069-81) in Immunofluorescence"

Authors: Jiang C,Zhang Q,Shanti RM,Shi S,Chang TH,Carrasco L,Alawi F,Le AD

Year
2017

Flow Cytometry (5)

Cancer science

Interleukin 6 regulates the expression of programmed cell death ligand 1 in thyroid cancer.

"Published figure using IL-6 monoclonal antibody (Product # 14-7069-81) in Flow Cytometry"

Authors: Zhang GQ,Jiao Q,Shen CT,Song HJ,Zhang HZ,Qiu ZL,Luo QY

Year
2021

Frontiers in immunology

CD19⁺CD24^{hi}CD38^{hi} B Cells Are Expanded in Juvenile Dermatomyositis and Exhibit a Pro-Inflammatory Phenotype After Activation Through Toll-Like Receptor 7 and Interferon-.

"14-7069-81 was used in Flow Cytometry to identify that immature transitional B cells were significantly expanded in active JDM, actively dividing, and correlated positively with disease activity."

Authors: Piper CJM,Wilkinson MGL,Deakin CT,Otto GW,Dowle S,Duurland CL,Adams S,Marasco E,Rosser EC,Radziszewska A,Carsetti R,Ioannou Y,Beales PL,Kelberman D,Isenberg DA,Mauri C,Nistala K,Wedderburn LR

Year
2019

Species
Human

[View more Flow references on thermofisher.com](#)

ELISA (8)

Scientific reports

PLC2 regulates TREM2 signalling and integrin-mediated adhesion and migration of human iPSC-derived macrophages.

"Published figure using IL-6 monoclonal antibody (Product # 14-7069-81) in ELISA"

Authors: Obst J,Hall-Roberts HL,Smith TB,Kreuzer M,Magno L,Di Daniel E,Davis JB,Mead E

Year
2021

[View more ELISA references on thermofisher.com](#)

More applications with references on thermofisher.com

Neu (2) IA (1) TCA (1) Misc (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.