

Phospho-STAT3 (Tyr705) Monoclonal Antibody (LUVNKLA), FITC, eBioscience™

| Product Details | |
|-----------------------------|--|
| Size | 100 Tests |
| Species Reactivity | Human, Mouse |
| Published Species | Human |
| Host/Isotype | Mouse / IgG2b, kappa |
| Recommended Isotype Control | Mouse IgG2b kappa Isotype Control (eBMG2b), FITC, eBioscience™ |
| Class | Monoclonal |
| Type | Antibody |
| Clone | LUVNKLA |
| Conjugate | FITC |
| Excitation/Emission Max | 498/517 nm |
| Form | Liquid |
| Concentration | 5 µL/Test |
| Purification | Affinity chromatography |
| Storage buffer | PBS, pH 7.2, with 0.2% BSA |
| Contains | 0.09% sodium azide |
| Storage conditions | 4° C, store in dark, DO NOT FREEZE! |
| RRID | AB_2572522 |

| Applications | Tested Dilution | Publications |
|-----------------------|----------------------|----------------|
| Flow Cytometry (Flow) | 5 µL (0.125 µg)/test | 6 Publications |

Product Specific Information

Description: This LUVNKLA monoclonal antibody recognizes human and mouse signal transducer and activator of transcription 3 (STAT3) when phosphorylated on tyrosine 705 (Y705). The STAT family represents seven transcription factors (STATs 1, 2, 3, 4, 5A, 5B, and 6) that are involved in many cellular processes including apoptosis, cell differentiation, and proliferation in a cell type- and cytokine-specific manner. STAT proteins are activated by ligand binding to cytokine receptors that associate with Janus kinase (JAK) family members.

Following their phosphorylation by JAKs, STAT proteins translocate to the nucleus where they bind to DNA and regulate transcription of specific genes in a cell type- and cytokine-specific manner. STAT3 is activated downstream of numerous cytokines including interferons, IL-5, IL-6, IL-10, and LIF. STAT3 is important for the differentiation of Th17 cells and mediates a variety of cellular processes including cell growth and survival. The importance of STAT3 is highlighted by both loss-of-function and gain-of-function mutations. Deletion of STAT3 in T cells results in decreased IL-6- and IL-2-mediated proliferation, while deletion of STAT3 in neutrophils and macrophages results in increased susceptibility to LPS-induced endotoxic shock and increased production of the pro-inflammatory cytokines IL-6 and TNF alpha. Hyper STAT3 activity is associated with poor prognosis of many different cancers.

Applications Reported: This LUVNKLA antibody has been reported for use in intracellular staining followed by flow cytometric analysis.

Applications Tested: This LUVNKLA antibody has been pre-titrated and tested by intracellular staining followed by flow


cytometric analysis of stimulated normal human peripheral blood cells. This can be used at 5 μ L (0.125 μ g) per test. A test is defined as the amount (μ g) of antibody that will stain a cell sample in a final volume of 100 μ L. Cell number should be determined empirically but can range from 10^5 to 10^8 cells/test.

Staining Protocol: We recommend using Protocol C: Two-step protocol: Fixation/Methanol. Protocol A: Two-step protocol: intracellular (cytoplasmic) proteins and Protocol B: One-step protocol: intracellular (nuclear) proteins cannot be used. All Protocols can be found in the Flow Cytometry Protocols: "Staining Intracellular Antigens for Flow Cytometry Protocol" located in the Best Protocols Section under the Resources tab online.

Excitation: 488 nm; Emission: 520 nm; Laser: Blue Laser.

Filtration: 0.2 μ m post-manufacturing filtered.

Product Images For Phospho-STAT3 (Tyr705) Monoclonal Antibody (LUVNKLA), FITC, eBioscience™



Phospho-STAT3 (Tyr705) Antibody (11-9033-42) in Flow
Intracellular staining of untreated (left) or 15-minute IL-6 treated (right) normal human peripheral blood cells with Anti-Human CD4 eFluor® 450 (Product # 48-0049-42) and Anti-Human/Mouse phospho-STAT3 (Y705) FITC. Cells in the lymphocyte gate were used for analysis. Cells were stained using the Intracellular Fixation/Methanol protocol.

View more figures on thermofisher.com

6 References

Flow Cytometry (6)

| | |
|---|---|
| Journal for immunotherapy of cancer Combinatorial immunotherapy of N-803 (IL-15 superagonist) and dinutuximab with ex vivo expanded natural killer cells significantly enhances in vitro cytotoxicity against GD2⁺ pediatric solid tumors and in vivo survival of xenografted immunodeficient NSG mice. "Published figure using Phospho-STAT3 (Tyr705) monoclonal antibody (Product # 11-9033-42) in Flow Cytometry" Authors: Chu Y,Nayyar G,Jiang S,Rosenblum JM,Soon-Shiong P,Safrit JT,Lee DA,Cairo MS | Year 2021 |
| Cell reports Inflammation-driven deaminase deregulation fuels human pre-leukemia stem cell evolution. "11-9033-42 was used in Flow Cytometry to show that lentiviral ADAR1p150 expression enhances pre-LSC replating and STAT3 splice isoform switching." Authors: Jiang Q,Isquith J,Ladel L,Mark A,Holm F,Mason C,He Y,Mondala P,Oliver I,Pham J,Ma W,Reynoso E,Ali S, Morris IJ,Diep R,Nasamran C,Xu G,Sasik R,Rosenthal SB,Birmingham A,Coso S,Pineda G,Crews L,Donohoe ME, Venter JC,Whisenant T,Mesa RA,Alexandrov LB,Fisch KM,Jamieson C | Year 2021 Species Human Dilution 1:10 |

View more Flow references on thermofisher.com

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.