CD69 Monoclonal Antibody (H1.2F3), PE-Cyanine5, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Mouse, Human
Host/Isotype	Armenian hamster / IgG
Recommended Isotype Control	Armenian Hamster IgG Isotype Control (eBio299Arm), PE-Cyanine5, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	H1.2F3
Conjugate	PE-Cyanine5
Excitation/Emission Max	568/666 nm
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_468772

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.5 µg/test	57 Publications

Product Specific Information

Description: The H1.2F3 monoclonal antibody reacts with mouse CD69, also known as very early activation antigen (VEA). CD69 is approximately 35 kDa and is expressed on the surface as a disulfide-linked dimer. While a small subset of lymphocytes in the thymus, spleen and lymph nodes express this antigen, activation of both T and B cells rapidly upregulates the surface expression of CD69, suggesting a role for CD69 in lymphocyte development and activation.

Applications Reported: The H1.2F3 antibody has been reported for use in flow cytometric analysis.

Applications Tested: The H1.2F3 antibody has been tested by flow cytometric analysis of resting and activated mouse splenocytes. This can be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10^5 to 10^8 cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.


Light sensitivity: This tandem dye is sensitive photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (cat. 00-8222) (100 µL cell sample + 100 µL IC Fixation Buffer) or 1-step Fix/Lyse Solution (cat. 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency /compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 488-561 nm; Emission: 667 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD69 Monoclonal Antibody (H1.2F3), PE-Cyanine5, eBioscience™



CD69 Antibody (15-0691-82) in Flow
Staining of non-stimulated (left) and 5-hour PMA activated C57Bl/6 splenocytes with staining buffer (autofluorescence) (open histogram) or 0.25 µg Anti-Mouse CD69 PE-Cyanine5 (filled histogram).Total cells were used for analysis.

View more figures on thermofisher.com

57 References

Flow Cytometry (57)

NPJ vaccines

Enhanced germinal center reaction by targeting vaccine antigen to major histocompatibility complex class II molecules.

"Published figure using CD69 monoclonal antibody (Product # 15-0691-82) in Flow Cytometry"

Authors: Andersen TK,Huszthy PC,Gopalakrishnan RP,Jacobsen JT,Fauskanger M,Tveita AA,Grødeland G,Bogen B

Year
2023

Theranostics

HSF1 promotes CD69^{+} Treg differentiation to inhibit colitis progression.

"Published figure using CD69 monoclonal antibody (Product # 15-0691-82) in Flow Cytometry"

Authors: Yu L,Zhou B,Zhu Y,Li L,Zhong Y,Zhu L,Wang H,Chen H,Xu J,Guo T,Feng L,Wang X,Cai Z,Wang J,Jin H

Year
2023

View more Flow references on thermofisher.com

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.