

CD15 Monoclonal Antibody (HI98), PE, eBioscience™

Product Details	
Size	100 Tests
Species Reactivity	Human
Published Species	Human
Host/Isotype	Mouse / IgM, kappa
Class	Monoclonal
Type	Antibody
Clone	HI98
Conjugate	PE
Excitation/Emission Max	565/576 nm
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.2% BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_11219674

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	5 µL (0.125 µg)/test	2 Publications

Product Specific Information


Description: The HI98 monoclonal antibody reacts with human CD15, Lewis X. This 3-fucosyl-N-acetyllactosamine carbohydrate moiety is expressed by granulocytes. Monocytes express this structure at varying degree while lymphocytes are negative.

Applications Reported: This HI98 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This HI98 antibody has been pre-titrated and tested by flow cytometric analysis of normal human peripheral blood cells. This can be used at 5 µL (0.125 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test.

Excitation: 488-561 nm; **Emission:** 578 nm; **Laser:** Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 µm post-manufacturing filtered.



CD15 Antibody (12-0159-42) in Flow
Staining of normal human peripheral blood cells with Mouse IgM Isotype Control PE (blue histogram) or Anti-Human CD15 PE (purple histogram). Cells in the granulocyte gate were used for analysis.

2 References

Flow Cytometry (2)

<p>Breast cancer research and treatment</p> <p>A high-risk luminal A dominant breast cancer subtype with increased mobility.</p> <p>"Published figure using CD15 monoclonal antibody (Product # 12-0159-42) in Flow Cytometry"</p> <p>Authors: Guo L,Chen G,Zhang W,Zhou L,Xiao T,Di X,Wang Y,Feng L,Zhang K</p>	<p>Year</p> <p>2019</p>
<p>Nature biotechnology</p> <p>High-throughput measurement of single-cell growth rates using serial microfluidic mass sensor arrays.</p> <p>"12-0159 was used in Flow cytometry/Cell sorting to reveal subpopulations of cells with divergent growth kinetics and assess cellular responses to antibiotics and antimicrobial peptides within minutes."</p> <p>Authors: Cermak N,Olcum S,Delgado FF,Wasserman SC,Payer KR,A Murakami M,Knudsen SM,Kimmerling RJ, Stevens MM,Kikuchi Y,Sandikci A,Ogawa M,Agache V,Bal��ras F,Weinstock DM,Manalis SR</p>	<p>Year</p> <p>2016</p> <p>Species</p> <p>Human</p>

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.