

CD45 Monoclonal Antibody (30-F11), APC, eBioscience™

Product Details

Size	100 µg
Species Reactivity	Mouse
Published Species	Mouse, Human
Host/Isotype	Rat / IgG2b, kappa
Recommended Isotype Control	Rat IgG2b kappa Isotype Control (eB149/10H5), APC, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	30-F11
Conjugate	APC
Excitation/Emission Max	651/660 nm
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_469392

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	1 Publication
Immunohistochemistry (Frozen) (IHC (F))	-	2 Publications
Immunocytochemistry (ICC/IF)	-	1 Publication
Flow Cytometry (Flow)	0.125 µg/test	131 Publications
Immunoprecipitation (IP)	-	1 Publication
Miscellaneous PubMed (Misc)	-	1 Publication

Product Specific Information

Description: The 30-F11 monoclonal antibody reacts with all isoforms of mouse CD45, also known as Leukocyte Common Antigen (LCA). CD45 is expressed by all hematopoietic cells excluding mature erythrocytes and platelets. The cytoplasmic portion of CD45 has tyrosine phosphatase enzymatic activity and plays an important role in activation of lymphocytes.


Applications Reported: The 30-F11 antibody has been reported for use in flow cytometric analysis.

Applications Tested: The 30-F11 antibody has been tested by flow cytometric analysis of mouse bone marrow cells and splenocytes. This can be used at less than or equal to 0.125 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Excitation: 633-647 nm; Emission: 660 nm; Laser: Red Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD45 Monoclonal Antibody (30-F11), APC, eBioscience™



CD45 Antibody (17-0451-82) in Flow
C57BL/6 mouse bone marrow cells were stained with TER-119 Monoclonal Antibody, FITC (Product # 11-5921-82) and 0.06 µg of Rat IgG2b kappa Isotype Control, APC (Product # 17-4031-82) (left) or 0.06 µg of CD45 Monoclonal Antibody, APC (right). Total viable cells were used for analysis.

Immunohistochemistry (1)

Nature communications	Year 2021
Genetic fate-mapping reveals surface accumulation but not deep organ invasion of pleural and peritoneal cavity macrophages following injury.	Species Mouse
"17-0451-82 was used in Flow Cytometry to report a dual recombinase-mediated genetic system designed to trace cavity macrophages in vivo by intersectional detection of two characteristic markers."	Dilution 1:400
Authors: Jin H,Liu K,Tang J,Huang X,Wang H,Zhang Q,Zhu H,Li Y,Pu W,Zhao H,He L,Li Y,Zhang S,Zhang Z,Zhao Y, Qin Y,Pflanz S,Kasmi KEI,Zhang W,Liu Z,Ginhoux F, Ji Y,He B,Wang L,Zhou B	

Immunohistochemistry (Frozen) (2)

Journal of neuroinflammation	Year 2020
CRID3, a blocker of apoptosis associated speck like protein containing a card, ameliorates murine spinal cord injury by improving local immune microenvironment.	Species Mouse
"17-0451-83 was used in Immunohistochemistry (Frozen) to study the effect of CRID3 on the local microenvironment and the possible role in neuroprotection following spinal cord injury."	Dilution 1:200
Authors: Chen YQ,Wang SN,Shi YJ,Chen J,Ding SQ,Tang J,Shen L,Wang R,Ding H,Hu JG,Lü HZ	

Proceedings of the National Academy of Sciences of the United States of America	Year 2011
Three chemokine receptors cooperatively regulate homing of hematopoietic progenitors to the embryonic mouse thymus.	Species Mouse
"17-0451 was used in Immunohistochemistry on frozen tissues to show that chemotaxis is the key mechanism regulating thymus homing in the mouse embryo."	
Authors: Calderón L,Boehm T	

Immunocytochemistry (1)

EBioMedicine	Year 2020
A liquid biopsy for detecting circulating mesothelial precursor cells: A new biomarker for diagnosis and prognosis in mesothelioma.	Species Mouse
"17-0451-83 was used in Immunocytochemistry to show the clinical significance of detecting MPC in blood for early-stage diagnosis and prognosis of mesothelioma."	
Authors: Duong BTV,Wu L,Green BJ,Bavaghar-Zaeimi F,Wang Z,Labib M,Zhou Y,Cantu FJP,Jeganathan T,Popescu S, Pantea J,de Perrot M,Kelley SO	

More applications with references on thermofisher.com

- Flow (131)
- IP (1)
- Misc (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.