

IL-10 Monoclonal Antibody (JES5-16E3), APC, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Mouse
Host/Isotope	Rat / IgG2b, kappa
Recommended Isotype Control	Rat IgG2b kappa Isotype Control (eB149/10H5), APC, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	JES5-16E3
Conjugate	APC
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.1% gelatin
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_469502

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.125 µg/test	56 Publications

Product Specific Information

Description: The JES5-16E3 antibody reacts with mouse interleukin-10 (IL-10). Mouse IL-10 is an ~18 kDa factor also known as Cytokine Synthesis Inhibitory Factor (CSIF). In the mouse, Th2 cells, B1 cells, macrophages, and keratinocytes are the major cell subsets that produce IL-10. IL-10 inhibits synthesis of Th1 cytokines and proliferation of T cells, and acts as a costimulatory signal for mast cells, developing thymocytes and the Th2 response.

Applications Reported: The JES5-16E3 antibody has been reported for use in capture of mouse IL-10 by ELISA and ELISPOT, intracellular staining for flow cytometric analysis, IHC, and neutralization of IL-10 bioactivity.

Applications Tested: The JES5-16E3 antibody has been tested by intracellular staining with flow cytometric analysis and can be used at less than or equal to 0.125 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Excitation: 633-647 nm; **Emission:** 660 nm; **Laser:** Red Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Flow Cytometry (56)

Oncoimmunology

Anti-melanoma vaccines engineered to simultaneously modulate cytokine priming and silence PD-L1 characterized using *ex vivo* myeloid-derived suppressor cells as a readout of therapeutic efficacy.

"17-7101 was used in Flow cytometry/Cell sorting to show that the simultaneous delivery of IL12 and a PD-L1-silencing shRNA exhibits therapeutically relevant anti-tumour activities."

Authors: Liechtenstein T,Perez-Janices N,Blanco-Luquin I,Goyvaerts C,Schwarze J,Dufait I,Lanna A,Ridder M,Guerrero-Setas D,Breckpot K,Escors D

Species
Mouse

Dilution
Not Cited

Year
2020

Frontiers in immunology

Limited Foxp3⁺ Regulatory T Cells Response During Acute *Trypanosoma cruzi* Infection Is Required to Allow the Emergence of Robust Parasite-Specific CD8⁺ T Cell Immunity.

"17-7101 was used in Flow cytometry/Cell sorting to study the role of regulatory T cells during *Trypanosoma cruzi* infection."

Authors: Araujo Furlan CL,Tosello Boari J,Rodriguez C,Canale FP,Fiocca Vernengo F,Boccardo S,Beccaria CG,Adoue V,Joffre O,Gruppi A,Montes CL,Acosta Rodriguez EV

Species
Mouse

Dilution
Not Cited

Year
2019

[View more Flow references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.