

LAP (Latency Associated peptide) Monoclonal Antibody (FNLAP), APC, eBioscience™

| Product Details | |
|-----------------------------|--|
| Size | 100 Tests |
| Species Reactivity | Human |
| Published Species | Human |
| Host/Isotype | Mouse / IgG1, kappa |
| Recommended Isotype Control | Mouse IgG1 kappa Isotype Control (P3.6.2.8.1), APC, eBioscience™ |
| Class | Monoclonal |
| Type | Antibody |
| Clone | FNLAP |
| Conjugate | APC |
| Excitation/Emission Max | 651/660 nm |
| Immunogen | E. coli derived hLAP-TGFb, mixed with VB3A9 |
| Form | Liquid |
| Concentration | 5 µL/Test |
| Purification | Affinity chromatography |
| Storage buffer | PBS, pH 7.2, with 0.2% BSA |
| Contains | 0.09% sodium azide |
| Storage conditions | 4° C, store in dark, DO NOT FREEZE! |
| RRID | AB_2573316 |

| Applications | Tested Dilution | Publications |
|-----------------------|--------------------|----------------|
| Flow Cytometry (Flow) | 5 µL (0.5 µg)/test | 6 Publications |

Product Specific Information

Description: The FNLAP monoclonal antibody reacts with human latency associated peptide (LAP, pro-TGF beta 1, LAP/TGF beta 1). Many different cells produce TGF beta and it mediates effects on the proliferation, differentiation and function of many cell types. TGF beta is synthesized as a precursor that contains LAP at the N-terminus and mature TGF beta at the C-terminus. Processing and cleavage of the precursor protein between amino acids 278 and 279 results in the formation of LAP dimers and TGF beta dimers that then non-covalently associate with each other to form the small latent TGF beta complex. LAP is secreted and can be found in the extracellular matrix. In addition, LAP can also be expressed on platelets and activated regulatory T cells. It is believed that this surface-expressed LAP is due to the binding of LAP to GARP (LRRC32), which is a transmembrane protein that is also found at high levels on platelets and activated regulatory T cells.


Applications Reported: This FNLAP antibody has been reported for use in flow cytometric analysis.

Applications Tested: This FNLAP antibody has been pre-titrated and tested by flow cytometric analysis of stimulated normal human peripheral blood cells using the Foxp3/Transcription Factor Staining Buffer Set (cat. 00-5523) and protocol. Please refer to Best Protocols: Protocol B: One step protocol for (nuclear) intracellular proteins located under the Resources Tab online. This can be used at 5 µL (0.5 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test.

Excitation: 633-647 nm; Emission: 660 nm; Laser: Red Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For LAP (Latency Associated peptide) Monoclonal Antibody (FNLAP), APC, eBioscience™



LAP (Latency Associated peptide) Antibody (17-9829-42) in Flow
Normal human peripheral blood cells were stimulated overnight with Human IL-2 Recombinant Protein (Product # 14-8029-81), Anti-Human CD3, and Anti-Human CD28 Functional Grade Purifieds (Product # 16-0037-81 and Product # 16-0289-81). These cells were then stained with Fixable Viability Dye eFluor® 450 (Product # 65-0863-14), followed by surface staining with Mouse IgG1 K Isotype Control APC (Product # 17-4714-81) (left) or Anti-Human LAP (Latency Associated Peptide) APC (right), then intracellular staining with Anti-Human Foxp3 PE-eFluor® 610 (Product # 61-4776-42) using the Foxp3/Transcription Factor Staining Buffer Set (Product # 00-5523-00) and protocol. Viable CD4+ lymphocytes were used for analysis.

View more figures on thermofisher.com

6 References

Flow Cytometry (6)

| | |
|--|-------------------------|
| <p>eLife</p> <p>Dendritic cell Piezo1 directs the differentiation of T_H1 and T_{reg} cells in cancer.</p> <p>"Published figure using LAP (Latency Associated peptide) monoclonal antibody (Product # 17-9829-42) in Flow Cytometry"</p> <p>Authors: Wang Y,Yang H,Jia A,Wang Y,Yang Q,Dong Y,Hou Y,Cao Y,Dong L,Bi Y,Liu G</p> | <p>Year</p> <p>2022</p> |
| <p>JCI insight</p> <p>Systematic testing and specificity mapping of alloantigen-specific chimeric antigen receptors in regulatory T cells.</p> <p>"Published figure using LAP (Latency Associated peptide) monoclonal antibody (Product # 17-9829-42) in Flow Cytometry"</p> <p>Authors: Dawson NA,Lamarche C,Hoeppli RE,Bergqvist P,Fung VC,Mclver E,Huang Q,Gillies J,Speck M,Orban PC, Bush JW,Mojibian M,Levings MK</p> | <p>Year</p> <p>2019</p> |

View more Flow references on thermofisher.com

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.