

Connexin 26 Monoclonal Antibody (CX-12H10)

Product Details

Size	100 µg
Species Reactivity	Human, Mouse, Rat
Published Species	Rat, Non-human primate, Bat, Human, Mouse
Host/Isotype	Mouse / IgG1, kappa
Class	Monoclonal
Type	Antibody
Clone	CX-12H10
Conjugate	Unconjugated
Immunogen	Synthetic peptide corresponding to a segment of the cytoplasmic loop of rat Connexin-26.
Form	Liquid
Concentration	0.5 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.4
Contains	0.1% sodium azide
Storage conditions	-20°C
RRID	AB_2533036

Applications	Tested Dilution	Publications
Western Blot (WB)	1-2 µg/mL	18 Publications
Immunohistochemistry (IHC)	-	25 Publications
Immunohistochemistry (Paraffin) (IHC (P))	-	1 Publication
Immunohistochemistry (Frozen) (IHC (F))	Assay-dependent	5 Publications
Immunocytochemistry (ICC/IF)	-	25 Publications
ELISA (ELISA)	0.1-1 µg/mL	-
Immunoprecipitation (IP)	-	1 Publication
Miscellaneous PubMed (Misc)	-	8 Publications


Product Specific Information

13-8100 reacts strongly with Connexin-26, which has a predicted molecular weight of 26.5 kDa. Reactivity of this antibody on western blots has been confirmed by using extracts from mouse liver, mouse brain, and rat brain and it appears to exhibit minimal cross-reaction with Cx30 by western blotting. The degree of cross-reaction with Cx30 by IHC is uncertain, but may be influenced by fixation conditions.

Product Images For Connexin 26 Monoclonal Antibody (CX-12H10)

Connexin 26 Antibody (13-8100) in WB

Western blot analysis of Connexin26 (Cx26) was performed by loading 30 µg of protein from mouse liver homogenate (not boiled) and 7 µL of EZ-RUN Prestained Rec Protein Ladder per well onto a 10% Tris-Hcl polyacrylamide gel. Proteins were transferred to a nitrocellulose membrane and blocked in blocking buffer composed of 20 mM Tris-HCl pH 8, 150 mM NaCl and 0.2% Tween-20 (TBST) supplemented with 5% skim milk powder (Carnation) for 1 hr at room temperature. Cx26 was detected at ~26 kDa using an anti-Cx26 antibody (Product # 13-8100, lane 1) at a dilution of 2 µg/mL in TBST supplemented with 1% skim milk powder and incubated overnight at 4°C on a rocking platform, followed by washing and incubation with a goat anti-mouse IgG horse radish peroxidase (HRP) conjugated secondary antibody at a dilution of 1:5,000 in TBST for 1 hr at room temperature. Lane 2: secondary antibody alone (primary omission). The upper band detected represents mouse IgG contamination in the mouse liver sample. Chemiluminescent detection was performed using Pierce ECL Western blotting substrate (Product # 32209). Data courtesy of Dr. James Nagy's lab.



View more figures on thermofisher.com

Western Blot (18)

<p>Frontiers in cell and developmental biology</p> <p>GJB2 Mutations Linked to Hearing Loss Exhibit Differential Trafficking and Functional Defects as Revealed in Cochlear-Relevant Cells.</p> <p>"Published figure using Connexin 26 monoclonal antibody (Product # 13-8100) in Western Blot"</p> <p>Authors: Beach R,Abitbol JM,Allman BL,Esseltine JL,Shao Q,Laird DW</p>	<p>Year 2020</p> <p>Species Mouse</p> <p>Dilution 1:200</p>
<p>The Journal of investigative dermatology</p> <p>Allele-Specific Small Interfering RNA Corrects Aberrant Cellular Phenotype in Keratitis-Ichthyosis-Deafness Syndrome Keratinocytes.</p> <p>"13-8100 was used in Western Blotting to provide an important proof-of-concept and model system for the potential use of allele-specific small interfering RNA in treating KID syndrome and other dominant genetic conditions."</p> <p>Authors: Lee MY,Wang HZ,White TW,Brooks T,Pittman A,Halai H,Petrova A,Xu D,Hart SL,Kinsler VA,Di WL</p>	<p>Year 2020</p> <p>Species Human</p>

[View more WB references on thermofisher.com](#)

Immunohistochemistry (25)

<p>Genes</p> <p>Dynamic Spatiotemporal Expression Changes in Connexins of the Developing Primate's Cochlea.</p> <p>"Published figure using Connexin 26 monoclonal antibody (Product # 13-8100) in Immunohistochemistry"</p> <p>Authors: Hosoya M,Fujioka M,Murayama AY,Ogawa K,Okano H,Ozawa H</p>	<p>Year 2021</p> <p>Species Non-human primate</p>
<p>International journal of molecular sciences</p> <p>Dysregulation of Connexin Expression Plays a Pivotal Role in Psoriasis.</p> <p>"Published figure using Connexin 26 monoclonal antibody (Product # 13-8100) in Immunohistochemistry"</p> <p>Authors: O'Shaughnessy EM,Duffy W,Garcia-Vega L,Hussey K,Burden AD,Zamiri M,Martin PE</p>	<p>Year 2021</p>

[View more IHC references on thermofisher.com](#)

More applications with references on thermofisher.com

- IHC (P) (1)
- IHC (F) (5)
- ICC/IF (25)
- IP (1)
- Misc (8)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.