

CD90.2 (Thy-1.2) Monoclonal Antibody (30-H12), eBioscience™

Product Details

Size	100 µg
Species Reactivity	Mouse
Published Species	Rat, Mouse
Host/Isotype	Rat / IgG2b, kappa
Class	Monoclonal
Type	Antibody
Clone	30-H12
Conjugate	Unconjugated
Form	Liquid
Concentration	0.5 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C
RRID	AB_467382

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	2 Publications
Immunohistochemistry (Frozen) (IHC (F))	Assay-Dependent	-
Immunocytochemistry (ICC/IF)	-	3 Publications
Flow Cytometry (Flow)	0.125 µg/test	12 Publications
Functional Assay (FN)	Assay-Dependent	1 Publication
Miscellaneous PubMed (Misc)	-	2 Publications

Product Specific Information

Description: The 30-H12 monoclonal antibody reacts with mouse CD90.2, also known as Thy-1.2, a GPI-linked membrane molecule. CD90.2 is expressed by mouse thymocytes and mature T cells as well as neurons in CD90.2-expressing mouse strains. These strains include BALB/c, CBA, C3H, C57BL/6, C58/J, SJL and others. Cells from CD90.1-expressing strains including PL and AKR do not stain with 30-H12. CD90 is involved in regulation of adhesion and signal transduction by T cells.

Applications Reported: The 30-H12 antibody has been reported for use in flow cytometric analysis, and immunohistochemical staining of frozen tissue sections. It has also been reported in in vivo and in vitro depletion. (Please use Functional Grade purified 30-H12, cat. 16-0903, in functional assays.).


Applications Tested: The 30-H12 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.125 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Purity: Greater than 90%, as determined by SDS-PAGE.

Aggregation: Less than 10%, as determined by HPLC.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD90.2 (Thy-1.2) Monoclonal Antibody (30-H12), eBioscience™



CD90.2 (Thy-1.2) Antibody (14-0903-82) in Flow
Staining of BALB/c splenocytes with 0.06 µg of Rat IgG2a K Isotype Control Purified (Product # 14-4031-82) (open histogram) or 0.06 µg of Anti-Mouse CD90-2 (Thy-1-2) Purified (filled histogram) followed by Anti-Rat IgG FITC (Product # 11-4811-85). Cells in the lymphocyte gate were used for analysis.

[View more figures on thermofisher.com](#)

Immunohistochemistry (2)

<p>Nature cell biology</p> <p>Denervation-activated STAT3-IL-6 signalling in fibro-adipogenic progenitors promotes myofibres atrophy and fibrosis.</p> <p>"Published figure using CD90.2 (Thy-1.2) monoclonal antibody (Product # 14-0903-82) in Immunohistochemistry"</p> <p>Authors: Madaro L,Passafaro M,Sala D,Etzaniz U,Lugarini F,Proietti D,Alfonsi MV,Nicoletti C,Gatto S,De Bardi M,Rojas-García R,Giordani L,Marinelli S,Pagliarini V,Sette C,Sacco A,Puri PL</p>	<p>Year 2018</p>
--	----------------------

<p>Nature communications</p> <p>A quiescent cell population replenishes mesenchymal stem cells to drive accelerated growth in mouse incisors.</p> <p>"Published figure using CD90.2 (Thy-1.2) monoclonal antibody (Product # 14-0903-82) in Immunofluorescence"</p> <p>Authors: An Z,Sabalic M,Bloomquist RF,Fowler TE,Streelman T,Sharpe PT</p>	<p>Year 2018</p>
---	----------------------

Immunocytochemistry (3)

<p>Nature cell biology</p> <p>Denervation-activated STAT3-IL-6 signalling in fibro-adipogenic progenitors promotes myofibres atrophy and fibrosis.</p> <p>"Published figure using CD90.2 (Thy-1.2) monoclonal antibody (Product # 14-0903-82) in Immunohistochemistry"</p> <p>Authors: Madaro L,Passafaro M,Sala D,Etzaniz U,Lugarini F,Proietti D,Alfonsi MV,Nicoletti C,Gatto S,De Bardi M,Rojas-García R,Giordani L,Marinelli S,Pagliarini V,Sette C,Sacco A,Puri PL</p>	<p>Year 2018</p>
--	----------------------

<p>Nature communications</p> <p>A quiescent cell population replenishes mesenchymal stem cells to drive accelerated growth in mouse incisors.</p> <p>"Published figure using CD90.2 (Thy-1.2) monoclonal antibody (Product # 14-0903-82) in Immunofluorescence"</p> <p>Authors: An Z,Sabalic M,Bloomquist RF,Fowler TE,Streelman T,Sharpe PT</p>	<p>Year 2018</p>
---	----------------------

[View more ICC/IF references on thermofisher.com](#)

More applications with references on thermofisher.com

- Flow (12)
- FN (1)
- Misc (2)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.