

IL-4 Monoclonal Antibody (BVD6-24G2), PE-Cyanine7, eBioscience™

Product Details	
Size	100 Tests
Species Reactivity	Mouse
Published Species	Mouse, Human
Host/Isotype	Rat / IgG1, kappa
Recommended Isotype Control	Rat IgG1 kappa Isotype Control (eBRG1), PE-Cyanine7, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	BVD6-24G2
Conjugate	PE-Cyanine7
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.1% gelatin, 0.2% BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_1659721

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	5 µL (0.5 µg)/test	17 Publications
In vitro Assay (IV)	-	1 Publication

Product Specific Information

Description: The BVD6-24G2 antibody reacts with mouse interleukin-4 (IL-4), a 14 kDa cytokine secreted by Th2 cells.

Applications Reported: This BVD6-24G2 antibody has been reported for use in intracellular staining followed by flow cytometric analysis.

Applications Tested: This BVD6-24G2 antibody is offered in 2 formats: - µg size: has been tested intracellular staining and flow cytometric analysis of restimulated mouse splenocytes cultures. This can be used at less than or equal to 1 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest. - test size: has been pre-titrated and tested intracellular staining and flow cytometric analysis of restimulated mouse splenocytes cultures. This can be used at 5 µL (0.5 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test.

Light sensitivity: This tandem dye is sensitive photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (cat. 00-8222) (100 µL cell sample + 100 µL IC Fixation Buffer) or 1-step Fix /Lyse Solution (cat. 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency /compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 488-561 nm; Emission: 775 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 µm post-manufacturing filtered.

18 References

Flow Cytometry (17)

Journal of cellular and molecular medicine

DEK-targeting aptamer DTA-64 attenuates bronchial EMT-mediated airway remodelling by suppressing TGF-1/Smad, MAPK and PI3K signalling pathway in asthma.

"Published figure using IL-4 monoclonal antibody (Product # 25-7042-42) in Flow Cytometry"

Authors: Song Y,Wang Z,Jiang J,Piao Y,Li L,Xu C,Piao H,Li L,Yan G

Species

Not Applicable

Dilution

Not Cited

Year

2020

International journal of molecular medicine

TIM4-TIM1 interaction modulates Th2 pattern inflammation through enhancing SIRT1 expression.

"25-7042 was used in Flow cytometry/Cell sorting to demonstrate that the interaction of T-cell immunoglobulin and mucin domain (TIM)4/TIM1 promotes T helper 2-cell proliferation through enhancing silent information regulator 1 expression in mice with nasal allergic rhinitis."

Authors: Hu T,Fan X,Ma L,Liu J,Chang Y,Yang P,Qiu S,Chen T,Yang L,Liu Z

Species

Mouse

Dilution

1:200

Year

2017

[View more Flow references on thermofisher.com](#)

In vitro Assay (1)

PloS one

The acute environment, rather than T cell subset pre-commitment, regulates expression of the human T cell cytokine amphiregulin.

"25-7042 was used in in vitro experiments to collate a detailed analysis of the regulation of Amphiregulin expression by human T cell subsets."

Authors: Qi Y,Operario DJ,Georas SN,Mosmann TR

Species

Human
Mouse

Dilution

Not Cited
Not Cited

Year

2012

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.