

FOXP3 Monoclonal Antibody (PCH101), PE-Cyanine5.5, eBioscience™

Product Details	
Size	100 Tests
Species Reactivity	Chimpanzee, Cynomolgus monkey, Human, Non-human primate, Rhesus monkey
Published Species	Non-human primate, Virus, Human, Mouse
Host/Isotype	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), PE-Cyanine5.5, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	PCH101
Conjugate	PE-Cyanine5.5
Excitation/Emission Max	564/692 nm
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.2% BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_11218682

Applications	Tested Dilution	Publications
Immunohistochemistry (Paraffin) (IHC (P))	-	1 Publication
Flow Cytometry (Flow)	5 µL (0.125 µg)/test	45 Publications

Product Specific Information

Description: eBioscience offers a panel of monoclonal antibodies to different epitopes of human Foxp3, providing useful tools for investigating the complete expression pattern of Foxp3 at the protein level, and discerning the precise subsets of Foxp3⁺ cells.

The PCH101 antibody reacts with the amino terminus of human foxp3 protein also known as FORKHEAD BOX P3, SCURFIN, and JM2; cross reactivity of this antibody to other proteins has not been determined. Foxp3, a 49-55 kDa protein, is a member of the forkhead/winged-helix family of transcriptional regulators, and was identified as the gene defective in 'scurfy' (sf) mice. Constitutive high expression of Foxp3 mRNA has been shown in CD4⁺CD25⁺ regulatory T cells (Treg cells), and ectopic expression of foxp3 in CD4⁺CD25⁻ cells imparts a Treg phenotype in these cells.

Intracellular staining of human peripheral blood mononuclear cells (PBMCs) with PCH101 antibody using the anti-human Foxp3 Staining Set and protocol reveals approximately 0.5-4% of lymphocytes staining, with the majority of staining occurring in the CD25⁺bright population. This is subject to donor variability.

PCH101 crossreacts with rhesus, chimpanzee and cynomolgus. We recommend the use of CD4 (OKT4, Product # 11-0048-42, or RPA-T4, Product # 11-0049-42, depending on the species) and CD25 (BC96, Product # 17-0259-42).

Applications Reported: This PCH101 antibody has been reported for use in intracellular staining followed by flow cytometric analysis.


Applications Tested: This PCH101 antibody has been pre-titrated and tested by intracellular staining and flow cytometric analysis of normal human peripheral blood cells using the Fcγ3/Transcription Factor Staining Buffer Set and protocol. Please refer to Best Protocols for Staining Protocol (refer to Protocol B: One-step protocol for intracellular (nuclear) proteins). This can be used at 5 μL (0.125 μg) per test. A test is defined as the amount (μg) of antibody that will stain a cell sample in a final volume of 100 μL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test.

Light sensitivity: This tandem dye is sensitive photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (Product # 00-8222) (100 μL cell sample + 100 μL IC Fixation Buffer) or 1-step Fix/Lyse Solution (Product # 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency/compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 488-561 nm; Emission: 695 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Product Images For FOXP3 Monoclonal Antibody (PCH101), PE-Cyanine5.5, eBioscience™



FOXP3 Antibody (35-4776-42)

Intracellular staining of human peripheral blood cells. As expected based on known relative expression patterns, Fcγ3 clone PCH101 stains a subset of the CD4+ T cells and does not stain the CD8+ T cells. Details: Normal human peripheral blood cells were surface stained with CD3 (clone UCHT1), CD4 (clone RPA-T4, top), and CD8 (clone OKT8, bottom), followed by intracellular staining with Rat IgG2a kappa Isotype Control (left) or Fcγ3 (clone PCH101, right) using the Fcγ3/Transcription Factor Staining Buffer Set and protocol. Lymphocytes in the CD3+ gate were used for analysis. {RE}

FOXP3 Antibody (35-4776-42) in Flow

Surface staining of normal human peripheral blood cells with Anti-Human CD4 APC (Product # 17-0048-42) followed by intracellular staining with Rat IgG2a K Isotype Control PE-Cyanine5-5 (Product # 35-4321-82) (left) or Anti-Human Fcγ3 PE-Cyanine5-5 (right) using the Fcγ3/Transcription Factor Staining Buffers (Product # 00-5523-00). Cells in the lymphocyte gate were used for analysis.

View more figures on thermofisher.com

Immunohistochemistry (Paraffin) (1)

Blood	Year 2006
Mucosal but not peripheral FOXP3+ regulatory T cells are highly increased in untreated HIV infection and normalize after suppressive HAART.	
Authors: Epple HJ,Loddenkemper C,Kunkel D,Tröger H,Maul J,Moos V,Berg E,Ullrich R,Schulzke JD,Stein H,Duchmann R,Zeitz M,Schneider T	

Flow Cytometry (45)

European journal of haematology	Year 2023
In chronic lymphocytic leukemia, activation of the thrombopoietin receptor promotes T-cell inhibitory properties, contributing to immunosuppression.	
"Published figure using FOXP3 monoclonal antibody (Product # 35-4776-42) in Flow Cytometry"	
Authors: Ringelstein-Harlev S,Fanadka M,Horowitz NA,Bettman NP,Katz T	

Immunology	Year 2023
AHR/TET2/NT5E axis downregulation is associated with the risk of systemic lupus erythematosus and its progression.	
"Published figure using FOXP3 monoclonal antibody (Product # 35-4776-42) in Flow Cytometry"	
Authors: Cheng HH,Hung-Ke L,Sheu ML,Lee CY,Tsai YC,Lai DW	

[View more Flow references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.