

Noggin Monoclonal Antibody (1H8noggin), eBioscience™

Product Details

Size	100 µg
Host/Isotype	Mouse / IgG2b, kappa
Class	Monoclonal
Type	Antibody
Clone	1H8noggin
Conjugate	Unconjugated
Form	Liquid
Concentration	0.5 mg/mL
Storage conditions	4° C
RRID	AB_2572913

Applications

Tested Dilution

Publications

Immunohistochemistry (Paraffin) (IHC (P))	10 µg/mL	-
Immunocytochemistry (ICC/IF)	Assay-Dependent	-

Product Specific Information

Description: The monoclonal antibody 1H8noggin recognizes human noggin. Noggin is a secreted, glycosylated, chemokine that binds and inhibits TGFbeta (transforming growth factor beta) family members such as bone morphogenic protein-4 and -2 (BMP-4, BMP-2). The binding of noggin to BMPs prevents interaction with signal-transducing BMP receptors (BMPR), responsible for activation of VEGF and other pathways that affect vascular patterning, neural tube formation, mesodermal differentiation, and oligodendroglialogenesis. Noggin expression is restricted both temporally and by cell type, for example by chondrogenic precursor cells during limb development, ectodermal cells in the dorsal neural tube, ependymal cells adjacent to the subventricular zone in adult brain, and stromal cells underlying luminal epithelium.

Applications Reported: This 1H8noggin antibody has been reported for use in immunohistochemical staining of formalin-fixed paraffin embedded tissue sections, microscopy, and immunocytochemistry.

Applications Tested: This 1H8noggin antibody has been tested by immunohistochemistry of formalin-fixed paraffin embedded human tissue using low pH antigen retrieval at less than or equal to 10 µg/mL. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Purity: Greater than 90%, as determined by SDS-PAGE.

Aggregation: Less than 10%, as determined by HPLC.

Filtration: 0.2 µm post-manufacturing filtered.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.