

IL-1 beta Monoclonal Antibody (B122), Functional Grade, eBioscience™

Product Details	
Size	5 mg
Species Reactivity	Mouse, Rat
Published Species	Mouse
Host/Isotype	Armenian hamster / IgG
Recommended Isotype Control	Armenian Hamster IgG Isotype Control (eBio299Arm), Functional Grade, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	B122
Conjugate	Functional Grade
Form	Liquid
Concentration	1 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	no preservative
Storage conditions	4° C
RRID	AB_2866193

Applications	Tested Dilution	Publications
Western Blot (WB)	-	1 Publication
ELISA (ELISA)	0.125 µg/mL	3 Publications
Neutralization (Neu)	Assay-Dependent	3 Publications
Functional Assay (FN)	Assay-Dependent	-

Product Specific Information

Description: The B122 antibody reacts with mouse and rat interleukin-1beta (IL-1beta), a 17 kDa factor secreted primarily by monocytes. IL-1 has effects on T-helper cells, inducing IL-2 secretion and expression of IL-2 receptors.

Applications Reported: The B122 antibody has been reported for use in cytokine neutralization and ELISA capture.

Applications Tested: The Functional Grade Purified B122 antibody has been tested by LAL assay to verify low endotoxin levels, by ELISA, and in bioassay for neutralization of mouse IL-1 beta bioactivity.

The B122 antibody at 0.125 µg/mL has been found to inhibit by 50% the biological effects of 4.0 ng/mL mouse IL-1 beta in a D10 cell proliferation assay. Detailed information and protocols about cytokine bioassays and in vitro cytokine neutralization using antibodies can be found in the BestProtocols® section.

The B122 antibody has been tested as the capture antibody in a sandwich ELISA for analysis of mouse interleukin-1 beta (IL-1 beta) in combination with the biotin anti-mouse Interleukin-1 beta (IL-1 beta) polyclonal (13-7112) antibody for detection and recombinant mouse IL-1 beta (14-8012) as the standard. A suitable range of concentrations of this antibody for ELISA capture is 1-4 µg/mL. A standard curve consisting of doubling dilutions of the recombinant standard over the range of 2000 pg/mL - 15 pg/mL should be included in each ELISA plate.

Storage and handling: Use in a sterile environment.

Filtration: 0.2 µm post-manufacturing filtered.

Purity: Greater than 90%, as determined by SDS-PAGE.

Endotoxin Level: Less than 0.001 ng/µg antibody, as determined by LAL assay.

Aggregation: Less than 10%, as determined by HPLC.

7 References

Western Blot (1)

Islets	Year 2013
The lysine deacetylase inhibitor Givinostat inhibits -cell IL-1 induced IL-1 transcription and processing.	Species Mouse
"16-7012 was used in Western Blotting to demonstrate that inhibition of -cell IL-1 expression and processing and Cxcl10 transcription contributes to the -cell protective actions of KDACi."	
Authors: Dahllöf MS,Christensen DP,Lundh M,Dinareello CA,Mascagni P,Grunnet LG,Mandrup-Poulsen T	

ELISA (3)

Biomolecules & therapeutics	Year 2019
Pro-Inflammatory Role of S1P₃ in Macrophages.	
"Published figure using IL-1 beta monoclonal antibody (Product # 16-7012-81) in ELISA"	
Authors: Heo JY,Im DS	

Scientific reports	Year 2019
Peli1 controls the survival of dopaminergic neurons through modulating microglia-mediated neuroinflammation.	
"Published figure using IL-1 beta monoclonal antibody (Product # 16-7012-81) in ELISA"	
Authors: Dai D,Yuan J,Wang Y,Xu J,Mao C,Xiao Y	

[View more ELISA references on thermofisher.com](#)

Neutralization (3)

Molecular neurodegeneration	Year 2020
NLRP12 collaborates with NLRP3 and NLRC4 to promote pyroptosis inducing ganglion cell death of acute glaucoma.	
"Published figure using IL-1 beta monoclonal antibody (Product # 16-7012-81) in Neutralization"	
Authors: Chen H,Deng Y,Gan X,Li Y,Huang W,Lu L,Wei L,Su L,Luo J,Zou B,Hong Y,Cao Y,Liu Y,Chi W	

[View more Neu references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.