

IL-13 Monoclonal Antibody (eBio13A), Functional Grade, eBioscience™

Product Details	
Size	500 µg
Species Reactivity	Mouse
Published Species	Mouse, Human
Host/Isotype	Rat / IgG1, kappa
Recommended Isotype Control	Rat IgG1 kappa Isotype Control (eBRG1), Functional Grade, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	eBio13A
Conjugate	Functional Grade
Form	Liquid
Concentration	1 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	no preservative
Storage Conditions	4° C
RRID	AB_763558

Applications	Tested Dilution	Publications
Control (Ctrl)	Assay-Dependent	-
ELISA (ELISA)	1-4 µg/mL	-
Functional Assay (FN)	Assay-Dependent	-
Flow Cytometry (Flow)	-	11 Publications
Neutralization (Neu)	-	1 Publication

Product Specific Information

Description: The eBio13A antibody reacts with mouse IL-13. IL-13 is a cytokine produced mainly by Th2 cells, but also by antigen-primed CD8 T cells. IL-13 has a strong involvement in allergic inflammation and parasitic clearing and in cancer models has been shown to have either inhibitory or stimulatory activity depending on the tumor. In humans, IL-13 is found to play a role in isotype switching in B cells. IL-13 is implicating in down modulating macrophage activity, through the reduction of pro-inflammatory cytokines (IL-1, IL-6, IL-8, IL-10, IL-12)

Applications Reported: The eBio13A antibody has been reported useful for ELISA and ELISPOT capture, as well as intracellular staining for flow cytometric analysis.

Applications Tested: The Functional Grade Purified eBio13A antibody has been tested by LAL assay to verify low endotoxin levels and has been tested for ELISA and ELISPOT capture.

The eBio13A antibody has been tested as the capture antibody in a sandwich ELISA (and ELISPOT) for analysis of mouse IL-13, in combination with the biotinylated eBio1316H antibody for detection (13-7135) and recombinant mouse IL-13 (14-8131) as the standard. A suitable range of concentrations of this antibody for ELISA capture is 1.0 - 4.0 µg/mL. A standard curve consisting of doubling dilutions of the recombinant standard over the range of 1000 pg/mL - 8.0 pg/mL should be included in each ELISA plate.

The Functional Grade Purified eBio1316H antibody (16-7135) is recommended for in vitro blocking studies.

Storage and handling: Use in a sterile environment.

Filtration: 0.2 µm post-manufacturing filtered.

Purity: Greater than 90%, as determined by SDS-PAGE.

Endotoxin Level: Less than 0.001 ng/µg antibody, as determined by LAL assay.

Aggregation: Less than 10%, as determined by HPLC.

12 References

Flow Cytometry (11)

Arthritis research and therapy

Fli1-haploinsufficient dermal fibroblasts promote skin-localized transdifferentiation of Th2-like regulatory T cells.

"Published figure using IL-13 monoclonal antibody (Product # 16-7133-85) in Flow Cytometry"

Authors: Saigusa R, Asano Y, Taniguchi T, Hirabayashi M, Nakamura K, Miura S, Yamashita T, Takahashi T, Ichimura Y, Toyama T, Yoshizaki A, Trojanowska M, Sato S

Species
Not Applicable

Dilution
Not Cited

Year
2018

Nature communications

Arf1-mediated lipid metabolism sustains cancer cells and its ablation induces anti-tumor immune responses in mice.

"Published figure using IL-13 monoclonal antibody (Product # 16-7133-85) in Flow Cytometry"

Authors: Wang G, Xu J, Zhao J, Yin W, Liu D, Chen W, Hou SX

Species
Not Applicable

Dilution
Not Cited

Year
2020

[View more Flow references on thermofisher.com](#)

Neutralization (1)

Nature communications

Bacterial colonization dampens influenza-mediated acute lung injury via induction of M2 alveolar macrophages.

"Published figure using IL-13 monoclonal antibody (Product # 16-7133-85) in Neutralization"

Authors: Wang J, Li F, Sun R, Gao X, Wei H, Li LJ, Tian Z

Species
Not Applicable

Dilution
Not Cited

Year
2013

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.