

CD95 (APO-1/Fas) Monoclonal Antibody (15A7), APC, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Mouse, Human
Host/Isotope	Mouse / IgG1, kappa
Recommended Isotype Control	Mouse IgG1 kappa Isotype Control (P3.6.2.8.1), APC, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	15A7
Conjugate	APC
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.1% gelatin
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_10717405

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	1 µg/test	14 Publications

Product Specific Information

Description: The 15A7 monoclonal antibody reacts with mouse CD95 (Fas, Apo-1), a 40-50 kDa member of the TNFR superfamily. CD95 is expressed by a broad range of hematopoietic and non-hematopoietic cells including monocytes, neutrophils, activated lymphocytes and fibroblasts. Interaction of CD95 on mature lymphocytes with its ligand (FasL) induces apoptosis and is thought to be important in peripheral tolerance. 15A7 reacts with mouse CD95 in BALB/c strain and a bit more weakly in C57Bl/6 strain. 15A7 does not induce apoptosis of Fas-expressing cells.


Applications Reported: This 15A7 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This 15A7 antibody has been tested by flow cytometric analysis of mouse thymocytes. This can be used at less than or equal to 1 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Excitation: 633-647 nm; Emission: 660 nm; Laser: Red Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD95 (APO-1/Fas) Monoclonal Antibody (15A7), APC, eBioscience™



CD95 (APO-1/Fas) Antibody (17-0951-82) in Flow

Staining of BALB/c thymocytes with 1 µg of Mouse IgG1 K Isotype Control APC (Product # 17-4714-81) (blue histogram) or 1 µg of Anti-Mouse CD95 (APO-1/Fas) APC (purple histogram). Total viable cells were used for analysis.

[View more figures on thermofisher.com](#)

14 References

Flow Cytometry (14)

Frontiers in immunology

Transforming Growth Factor- and Interleukin-10 Synergistically Regulate Humoral Immunity *via* Modulating Metabolic Signals.

"17-0951 was used in Flow cytometry/Cell sorting to study the requirement of a combination of TGF- and IL-10 to suppress B cell activation induced by toll-like receptor stimulation."

Authors: Komai T, Inoue M, Okamura T, Morita K, Iwasaki Y, Sumitomo S, Shoda H, Yamamoto K, Fujio K

Species
Mouse

Dilution
Not Cited

Year
2019

Nature communications

T cells control humoral immune response by inducing T follicular helper cell differentiation.

"17-0951 was used in Flow cytometry/Cell sorting to demonstrate that complete Freund's adjuvant immunisation induces a subpopulation of CXCR5-expressing T cells in the draining lymph nodes."

Authors: Rezende RM, Lanser AJ, Rubino S, Kuhn C, Skillin N, Moreira TG, Liu S, Gabriely G, David BA, Menezes GB, Weiner HL

Species
Mouse

Dilution
Not Cited

Year
2018

[View more Flow references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.