

CD49b (Integrin alpha 2) Monoclonal Antibody (DX5), PE-Cyanine7, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Mouse
Host/Isotype	Rat / IgM, kappa
Class	Monoclonal
Type	Antibody
Clone	DX5
Conjugate	PE-Cyanine7
Excitation/Emission Max	569/780 nm
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_469667

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.5 µg/test	21 Publications
Functional Assay (FN)	-	1 Publication
Miscellaneous PubMed (Misc)	-	1 Publication

Product Specific Information

Description: The DX5 monoclonal antibody reacts with CD49b, an antigen expressed on a majority of mouse natural killer cells and a subset of T cells. DX5 reacts with all strains of mouse tested including the most commonly used strains, BALB/c, C57BL/6, C3H, CBA, DBA, AKR, SJL and 129. Simultaneous staining of C57BL/6 spleen cells with anti-NK1.1 mAb (PK136) and DX5 reveals coexpression of both markers by a majority of cells as well as presence of small populations of DX5+PK136- and DX5-PK136+ cells.

Applications Reported: This DX5 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This DX5 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Light sensitivity: This tandem dye is sensitive photo-induced oxidation. Please protect this vial and stained samples from light.


Fixation: Samples can be stored in IC Fixation Buffer (cat. 00-8222) (100 µL cell sample + 100 µL IC Fixation Buffer) or 1-step Fix/Lyse Solution (cat. 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency/compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific

performance should be determined empirically.

Excitation: 488-561 nm; Emission: 775 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD49b (Integrin alpha 2) Monoclonal Antibody (DX5), PE-Cyanine7, eBioscience™



CD49b (Integrin alpha 2) Antibody (25-5971-82) in Flow
Staining of C57BL/6 splenocytes with Anti-Mouse NK1-1 FITC (Product # 11-5941-82) and staining buffer (autofluorescence) (left) or 0.25 µg of Anti-Mouse CD49b (Integrin alpha 2) PE-Cyanine7 (right). Total viable cells were used for analysis.

[View more figures on thermofisher.com](https://thermofisher.com)

Flow Cytometry (21)

Journal for immunotherapy of cancer

Ultrasound combined with nanobubbles promotes systemic anticancer immunity and augments anti-PD1 efficacy.

"25-5971-82 was used in Flow Cytometry to provide a promising strategy for sensitizing poorly immunogenic solid tumors to immunotherapy in the clinic."

Authors: Hu J,He J,Wang Y,Zhao Y,Fang K,Dong Y,Chen Y,Zhang Y,Zhang C,Wang H,Tan J,Wang J,Zi R,Liu C,Liang H,Guo Y,Ou J

Year
2022

Species
Mouse

iScience

Immunogenicity and protective efficacy of an intranasal live-attenuated vaccine against SARS-CoV-2.

"25-5971-82 was used in Flow Cytometry to evaluate a Newcastle disease virus (NDV)-based vectored-vaccine in mice and hamsters for its immunogenicity, safety and protective efficacy against SARS-CoV-2."

Authors: Park JG,Oladunni FS,Rohaim MA,Whittingham-Dowd J,Tollitt J,Hodges MDJ,Fathallah N,Assas MB,Alhazmi W,Almilaibary A,Iqbal M,Chang P,Escalona R,Shivanna V,Torrelles JB,Worthington JJ,Jackson-Jones LH,Martinez-Sobrido L,Munir M

Year
2021

Species
Mouse

[View more Flow references on thermofisher.com](#)

Functional Assay (1)

Journal of leukocyte biology

Phenotypic differences between Th1 and Th17 cells and negative regulation of Th1 cell differentiation by IL-17.

"25-5971 was used in Functional assays to compare the cell surface marker expression profiles of Th1 and Th17 cells."

Authors: Nakae S,Iwakura Y,Suto H,Galli SJ

Year
2007

Species
Mouse

Miscellaneous PubMed (1)

Journal of immunology (Baltimore, Md. : 1950)

Chronic helminth infection promotes immune regulation in vivo through dominance of CD11cloCD103- dendritic cells.

"25-5971 was used in Magnetic cell separation to identify that the preferential expansion of a novel population of CD11c (lo) non-plasmacytoid DCs is associated with the pro-regulatory environment of chronic intestinal helminth infection."

Authors: Smith KA,Hochweller K,Hämmerling GJ,Boon L,MacDonald AS,Maizels RM

Year
2011

Species
Mouse

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.