

IL-17A Monoclonal Antibody (eBio17B7), PE-Cyanine7, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse, Rat
Published Species	Rat, Mouse
Host/Isotope	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), PE-Cyanine7, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	eBio17B7
Conjugate	PE-Cyanine7
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.1% gelatin
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_10732356

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.5 µg/test	55 Publications
Functional Assay (FN)	-	1 Publication
Immunohistochemistry (Paraffin) (IHC (P))	-	1 Publication
Miscellaneous PubMed (Misc)	-	1 Publication

Product Specific Information

Description: The eBio17B7 antibody reacts with mouse and rat IL-17A with no recognition of IL-17F. Interleukin-17A (IL-17A) is a CD4+ T cell-derived cytokine that promotes inflammatory responses in cell lines and is elevated in rheumatoid arthritis, asthma, multiple sclerosis, psoriasis, and transplant rejection. The cDNA encoding human IL-17A was isolated from a library of CD4+ T cells; the encoded protein exhibits 72 percent amino acid identity with HVS13, an open reading frame from a T lymphotropic Herpesvirus saimiri, and 63 percent with mouse CTLA-8 (cytotoxic T-lymphocyte associated antigen-8). Human IL-17A exists as glycosylated 20-30 kD homodimers. High levels of IL-17A homodimer are produced by activated peripheral blood CD4+ T-cells. IL-17A enhances expression of the intracellular adhesion molecule-1 (ICAM-1) in human fibroblasts. Human IL-17A also stimulates epithelial, endothelial, or fibroblastic cells to secrete IL-6, IL-8, G-CSF, and PGE2. In the presence of human IL-17A, fibroblasts can sustain the proliferation of CD34+ hematopoietic progenitors and induce maturation into neutrophils. Mouse, rat, and human IL-17A can induce IL-6 secretion in mouse stromal cells, indicating that all homologs can recognize the mouse IL-17A receptor.

IL-23-dependent, IL-17A-producing CD4+ T cells (Th-17 cells) have been identified as a unique subset of Th cells that develops along a pathway that is distinct from the Th1- and Th2- cell differentiation pathways. The hallmark effector molecules of Th1 and

Th2 cells, e.g., IFN gamma and IL-4, have each been found to negatively regulate the generation of these Th-17 cells.

Applications Reported: This eBio17B7 antibody has been reported for use intracellular staining followed by flow cytometric analysis.

Applications Tested: This eBio17B7 antibody has been tested by intracellular staining and flow cytometric analysis of restimulated, Th17-polarized mouse splenocytes using the Intracellular Fixation and Permeabilization Buffer Set (cat. 88-8824) and protocol. This can be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Staining has been successfully done using the Foxp3 buffer system (cat 00-5523)


Light sensitivity: This tandem dye is sensitive to photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (cat. 00-8222) (100 µL of cell sample + 100 µL of IC Fixation Buffer) or 1-step Fix/Lyse Solution (cat. 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency /compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 488-561 nm; Emission: 775 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For IL-17A Monoclonal Antibody (eBio17B7), PE-Cyanine7, eBioscience™



IL-17A Antibody (25-7177-82) in Flow

Intracellular staining of 10-day Th17-polarized mouse splenocytes either unstimulated (left) or stimulated with Cell Stimulation Cocktail (plus protein transport inhibitors) (500X) (Product # 00-4975-03) (right) with Anti-Mouse CD4 FITC (Product # 11-0042-82) and 0.25 µg of Anti-Mouse/Rat IL-17A PE-Cyanine7 using the Intracellular Fixation and Permeabilization Buffer Set (Product # 88-8824-00) and protocol.

[View more figures on thermofisher.com](https://www.thermofisher.com)

Flow Cytometry (55)

Evidence-based complementary and alternative medicine : eCAM

Baicalin Downregulates RLRs Signaling Pathway to Control Influenza A Virus Infection and Improve the Prognosis.

"Published figure using IL-17A monoclonal antibody (Product # 25-7177-82) in Flow Cytometry"

Authors: Pang P,Zheng K,Wu S,Xu H,Deng L,Shi Y,Chen X

Species
Mouse
Not Applicable

Dilution
Not Cited
Not Cited

Year
2020

Frontiers in pharmacology

Traditional Herbal Medicine-Derived Sulforaphene LFS-01 Reverses Colitis in Mice by Selectively Altering the Gut Microbiota and Promoting Intestinal Gamma-Delta T Cells.

"Published figure using IL-17A monoclonal antibody (Product # 25-7177-82) in Flow Cytometry"

Authors: Li M,Gao J,Tang Y,Liu M,Wu S,Qu K,Long X,Li H,Liu M,Liu Y,Yuan J,Mao L,Liu Y,Zheng X,Wang E,Wang J, Yang Y

Species
Not Applicable

Dilution
Not Cited

Year
2020

[View more Flow references on thermofisher.com](#)

Immunohistochemistry (Paraffin) (1)

BMC immunology

Role of epithelial integrin-linked kinase in promoting intestinal inflammation: effects on CCL2, fibronectin and the T cell repertoire.

Authors: Assi K,Patterson S,Dedhar S,Owen D,Levings M,Salh B

Species
Not Applicable

Dilution
Not Cited

Year
2011

Functional Assay (1)

International immunopharmacology

Anti-IL-23 antibody blockade of IL-23/IL-17 pathway attenuates airway obliteration in rat orthotopic tracheal transplantation.

Authors: Cao H,Lan Q,Shi Q,Zhou X,Liu G,Liu J,Tang G,Qiu C,Qiu C,Xu J,Fan H,Liu Z

Species
Not Applicable

Dilution
Not Cited

Year
2011

More applications with references on thermofisher.com

Misc (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.