

PTEN Monoclonal Antibody (2F4C9)

Product Details

Size	100 µg
Species Reactivity	Human, Mouse
Published Species	Human
Host/Isotype	Mouse / IgG2a
Class	Monoclonal
Type	Antibody
Clone	2F4C9
Conjugate	Unconjugated
Immunogen	Recombinant protein derived from the PTEN protein.
Form	Liquid
Concentration	0.5 mg/mL
Purification	Protein A
Storage buffer	PBS, pH 7.4
Contains	0.1% sodium azide
Storage conditions	-20°C
RRID	AB_2533087

Applications	Tested Dilution	Publications
Western Blot (WB)	1-3 µg/mL	1 Publication
Immunohistochemistry (IHC)	-	3 Publications
Immunocytochemistry (ICC/IF)	0.5 µg/mL	1 Publication
ELISA (ELISA)	0.1-1 µg/mL	-

Product Specific Information

32-5800 reacts specifically with the human PTEN protein. Reactivity was confirmed with cell lines which contain endogenous PTEN (NIH3T3, K652, and DU145 prostate cancer line) as well as transfected cell lines (Rat1 and 293T cells). This antibody detects the ~55 kDa PTEN protein and was successfully used in western blotting analysis of PTEN in breast cancer cell lines. No cross-reactivity to any other proteins has been detected.

Product Images For PTEN Monoclonal Antibody (2F4C9)

PTEN Antibody (32-5800)

Antibody specificity was demonstrated by CRISPR-Cas9 mediated knockout of target protein. A loss of signal was observed for target protein in PTEN KO cell line compared to control cell line using Anti-PTEN Monoclonal Antibody (2F4C9) (Product # 32-5800). {KO}

PTEN Antibody (32-5800) in WB

Western blot analysis of PTEN was performed by loading 20 µg of A431 (lane1), HeLa (lane2), NIH/3T3 (lane3) and HEK-293 (lane4) cell lysate using Novex® NuPAGE® 10 % Bis-Tris gel (Product # NP0301BOX), XCell SureLock Electrophoresis System (Product # EI0002), Novex® Sharp Pre-Stained Protein Standard (LC5800), and iBlot® Dry Blotting System (IB21001). Proteins were transferred to a nitrocellulose membrane and blocked with 5 % skim milk for 1 hour at room temperature. PTEN was detected at ~55 kDa using PTEN Mouse monoclonal Antibody (Product # 32-5800) at 1-3 µg/mL in 2.5 % skim milk at 4°C overnight on a rocking platform. Goat Anti-Mouse IgG - HRP Secondary Antibody (Product # 62-6520) at 1:4000 dilution was used and chemiluminescent detection was performed using Pierce™ ECL Western Blotting Substrate (Product # 32106).

PTEN Antibody (32-5800) in ICC/IF

Immunofluorescent analysis of PTEN was done on 70% confluent log phase HeLa cells. The cells were fixed with 4% paraformaldehyde for 15 minutes, permeabilized with 0.25% Triton™ X-100 for 10 minutes, and blocked with 5% BSA for 1 hour at room temperature. The cells were labeled with PTEN Mouse Monoclonal Antibody (Product # 32-5800) at 0.5 µg/mL in 1% BSA and incubated for 3 hours at room temperature and then labeled with Alexa Fluor 488 Rabbit Anti-Mouse IgG Secondary Antibody (Product # A-11059) at a dilution of 1:400 for 30 minutes at room temperature (Panel a: green). Nuclei (Panel b: blue) were stained with SlowFade Gold Antifade Mountant with DAPI (Product # S36938). F-actin (Panel c: red) was stained with Alexa Fluor 594 Phalloidin (Product # A12381). Panel d is a merged image showing nuclear localization and panel e is a no primary antibody control. The images were captured at 20X magnification.

View more figures on thermofisher.com

Western Blot (1)

<p>Oncotarget</p> <p>The ISG15-specific protease USP18 regulates stability of PTEN.</p> <p>"Published figure using PTEN monoclonal antibody (Product # 32-5800) in Western Blot"</p> <p>Authors: Mustachio LM,Kawakami M,Lu Y,Rodriguez-Canales J,Mino B,Behrens C,Wistuba I,Bota-Rabassedas N,Yu J, Lee JJ,Roszik J,Zheng L,Liu X,Freemantle SJ,Dmitrovsky E</p>	<p>Year 2017</p> <p>Species Human</p> <p>Dilution 1:10</p>
---	---

Immunohistochemistry (3)

<p>Oncotarget</p> <p>The ISG15-specific protease USP18 regulates stability of PTEN.</p> <p>"Published figure using PTEN monoclonal antibody (Product # 32-5800) in Western Blot"</p> <p>Authors: Mustachio LM,Kawakami M,Lu Y,Rodriguez-Canales J,Mino B,Behrens C,Wistuba I,Bota-Rabassedas N,Yu J, Lee JJ,Roszik J,Zheng L,Liu X,Freemantle SJ,Dmitrovsky E</p>	<p>Year 2017</p> <p>Species Human</p> <p>Dilution 1:10</p>
---	---

<p>Hepatology research : the official journal of the Japan Society of Hepatology</p> <p>Epigenetic and genetic alterations of PTEN in hepatocellular carcinoma.</p> <p>Authors: Wang L,Wang WL,Zhang Y,Guo SP,Zhang J,Li QL</p>	<p>Year 2007</p> <p>Species Human</p>
---	---

[View more IHC references on thermofisher.com](#)

Immunocytochemistry (1)

<p>Oncotarget</p> <p>The ISG15-specific protease USP18 regulates stability of PTEN.</p> <p>"Published figure using PTEN monoclonal antibody (Product # 32-5800) in Western Blot"</p> <p>Authors: Mustachio LM,Kawakami M,Lu Y,Rodriguez-Canales J,Mino B,Behrens C,Wistuba I,Bota-Rabassedas N,Yu J, Lee JJ,Roszik J,Zheng L,Liu X,Freemantle SJ,Dmitrovsky E</p>	<p>Year 2017</p> <p>Species Human</p> <p>Dilution 1:10</p>
---	---

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.