

STAT4 Monoclonal Antibody (ST4-5D6)


Product Details	
Size	100 µg
Species Reactivity	Human, Mouse, Rat
Published Species	Rat, Virus, Human, Mouse
Host/Isotype	Mouse / IgG2a, kappa
Class	Monoclonal
Type	Antibody
Clone	ST4-5D6
Conjugate	Unconjugated
Immunogen	A synthetic peptide derived form the C terminus of murine STAT4.
Form	Liquid
Concentration	0.5 mg/mL
Purification	Protein A
Storage buffer	PBS, pH 7.4
Contains	0.1% sodium azide
Storage conditions	-20°C
RRID	AB_2533108

Applications	Tested Dilution	Publications
Western Blot (WB)	0.5-3 µg/mL	2 Publications
Immunocytochemistry (ICC/IF)	1:100	-
ELISA (ELISA)	0.1-1.0 µg/mL	-
Immunoprecipitation (IP)	5 µg	-
Gel Shift (GS)	1-5 µg/mL	-

Product Images For STAT4 Monoclonal Antibody (ST4-5D6)


STAT4 Antibody (33-2300)

Antibody specificity was demonstrated by detection of differential basal expression of the target across cell lines and tissues owing to their inherent genetic constitution. Relative expression of Signal transducer and activator of transcription 4 was observed in Mouse testis as positive model versus in Mouse skeletal muscle, stomach and liver as negative models using Anti-STAT4 Monoclonal Antibody (ST4-5D6) (Product # 33-2300) in Western Blot. {RE}




STAT4 Antibody (33-2300) in WB

Western blot was performed using Anti-STAT4 Monoclonal Antibody (ST4-5D6) (Product # 33-2300) and a ~86 kDa band corresponding to Signal transducer and activator of transcription 4 was observed across cell lines and tissues tested. Whole cell extracts (50 µg lysate) of SH-SY5Y (Lane 1), A549 (Lane 2), HepG2 (Lane 3), HEK-293 (Lane 4), Mouse Testis (Lane 5), Mouse Stomach (Lane 6), Mouse Skeletal Muscle (Lane 7), Mouse Liver (Lane 8) were electrophoresed using NuPAGE™ 4-12% Bis-Tris Protein Gel (Product # NP0322BOX). Resolved proteins were then transferred onto a nitrocellulose membrane (Product # IB23001) by iBlot® 2 Dry Blotting System (Product # IB21001). The blot was probed with the primary antibody (0.5 µg/mL) and detected by chemiluminescence with Goat anti-Mouse IgG (H+L) Superclonal™ Recombinant Secondary Antibody, HRP (Product # A28177, 1:20000) using the iBright FL 1000 (Product # A32752). Chemiluminescent detection was performed using SuperSignal™ West Pico PLUS Chemiluminescent Substrate (Product # 34580). A 25 kDa band corresponding to IgG was observed in the mouse tissue lysates.



STAT4 Antibody (33-2300) in WB

Western blot analysis was performed on whole cell extracts (30 µg lysate) of Mouse testis (Lane 1), Rat testis (Lane 2), Mouse Stomach (Lane 3), Rat stomach (Lane 4). The blots were probed with Anti-STAT4 Mouse Monoclonal Antibody (Product # 33-2300, 1-3 µg/mL) and detected by chemiluminescence using Goat anti-Mouse IgG (H+L) Secondary Antibody, HRP conjugate (Product # 62-6520, 1:4000 dilution). A 86 kDa band corresponding to STAT4 was observed across tissue tested along with a 160 kDa extra band in Mouse Testis and Rat Testis. Known quantity of protein samples were electrophoresed using Novex® NuPAGE® 4-12 % Bis-Tris gel (Product # NP0321BOX), XCell SureLock™ Electrophoresis System (Product # EI0002) and Novex® Sharp Pre-Stained Protein Standard (Product # LC5800). Resolved proteins were then transferred onto a transferred onto a nitrocellulose membrane with Pierce™ Power Blotter System (22834). The membrane was probed with the relevant primary and secondary Antibody following blocking with 5 % skimmed milk. Chemiluminescent detection was performed using Pierce™ ECL Western Blotting Substrate (Product # 32106).



View more figures on thermofisher.com

Western Blot (2)

<p>The Journal of investigative dermatology</p> <p>Increased sensitivity to interferon-alpha in psoriatic T cells.</p> <p>Authors: Eriksen KW,Lovato P,Skov L,Krejsgaard T,Kaltoft K,Geisler C,Ødum N</p>	<p>Year</p> <p>2005</p> <p>Species</p> <p>Rat</p>
<p>Cancer research</p> <p>Activated signal transducer and activator of transcription (STAT) 3: localization in focal adhesions and function in ovarian cancer cell motility.</p> <p>Authors: Silver DL,Naora H,Liu J,Cheng W,Montell DJ</p>	<p>Year</p> <p>2004</p> <p>Species</p> <p>Human Virus Mouse</p> <p>Dilution</p> <p>1:250 1:250 1:250</p>

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.