

# SPARC Monoclonal Antibody (ON1-1)

Product Details	
Size	100 µg
Species Reactivity	Bovine, Human, Pig, Rabbit
Published Species	Dog, Rat, Human
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	ON1-1
Conjugate	Unconjugated
Immunogen	Full-length Bovine bone osteonectin (SPARC)
Form	Lyophilized
Concentration	2.0 mg/mL
Purification	Ion-exchange chromatography
Storage buffer	10mM PBS, pH 7.4, with 1% BSA
Contains	no preservative
Storage conditions	4° C
RRID	AB_2533126

Applications	Tested Dilution	Publications
Western Blot (WB)	5-10 µg/mL	3 Publications
Immunohistochemistry (IHC)	5-10 µg/mL	18 Publications
Immunohistochemistry (Paraffin) (IHC (P))	-	3 Publications
Immunocytochemistry (ICC/IF)	-	3 Publications
Flow Cytometry (Flow)	1 µg/mL	-
ELISA (ELISA)	Assay-dependent	2 Publications
Miscellaneous PubMed (Misc)	-	1 Publication

## Product Specific Information

**Source:** Monoclonal antibody was obtained by fusing the mouse myeloma cell-line P3-X63-Ag8-U1 with spleen cells of BALB/c mouse after immunization with bovine bone osteonectin (SPARC). The monoclonal antibody was harvested from ascitic fluid.

**Specificity:** This antibody reacts with both bone derived and platelet derived Osteonectin (ELISA). This antibody does not react with non-activated platelet and reacts with thrombin-stimulated platelet (flow cytometric analysis). This antibody reacts with human and bovine Osteonectin (Western blot analysis). This antibody cross reacts with rabbit and porcine Osteonectin. (ELISA)

**Storage:** 4°C. This product does not contain preservative. The stock solution (2.0 mg/mL) should be stored in aliquots at -20°C for 1 year, or should be stored at 4°C for 6 months after adding 0.1% sodium azide. Avoid repeated freeze-thaw cycles.

**Reconstitution:** Dissolve the lyophilized antibody in 50 µL of distilled water (final concentration: 2.0 mg/mL). This solution can be used as a stock solution. If dilution is necessary for your application, dilute the stock solution with the following Dilution solution just prior to use. When the entire amount of antibody is to be used over a short time period, it may be dissolved directly in 500 µL or more of the Dilution solution. Be sure to store the antibody at a minimum concentration of 2.0 mg/mL. A

lower antibody concentration may result in decreased stability. Reconstituted antibody solution should contain 0.1% sodium azide as a preservative when stored at 4°C.

## 30 References

### Western Blot (3)

Asian journal of andrology

#### Secreted protein acidic and rich in cysteine (SPARC) induces epithelial-mesenchymal transition, enhancing migration and invasion, and is associated with high Gleason score in prostate cancer.

"33-5500 was used in Immunohistochemistry to show that secreted protein acidic and rich in cysteine (SPARC) is highly expressed in PCa tissues with a higher Gleason score."

Authors: López-Moncada F,Torres MJ,Castellón EA,Contreras HR

Year  
2020

Species  
Human

BMC cancer

#### Diagnostic role of circulating extracellular matrix-related proteins in non-small cell lung cancer.

"Published figure using SPARC monoclonal antibody (Product # 33-5500) in Western Blot"

Authors: Andriani F,Landoni E,Mensah M,Facchinetti F,Miceli R,Tagliabue E,Giussani M,Callari M,De Cecco L,Colombo MP,Roz L,Pastorino U,Sozzi G

Year  
2018

Species  
Human

[View more WB references on thermofisher.com](#)

### Immunohistochemistry (18)

Cancers

#### Expression of Extracellular Matrix-Related Genes and Their Regulatory microRNAs in Problematic Colorectal Polyps.

"33-5500 was used in Immunohistochemistry to analyse the expression of selected extracellular matrix (ECM)-related genes and proteins, and their regulatory microRNAs using RT-qPCR and immunohistochemistry in biopsies from 44 patients."

Authors: Žlajpah M,Boštjani E,Tepeš B,Zidar N

Year  
2020

Species  
Human

Dilution  
1:400

Asian journal of andrology

#### Secreted protein acidic and rich in cysteine (SPARC) induces epithelial-mesenchymal transition, enhancing migration and invasion, and is associated with high Gleason score in prostate cancer.

"33-5500 was used in Immunohistochemistry to show that secreted protein acidic and rich in cysteine (SPARC) is highly expressed in PCa tissues with a higher Gleason score."

Authors: López-Moncada F,Torres MJ,Castellón EA,Contreras HR

Year  
2020

Species  
Human

[View more IHC references on thermofisher.com](#)

### More applications with references on thermofisher.com

IHC (P) (3)

ICC/IF (3)

ELISA (2)

Misc (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.