

CD3e Monoclonal Antibody (145-2C11), PE-Cyanine5.5, eBioscience™

Product Details	
Size	100 µg
Species	Mouse
Published Species	Artificial Control, Mouse, Human
Expression System	Armenian hamster / IgG
Recommended Isotype Control	Armenian Hamster IgG Isotype Control (eBio299Arm), PE-Cyanine5.5, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	145-2C11
Conjugate	PE-Cyanine5.5
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_11219266

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.25 µg/test	90 Publications
Functional Assay (FN)	-	1 Publication
Immunohistochemistry (Frozen) (IHC (F))	-	2 Publications

Product Specific Information

Description: The 145-2C11 monoclonal antibody reacts with mouse CD3e, a 20 kDa subunit of the TCR complex. Along with the other CD3 subunits, gamma and delta, the epsilon chain is required for proper assembly, trafficking and surface expression of the TCR complex. CD3 is expressed by thymocytes in a developmentally regulated manner and by all mature T cells. Binding of 145-2C11 to TCR initiates the intracellular biochemical pathway resulting in cellular activation, proliferation, and apoptosis depending on specific conditions utilized. 145-2C11 is commonly used as a phenotypic marker for mouse T cells.

Applications Reported: This 145-2C11 antibody has been reported for use in flow cytometric analysis.


Applications Tested: This 145-2C11 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.25 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Light sensitivity: This tandem dye is sensitive photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (cat. 00-8222) (100 μ L cell sample + 100 μ L IC Fixation Buffer) or 1-step Fix/Lyse Solution (cat. 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency/compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 488-561 nm; Emission: 695 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser

Product Images For CD3e Monoclonal Antibody (145-2C11), PE-Cyanine5.5, eBioscience™



CD3e Antibody (35-0031-82) in Flow

Staining of BALB/c splenocytes with Anti-Human/Mouse CD45R (B220) FITC (Product # 11-0452-82) and 0.125 μ g of Armenian Hamster IgG Isotype Control PE-Cyanine5-5 (Product # 35-4888-80) (left) or 0.125 μ g of Anti-Mouse CD3e PE-Cyanine5-5 (right). Cells in the lymphocyte gate were used for analysis.

[View more figures on thermofisher.com](http://thermofisher.com)

Flow Cytometry (90)

Frontiers in immunology

Tp12 Protects Against Fulminant Hepatitis Through Mobilization of Myeloid-Derived Suppressor Cells.

"Published figure using CD3e monoclonal antibody (Product # 35-0031-82) in Flow Cytometry"

Authors: Xu J,Pei S,Wang Y,Liu J,Qian Y,Huang M,Zhang Y,Xiao Y

Species
Not Applicable

Dilution
Not Cited

Year
2020

Clinical and translational allergy

The efficacy of oral and subcutaneous antigen-specific immunotherapy in murine cow's milk- and peanut allergy models.

"35-0031 was used in Flow cytometry/Cell sorting to compare oral immunotherapy and subcutaneous immunotherapy models for cows milk and peanut allergy."

Authors: Vonk MM,Wagenaar L,Pieters RHH,Knippels LMJ,Willemsen LEM,Smit JJ,van Esch BCAM,Garssen J

Species
Mouse

Dilution
1:100

Year
2020

[View more Flow references on thermofisher.com](#)

Immunohistochemistry (Frozen) (2)

International journal of cancer

HSP70 vaccine in combination with gene therapy with plasmid DNA encoding sPD-1 overcomes immune resistance and suppresses the progression of pulmonary metastatic melanoma.

Authors: Geng H,Zhang GM,Xiao H,Yuan Y,Li D,Zhang H,Qiu H,He YF,Feng ZH

Species
Not Applicable

Dilution
Not Cited

Year
2006

Investigative ophthalmology and visual science

CCR5-deficient mice develop experimental autoimmune uveoretinitis in the context of a deviant effector response.

Authors: Takeuchi A,Usui Y,Takeuchi M,Hattori T,Kezuka T,Suzuki J,Okunuki Y,Iwasaki T,Haino M,Matsushima K,Usui M

Species
Not Applicable

Dilution
Not Cited

Year
2005

More applications with references on thermofisher.com

FN (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.