

CD323 (JAM3) Monoclonal Antibody (SHM33), eFluor™ 570, eBioscience™

Product Details

Size	25 µg
Species Reactivity	Human
Host/Isotype	Mouse / IgG2a, kappa
Class	Monoclonal
Type	Antibody
Clone	SHM33
Conjugate	eFluor™ 570
Excitation/Emission Max	556/569 nm
Form	Liquid
Concentration	0.2 mg/mL
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2573603

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	Assay-Dependent	-
Immunocytochemistry (ICC/IF)	1 µg/mL	-

Product Specific Information

Description: The SHM33 monoclonal antibody reacts with human CD323, which is also known as Junctional Adhesion Molecule (JAM) 3. A member of the Ig superfamily of transmembrane proteins, CD323 is expressed on endothelial and epithelial cells, smooth muscle cells, peripheral nerves, platelets, and some B cells. In addition, this receptor is expressed on VEGF and histamine-stimulated endothelial cells, as well as on activated T cells. CD323 is involved in neutrophil transmigration during inflammation, angiogenesis, cell polarity, and nerve conduction. CD323 interacts homo- and heterotypically with beta2 and beta3 integrins, JAM2, and the viral receptor CAR.


Applications Reported: This SHM33 antibody has been reported for use in microscopy, immunohistochemical staining, and immunocytochemistry.

Applications Tested: This SHM33 antibody has been tested by immunocytochemistry of methanol-fixed human cells and can be used at less than or equal to 1 µg/mL. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Filter Recommendation: When using this eFluor® 570 antibody conjugate, we recommend a filter that will capture the 570 emission wavelength (for example, Excitation 545/25, 565LP, Emission 605/70). A standard Alexa Fluor® 555 or TRITC filter is acceptable.

Excitation: 555 nm; Emission: 570 nm

Product Images For CD323 (JAM3) Monoclonal Antibody (SHM33), eFluor™ 570, eBioscience™



CD323 (JAM3) Antibody (41-3239-80) in ICC/IF

Immunocytochemistry of methanol-fixed HEK293 cells stained with 1 µg/mL of Mouse IgG2a K Isotype Control eFluor® 570 (left) or 1 µg/mL of Anti-Human CD323 (JAM3) eFluor® 570 (right). Nuclei are stained with DAPI.

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.