

SMAD2 Monoclonal Antibody (42)


Product Details	
Size	100 µg
Species Reactivity	Bovine, Human, Mouse, Rhesus monkey, Rat
Published Species	Rat, Human
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	42
Conjugate	Unconjugated
Immunogen	Recombinant protein derived from the N-terminal region of human Smad2 protein.
Form	Liquid
Concentration	0.5 mg/mL
Purification	Protein A
Storage buffer	PBS, pH 7.4
Contains	0.1% sodium azide
Storage conditions	-20°C
RRID	AB_2532216

Applications	Tested Dilution	Publications
Western Blot (WB)	1 µg/mL	4 Publications
Immunohistochemistry (Paraffin) (IHC (P))	1:20	-
Flow Cytometry (Flow)	Assay-dependent	-

Product Images For SMAD2 Monoclonal Antibody (42)


SMAD2 Antibody (436500)

Antibody specificity was demonstrated by siRNA mediated knockdown of target protein. MCF-7 cells were transfected with SMAD2 siRNA and decrease in signal was observed in Western Blot using Anti-SMAD2 Monoclonal Antibody (42) (Product # 436500). {KD}




SMAD2 Antibody (436500) in IHC (P)

Immunohistochemistry analysis of SMAD2 showing staining in the cytoplasm and nucleus of paraffin-embedded human placenta tissue (right) compared to a negative control without primary antibody (left). To expose target proteins, antigen retrieval was performed using 10mM sodium citrate (pH 6.0), microwaved for 8-15 min. Following antigen retrieval, tissues were blocked in 3% H2O2-methanol for 15 min at room temperature, washed with ddH2O and PBS, and then probed with a Anti- SMAD2 Monoclonal Antibody (Product # 436500) diluted in 3% BSA-PBS at a dilution of 1:20 overnight at 4°C in a humidified chamber. Tissues were washed extensively in PBST and detection was performed using an HRP-conjugated secondary antibody followed by colorimetric detection using a DAB kit. Tissues were counterstained with hematoxylin and dehydrated with ethanol and xylene to prep for mounting.



SMAD2 Antibody (436500) in IHC (P)

Immunohistochemistry analysis of SMAD2 showing staining in the cytoplasm and nucleus of paraffin-embedded human brain tissue (right) compared to a negative control without primary antibody (left). To expose target proteins, antigen retrieval was performed using 10mM sodium citrate (pH 6.0), microwaved for 8-15 min. Following antigen retrieval, tissues were blocked in 3% H2O2-methanol for 15 min at room temperature, washed with ddH2O and PBS, and then probed with a Anti- SMAD2 Monoclonal Antibody (Product # 436500) diluted in 3% BSA-PBS at a dilution of 1:20 overnight at 4°C in a humidified chamber. Tissues were washed extensively in PBST and detection was performed using an HRP-conjugated secondary antibody followed by colorimetric detection using a DAB kit. Tissues were counterstained with hematoxylin and dehydrated with ethanol and xylene to prep for mounting.



View more figures on thermofisher.com

Western Blot (4)

<p>Pharmaceuticals (Basel, Switzerland)</p> <p>Fucoidan-Mediated Inhibition of Fibrotic Properties in Oral Submucous Fibrosis via the MEG3/miR-181a/Egr1 Axis.</p> <p>"436500 was used in Western Blotting to investigate the anti-fibrotic effect of fucoidan on oral fibrosis."</p> <p>Authors: Fang CY,Chen SH,Huang CC,Liao YW,Chao SC,Yu CC</p>	<p>Year 2022</p> <p>Species Human</p>
<p>Oxidative medicine and cellular longevity</p> <p>BGP-15 Protects against Heart Failure by Enhanced Mitochondrial Biogenesis and Decreased Fibrotic Remodelling in Spontaneously Hypertensive Rats.</p> <p>"436500 was used in Western Blotting to investigate the effects of BGP-15, an insulin-sensitizing molecule, in a chronic hypertension-induced heart failure model, revealing that BGP-15 preserved cardiac function, reduced collagen deposition and cardiomyocyte hypertrophy, enhanced prosurvival signaling pathways, and increased mitochondrial biogenesis."</p> <p>Authors: Horvath O,Ordog K,Bruszt K,Deres L,Gallyas F,Sumegi B,Toth K,Halmosi R</p>	<p>Year 2021</p> <p>Species Rat</p> <p>Dilution 1:1,000</p>

[View more WB references on thermofisher.com](#)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.