

PDGF-D Polyclonal Antibody


Product Details	
Size	100 µg
Species Reactivity	Human, Mouse, Rat
Published Species	Rat, Mouse, Human
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	Synthetic peptide derived from the C-terminal region of the human PDGF-D
Form	Liquid
Concentration	0.25 mg/mL
Purification	Antigen affinity chromatography
Storage buffer	PBS, pH 7.4
Contains	0.1% sodium azide
Storage conditions	-20°C
RRID	AB_2533455

Applications	Tested Dilution	Publications
Western Blot (WB)	Assay-dependent	3 Publications
Immunohistochemistry (IHC)	-	5 Publications
Immunohistochemistry (Paraffin) (IHC (P))	1:50	1 Publication

Product Images For PDGF-D Polyclonal Antibody


PDGF-D Antibody (40-2100) in WB

Western blot analysis was performed on whole cell extracts (30 µg lysate) of Mouse Brain (Lane 1), A549 (Lane 2), SH-SY5Y (Lane 3) and THP-1 (Lane 4). The blots were probed with Anti-PDGFD Rabbit Polyclonal Antibody (Product # 40-2100, 1-3 µg/mL) and detected by chemiluminescence Goat Anti-Rabbit IgG Secondary Antibody, HRP conjugate (Product # G-21234, 1:5000 dilution). A 42 kDa band corresponding to PDGFD was observed across cell lines and tissues tested. An extra band at ~ 35 kDa was observed in cell lines alone. Known quantity of protein samples were electrophoresed using Novex® NuPAGE®12 % Bis-Tris gel (Product # NP0342BOX), XCell SureLock™ Electrophoresis System (Product # EI0002) and Novex® Sharp Pre-Stained Protein Standard (Product # LC5800). Resolved proteins were then transferred onto a nitrocellulose membrane by iBlot® 2 Dry Blotting System (Product # IB21001). The membrane was probed with the relevant primary and secondary Antibody following blocking with 5 % skimmed milk. Chemiluminescent detection was performed using Pierce™ ECL Western Blotting Substrate (Product # 32106).




PDGF-D Antibody (40-2100) in WB

Western Blot analysis of (A) NTERA-2 cell lysates, (B) mouse testis homogenates, (C) SK-OV-3 cell lysates, and (D) fetal mouse brain homogenates using Zymed Rb anti-PDGF-D (Product # 40-2100).



PDGF-D Antibody (40-2100) in WB

Western blot analysis of (A) U251 and (B) A172 cell lysates, and (C) rat ovary homogenates using Rb anti-PDGF-D (Product # 40-2100).



View more figures on thermofisher.com

Western Blot (3)

<p>The Journal of experimental medicine</p> <p>PDGF-D activation by macrophage-derived uPA promotes AngII-induced cardiac remodeling in obese mice.</p> <p>"40-2100 was used in Immunohistochemistry to provide for the first time a new interaction pattern between macrophage and adipocyte: that macrophage-derived uPA activates adipocyte-secreted PDGF-D, which finally accelerates AngII-induced cardiac remodeling in obese mice."</p> <p>Authors: Cheng YW,Zhang ZB,Lan BD,Lin JR,Chen XH,Kong LR,Xu L,Ruan CC,Gao PJ</p>	<p>Year 2021</p> <p>Species Mouse</p>
<p>The Journal of clinical investigation</p> <p>Cytomegalovirus promotes murine glioblastoma growth via pericyte recruitment and angiogenesis.</p> <p>"Published figure using PDGF-D polyclonal antibody (Product # 40-2100) in Immunohistochemistry"</p> <p>Authors: Krenzlin H,Behera P,Lorenz V,Passaro C,Zdioruk M,Nowicki MO,Grauwet K,Zhang H,Skubal M,Ito H,Zane R,Gutknecht M,Griessl MB,Ricklefs F,Ding L,Peled S,Rooj A,James CD,Cobbs CS,Cook CH,Chiocca EA,Lawler SE</p>	<p>Year 2019</p>

[View more WB references on thermofisher.com](#)

Immunohistochemistry (5)

<p>Journal of neuroinflammation</p> <p>SU16f inhibits fibrotic scar formation and facilitates axon regeneration and locomotor function recovery after spinal cord injury by blocking the PDGFR pathway.</p> <p>"Published figure using PDGF-D polyclonal antibody (Product # 40-2100) in Immunohistochemistry"</p> <p>Authors: Li Z,Yu S,Liu Y,Hu X,Li Y,Xiao Z,Chen Y,Tian D,Xu X,Cheng L,Zheng M,Jing J</p>	<p>Year 2022</p>
<p>The Journal of experimental medicine</p> <p>PDGF-D activation by macrophage-derived uPA promotes AngII-induced cardiac remodeling in obese mice.</p> <p>"40-2100 was used in Immunohistochemistry to provide for the first time a new interaction pattern between macrophage and adipocyte: that macrophage-derived uPA activates adipocyte-secreted PDGF-D, which finally accelerates AngII-induced cardiac remodeling in obese mice."</p> <p>Authors: Cheng YW,Zhang ZB,Lan BD,Lin JR,Chen XH,Kong LR,Xu L,Ruan CC,Gao PJ</p>	<p>Year 2021</p> <p>Species Mouse</p>

[View more IHC references on thermofisher.com](#)

More applications with references on thermofisher.com

IHC (P) (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.