

CD49b (Integrin alpha 2) Monoclonal Antibody (DX5), APC-eFluor 780, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Mouse
Host/Isotope	Rat / IgM, kappa
Class	Monoclonal
Type	Antibody
Clone	DX5
Conjugate	APC-eFluor® 780
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_11218895

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.25 µg/test	3 Publications

Product Specific Information

Description: The DX5 monoclonal antibody reacts with CD49b, an antigen expressed on a majority of mouse natural killer cells and a subset of T cells. DX5 reacts with all strains of mouse tested including the most commonly used strains, BALB/c, C57BL/6, C3H, CBA, DBA, AKR, SJL and 129. Simultaneous staining of C57BL/6 spleen cells with anti-NK1.1 mAb (PK136) and DX5 reveals coexpression of both markers by a majority of cells as well as presence of small populations of DX5+PK136- and DX5-PK136+ cells.

Applications Reported: This DX5 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This DX5 antibody has been tested by flow cytometric analysis of C57BL/6 mouse spleen cells. This can be used at less than or equal to 0.25 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

APC-eFluor 780 emits at 780 nm and is excited with the Red laser (633 nm). Please make sure that your instrument is capable of detecting this fluorochoime.

Light sensitivity: This tandem is sensitive to photo-induced oxidation. Please protect this vial and stained samples from light.


Fixation: Samples can be stored in IC Fixation Buffer (cat. 00-8222) (100 µL cell sample + 100 µL IC Fixation Buffer) or 1-step Fix /Lyse Solution (cat. 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency

/compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 633-647 nm; Emission: 780 nm; Laser: Red Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD49b (Integrin alpha 2) Monoclonal Antibody (DX5), APC-eFluor 780, eBioscience™



CD49b (Integrin alpha 2) Antibody (47-5971-82) in Flow

Staining of C57Bl/6 splenocytes with Anti-Mouse NK1-1 PE-Cy7 (Product # 25-5941-82) and 0.125 µg of Anti-Mouse CD49b (Integrin alpha 2) APC-eFluor® 780. Cells in the lymphocyte gate were used for analysis.

[View more figures on thermofisher.com](https://www.thermofisher.com)

Flow Cytometry (3)

Nature communications

Loss of HIF-1 in natural killer cells inhibits tumour growth by stimulating non-productive angiogenesis.

"47-5971 was used in Flow cytometry/Cell sorting to investigate the mechanisms by which loss of HIF1 in natural killer cells inhibits tumour growth."

Authors: Krzywinska E, Kantari-Mimoun C, Kerdiles Y, Sobecki M, Isagawa T, Gotthardt D, Castells M, Haubold J, Millien C, Viel T, Tavitian B, Takeda N, Fandrey J, Vivier E, Sexl V, Stockmann C

Species
Mouse

Dilution
Not Cited

Year
2017

PloS one

Differential regulation of C5a receptor 1 in innate immune cells during the allergic asthma effector phase.

"47-5971 was used in Flow cytometry/Cell sorting to demonstrate a complex regulation pattern of C5aR1 in the airways, lung tissue and lymph nodes of mice."

Authors: Ender F, Wiese AV, Schmutte I, Sun J, Vollbrandt T, König P, Laumonier Y, Köhl J

Species
Mouse

Dilution
Not Cited

Year
2017

[View more Flow references on thermofisher.com](#)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.