

CD123 Monoclonal Antibody (6H6), eFluor™ 450, eBioscience™

Product Details

Size	100 Tests
Species Reactivity	Human
Published Species	Human
Host/Isotype	Mouse / IgG1, kappa
Recommended Isotype Control	Mouse IgG1 kappa Isotype Control (P3.6.2.8.1), eFluor™ 450, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	6H6
Conjugate	eFluor™ 450
Excitation/Emission Max	405/445 nm
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.2% BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_1548710

Applications	Tested Dilution	Publications
Immunohistochemistry (Paraffin) (IHC (P))	-	2 Publications
Immunohistochemistry (Frozen) (IHC (F))	-	2 Publications
Flow Cytometry (Flow)	5 µL (0.25 µg)/test	13 Publications

Product Specific Information

Description: The 6H6 monoclonal antibody reacts with human CD123, the alpha chain of the IL-3 receptor. This 60-70 kDa transmembrane protein binds to IL-3 with low affinity by itself, and when associated with CD131 (common beta chain) binds IL-3 with high affinity. CD123 is expressed by myeloid precursors, macrophages, dendritic cells, mast cells, basophils, and megakaryocytes.

Applications Reported: This 6H6 antibody has been reported for use in flow cytometric analysis.


Applications Tested: This 6H6 antibody has been pre-titrated and tested by flow cytometric analysis of normal human peripheral blood cells. This can be used at 5 µL (0.25 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test.

eFluor® 450 is an alternative to Pacific Blue®. eFluor® 450 emits at 445 nm and is excited with the Violet laser (405 nm). Please make sure that your instrument is capable of detecting this fluorochrome.

Excitation: 405 nm; **Emission:** 445 nm; **Laser:** Violet Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD123 Monoclonal Antibody (6H6), eFluor™ 450, eBioscience™



CD123 Antibody (48-1239-42) in Flow
Staining of normal human peripheral blood cells with Anti-Human CD85g (ILT7) PE (Product # 12-5179-42) and Mouse IgG1 kappa Isotype Control eFluor® 450 (Product # 48-4714-82) (left) or Anti-Human CD123 eFluor® 450 (right). Cells in the lymphocyte gate were used for analysis.

View more figures on thermofisher.com

17 References

Immunohistochemistry (Paraffin) (2)

<p>The Journal of investigative dermatology</p> <p>Local activation of the innate immune system in Buruli ulcer lesions.</p> <p>Authors: Peduzzi E,Groeper C,Schütte D,Zajac P,Rondini S,Mensah-Quainoo E,Spagnoli GC,Pluschke G, Daubenberger CA</p>	<p>Year 2007</p>
--	----------------------

<p>Modern pathology : an official journal of the United States and Canadian Academy of Pathology, Inc</p> <p>Expression of the plasmacytoid dendritic cell marker BDCA-2 supports a spectrum of maturation among CD4+ CD56+ hematodermic neoplasms.</p> <p>Authors: Jaye DL,Geigerman CM,Herling M,Eastburn K,Waller EK,Jones D</p>	<p>Year 2006</p>
--	----------------------

Immunohistochemistry (Frozen) (2)

<p>Journal of clinical pathology</p> <p>CD56-positive haematological neoplasms of the skin: a multicentre study of the Cutaneous Lymphoma Project Group of the European Organisation for Research and Treatment of Cancer.</p> <p>"Published figure using CD123 monoclonal antibody (Product # 48-1239-42) in Immunohistochemistry"</p> <p>Authors: Assaf C,Gellrich S,Whittaker S,Robson A,Cerroni L,Massone C,Kerl H,Rose C,Chott A,Chimenti S,Hallermann C,Petrella T,Wechsler J,Bagot M,Hummel M,Bullani-Kerl K,Bekkenk MW,Kempf W,Meijer CJ,Willems R,Sterry W</p>	<p>Year 2007</p>
--	----------------------

<p>Nature immunology</p> <p>Epithelial cells trigger frontline immunoglobulin class switching through a pathway regulated by the inhibitor SLPI.</p> <p>Authors: Xu W,He B,Chiu A,Chadburn A,Shan M,Buldys M,Ding A,Knowles DM,Santini PA,Cerutti A</p>	<p>Year 2007</p>
--	----------------------

More applications with references on thermofisher.com

Flow (13)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.