

HLA-DR Monoclonal Antibody (LN3), eFluor 450, eBioscience™

Product Details	
Size	100 Tests
Species	Human
Published Species	Human
Expression System	Mouse / IgG2b, kappa
Recommended Isotype Control	Mouse IgG2b kappa Isotype Control (eBMG2b), eFluor 450, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	LN3
Conjugate	eFluor® 450
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.1% gelatin, 0.2% BSA
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_10718248

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	5 µL (0.125 µg)/test	9 Publications
ELISA (ELISA)	-	1 Publication
Immunocytochemistry (ICC)	-	1 Publication
Immunohistochemistry (IHC)	-	1 Publication

Product Specific Information

Description: The LN3 mAb reacts with the human major histocompatibility complex (MHC) class II, HLA-DR. HLA-DR is expressed on the surface of human antigen presenting cells (APC) including B cells, monocytes, macrophages, DCs, and activated T cells. HLA-DR is a heterodimeric transmembrane protein composed of alpha and beta subunits and plays an important role in the presentation of peptides to CD4⁺ T lymphocytes.

Applications Reported: This LN3 antibody has been reported for use in flow cytometric analysis.


Applications Tested: This LN3 antibody has been pre-titrated and tested by flow cytometric analysis of normal human peripheral blood cells. This can be used at 5 µL (0.125 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test.

eFluor® 450 is an alternative to Pacific Blue®. eFluor® 450 emits at 445 nm and is excited with the Violet laser (405 nm). Please make sure that your instrument is capable of detecting this fluorochrome.

Excitation: 405 nm; Emission: 445 nm; Laser: Violet Laser.

Filtration: 0.2 µm post-manufacturing filtered.


✓ Advanced Verification Data



HLA-DR Antibody (48-9956-42)

Staining of human peripheral blood cells. As expected based on known relative expression patterns, HLA-DR clone LN3 stains monocytes and a subset of lymphocytes (B cells) but does not stain granulocytes. Details: Normal human whole blood was surface stained with HLA-DR (clone LN3). After staining, red blood cells were lysed using 1-step Fix/Lyse Buffer. Cells in the lymphocyte (purple histogram), monocyte (orange histogram), or granulocyte (blue histogram) gates were used for analysis of HLA-DR staining. Relative expression validation info.

Product Images For HLA-DR Monoclonal Antibody (LN3), eFluor 450, eBioscience™



HLA-DR Antibody (48-9956-42) in Flow

Staining of normal human peripheral blood cells with Mouse IgG2b K Isotype Control eFluor® 450 (Product # 48-4732-82) (blue histogram) or Anti-Human HLA-DR eFluor® 450 (purple histogram). Cells in the lymphocyte (left) or monocyte (right) gate were used for analysis.

View more figures on thermofisher.com

12 References

Immunohistochemistry (1)

Frontiers in molecular neuroscience

Increased White Matter Inflammation in Aging- and Alzheimer's Disease Brain.

"Published figure using HLA-DR monoclonal antibody (Product # 48-9956-42) in Immunohistochemistry"

Authors: Raj D, Yin Z, Breur M, Doorduyn J, Holtman IR, Olah M, Mantingh-Otter IJ, Van Dam D, De Deyn PP, den Dunnen W, Eggen BJL, Amor S, Boddeke E

Species
Not Applicable

Dilution
Not Cited

Year
2020

Flow Cytometry (9)

mAbs

Improved in vitro and in vivo activity against CD303-expressing targets of the chimeric 122A2 antibody selected for specific glycosylation pattern.

"48-9956 was used in Flow cytometry/Cell sorting to indicate that ch122A2 mAb could represent a promising cytotoxic mAb candidate for pathologies requiring a decrease in type I IFNs or pDCs."

Authors: Fournier N, Jacque E, Fontayne A, Derache D, Dupont G, Verhaeghe L, Baptista L, Dehenne A, Dezetter AS, Terrier A, Longue A, Pochet-Beghin V, Beghin C, Chtourou S, de Romeuf C

Species
Human

Dilution
Not Cited

Year
2019

Cell reports

Large-Scale Human Dendritic Cell Differentiation Revealing Notch-Dependent Lineage Bifurcation and Heterogeneity.

"Published figure using HLA-DR monoclonal antibody (Product # 48-9956-42) in Flow Cytometry"

Authors: Balan S, Arnold-Schrauf C, Abbas A, Couespel N, Savoret J, Imperatore F, Villani AC, Vu Manh TP, Bhardwaj N, Dalod M

Species
Not Applicable

Dilution
Not Cited

Year
2018

[View more Flow references on thermofisher.com](#)

ELISA (1)

Stem cell reports

Lack of T Cell Response to iPSC-Derived Retinal Pigment Epithelial Cells from HLA Homozygous Donors.

"Published figure using HLA-DR monoclonal antibody (Product # 48-9956-42) in ELISA"

Authors: Sugita S, Iwasaki Y, Makabe K, Kimura T, Futagami T, Suegami S, Takahashi M

Species
Human

Dilution
Not Cited

Year
2016

More applications with references on thermofisher.com

ICC (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.