

# IL-10 Monoclonal Antibody (JES3-9D7), eFluor™ 660, eBioscience™

Product Details	
Size	100 Tests
Species Reactivity	Human
Published Species	Human
Host/Isotype	Rat / IgG1, kappa
Recommended Isotype Control	Rat IgG1 kappa Isotype Control (eBRG1), eFluor™ 660, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	JES3-9D7
Conjugate	eFluor™ 660
Excitation/Emission Max	651/668 nm
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.2% BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_11149363

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	2 Publications
Flow Cytometry (Flow)	5 µL (0.125 µg)/test	8 Publications
ELISA (ELISA)	-	4 Publications
Functional Assay (FN)	-	1 Publication

## Product Specific Information

**Description:** The JES3-9D7 monoclonal antibody reacts with human interleukin-10 (IL-10).

**Applications Reported:** This JES3-9D7 antibody has been reported for use in flow cytometric analysis, and intracellular staining followed by flow cytometric analysis.


**Applications Tested:** This JES3-9D7 antibody has been pre-titrated and tested by intracellular staining and flow cytometry analysis of Th2 polarized and stimulated human peripheral blood cells. This can be used at 5 µL (0.125 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10<sup>5</sup> to 10<sup>8</sup> cells/test.

eFluor® 660 is a replacement for Alexa Fluor® 647. eFluor® 660 emits at 659 nm and is excited with the red laser (633 nm). Please make sure that your instrument is capable of detecting this fluorochrome.

Excitation: 633-647 nm; Emission: 668 nm; Laser: Red Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For IL-10 Monoclonal Antibody (JES3-9D7), eFluor™ 660, eBioscience™



IL-10 Antibody (50-7108-42) in Flow

CD4+ human peripheral blood cells were polarized under Th2 conditions then were unstimulated (left) or stimulated for 5 hours with Cell Stimulation Cocktail (plus protein transport inhibitors) (Product # 00-4975-03). Cells were intracellularly stained with Anti-Human CD4 FITC (Product # 11-0049-42) and Anti-Human IL-10 eFluor® 660 using the Fixation & Permeabilization Buffers (Product # 88-8824-00). Total viable cells were used for analysis.

View more figures on [thermofisher.com](https://thermofisher.com)

Immunohistochemistry (2)

<p>Saudi journal of biological sciences</p> <p><b>Histological changes of cervical tumours following <i>Zanthoxylum acanthopodium</i> DC treatment, and its impact on cytokine expression.</b></p> <p>"Published figure using IL-10 monoclonal antibody (Product # 50-7108-42) in Immunohistochemistry"</p> <p>Authors: Simanullang RH,Situmorang PC,Herlina M,Silalahi B,Manurung SS</p>	<p>Year</p> <p>2022</p>
<p>Laboratory investigation; a journal of technical methods and pathology</p> <p><b>Functional expression of aryl hydrocarbon receptor on mast cells populating human endometriotic tissues.</b></p> <p>"Published figure using IL-10 monoclonal antibody (Product # 50-7108-42) in ELISA"</p> <p>Authors: Mariuzzi L,Domenis R,Orsaria M,Marzinotto S,Londero AP,Bulfony M,Candotti V,Zanello A,Ballico M,Mimmi MC,Calcagno A,Marchesoni D,Di Loreto C,Beltrami AP,Cesselli D,Gri G</p>	<p>Year</p> <p>2016</p> <p>Species</p> <p>Human</p>

Flow Cytometry (8)

<p>Journal of cardiovascular development and disease</p> <p><b>Circulating Regulatory B-Lymphocytes in Patients with Acute Myocardial Infarction: A Pilot Study.</b></p> <p>"Published figure using IL-10 monoclonal antibody (Product # 50-7108-42) in Flow Cytometry"</p> <p>Authors: Volodarsky I,Shimoni S,Haberman D,Mirkin V,Fabrikant Y,Yoskovich Mashriki T,Zalik A,George J</p>	<p>Year</p> <p>2022</p>
<p>Journal of inflammation research</p> <p><b>Altered T-Cell Subsets are Associated with Dysregulated Cytokine Secretion of CD4<sup>+</sup> T Cells During HIV Infection.</b></p> <p>"Published figure using IL-10 monoclonal antibody (Product # 50-7108-42) in Flow Cytometry"</p> <p>Authors: Wang D,Jiang Y,Song Y,Zeng Y,Li C,Wang X,Liu Y,Xiao J,Kong Y,Zhao H</p>	<p>Year</p> <p>2022</p>

View more Flow references on thermofisher.com

More applications with references on thermofisher.com

- ELISA (4)
- FN (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.