

CD284 (TLR4) Monoclonal Antibody (HTA125), Alexa Fluor™ 700, eBioscience™

Product Details	
Size	100 Tests
Species Reactivity	Human
Published Species	Shark, Human
Host/Isotype	Mouse / IgG2a, kappa
Recommended Isotype Control	Mouse IgG2a kappa Isotype Control (eBM2a), Alexa Fluor™ 700, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	HTA125
Conjugate	Alexa Fluor™ 700
Excitation/Emission Max	696/719 nm
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.2% BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_10597889

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	3 Publications
Immunohistochemistry (Paraffin) (IHC (P))	-	1 Publication
Immunocytochemistry (ICC/IF)	-	2 Publications
Flow Cytometry (Flow)	5 µL (1 µg)/test	12 Publications
ELISA (ELISA)	-	1 Publication
Neutralization (Neu)	-	8 Publications
Functional Assay (FN)	-	1 Publication

Product Specific Information

Description: The HTA125 monoclonal antibody reacts with human Toll-like receptor 4 (TLR4). So far, at least ten members of the Toll family have been identified in humans. This family of type I transmembrane proteins is characterized by an extracellular domain with leucine-rich repeats and a cytoplasmic domain with homology to the type I IL-1 receptor. Two of these receptors, TLR2 and TLR4, are pattern recognition receptors and signaling molecules in response to bacterial lipoproteins and have been implicated in innate immunity and inflammation. TLR4 physically associates with another molecule called MD-2, and together with CD14, this complex is responsible for LPS recognition and signaling. TLR4 is expressed by peripheral blood monocytes. HTA125 has been reported to immunoprecipitate human TLR4 (~100 kDa) from transfected cells. Most TLR cell surface expression, especially TLR1 and TLR4, occurs at low levels on monocytes and at even lower levels on other cell types including granulocytes and immature dendritic cells (iDC). Furthermore, a relatively high degree of variability in TLR surface expression has been reported among normal donors.

It is highly recommended that for optimal staining of TLR4, whole blood be stained using the lysed whole blood protocol (found in Best Protocols) rather than Ficoll-gradient prepared normal human peripheral blood cells. The use of a density gradient appears to reduce the staining intensity significantly.

Applications Reported: This HTA125 antibody has been reported for use in flow cytometric analysis.


Applications Tested: This HTA125 antibody has been pre-titrated and tested by flow cytometric analysis of normal human peripheral blood cells. This can be used at 5 μ L (1.0 μ g) per test. A test is defined as the amount (μ g) of antibody that will stain a cell sample in a final volume of 100 μ L. Cell number should be determined empirically but can range from 10^5 to 10^8 cells /test.

Alexa Fluor® 700 emits at 723 nm and can be excited with the red laser (633 nm). Most instruments will require a 685 LP mirror and 710/20 filter. Please make sure that your instrument is capable of detecting this fluorochrome.

Excitation: 633-647 nm; Emission: 723 nm; Laser: Red Laser.

Filtration: 0.2 μ m post-manufacturing filtered.

Product Images For CD284 (TLR4) Monoclonal Antibody (HTA125), Alexa Fluor™ 700, eBioscience™



[View more figures on thermofisher.com](#)

Immunohistochemistry (3)

<p>PloS one</p> <p>TLR4 Expression Is Associated with Left Ventricular Dysfunction in Patients Undergoing Coronary Artery Bypass Surgery.</p> <p>"Published figure using CD284 (TLR4) monoclonal antibody (Product # 56-9917-42) in Flow Cytometry"</p> <p>Authors: Avlas O,Bragg A,Fuks A,Nicholson JD,Farkash A,Porat E,Aravot D,Levy-Drummer RS,Cohen C,Shainberg A, Arad M,Hochhauser E</p>	<p>Year 2016</p>
<p>PloS one</p> <p>Biologically active polymers from spontaneous carotenoid oxidation: a new frontier in carotenoid activity.</p> <p>"Published figure using CD284 (TLR4) monoclonal antibody (Product # 56-9917-42) in Immunocytochemistry"</p> <p>Authors: Johnston JB,Nickerson JG,Daroszewski J,Mogg TJ,Burton GW</p>	<p>Year 2015</p>

[View more IHC references on thermofisher.com](#)

Immunohistochemistry (Paraffin) (1)

<p>Microbes and infection</p> <p>Human heat shock protein 60 stimulates vascular smooth muscle cell proliferation through Toll-like receptors 2 and 4.</p> <p>Authors: de Graaf R,Kloppenburg G,Kitslaar PJ,Bruggeman CA,Stassen F</p>	<p>Year 2006</p>
---	-----------------------------

Immunocytochemistry (2)

<p>Science signaling</p> <p>The COP II adaptor protein TMED7 is required to initiate and mediate the delivery of TLR4 to the plasma membrane.</p> <p>"Published figure using CD284 (TLR4) monoclonal antibody (Product # 56-9917-42) in Immunofluorescence"</p> <p>Authors: Liaunardy-Jopeace A,Bryant CE,Gay NJ</p>	<p>Year 2014</p> <p>Species Human</p>
---	---

More applications with references on thermofisher.com

- Flow (12)
- ELISA (1)
- Neu (8)
- FN (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.