

# CD9 Monoclonal Antibody (eBioSN4 (SN4 C3-3A2)), Super Bright™ 436, eBioscience™

Product Details	
Size	25 Tests
Species Reactivity	Human
Published Species	Human
Host/Isotype	Mouse / IgG1, kappa
Recommended Isotype Control	Mouse IgG1 kappa Isotype Control (P3.6.2.8.1), Super Bright™ 436, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	eBioSN4 (SN4 C3-3A2)
Conjugate	Super Bright™ 436
Excitation/Emission Max	413/431 nm
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2762499

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	5 µL (0.25 µg)/test	4 Publications

## Product Specific Information

Description: The eBioSN4 monoclonal antibody reacts with human CD9. CD9 is a 24 kDa member of the tetraspanin family, whose members are characterized by the presence of 4 hydrophobic transmembrane domains. CD9 is expressed in platelets, eosinophils, basophils, pre-B cells, activated T cells and neural cell lines. Furthermore, CD9 expression has been associated with a malignant phenotype, including expression on 90% of non T cell acute lymphoblastic leukemia cells and on 50% of chronic lymphocytic and acute myeloblastic leukemias. In platelets, CD9 is expressed in alpha-granules and through association with the integrin alphaIIb/betaIII plays a role in platelet aggregation, as demonstrated by the use of anti-human CD9 antibodies. CD9 has also been shown to induce the aggregation of pre-B cell lines, and the adhesion and migration of pre-B cells and Schwann cells. Additionally, it has been demonstrated that CD9 is able to provide a co-stimulatory signal for T cells independently of CD28, in the absence of antigen-presenting cells. Binding of the eBioSN4 monoclonal antibody partially cross-blocks binding of another anti-human CD9 monoclonal antibody, MM2/57.

Applications Reported: This eBioSN4 (SN4 C3-3A2) antibody has been reported for use in flow cytometric analysis.

Applications Tested: This eBioSN4 (SN4 C3-3A2) antibody has been pre-titrated and tested by flow cytometric analysis of normal human platelets. This can be used at 5 µL (0.25 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10<sup>5</sup> to 10<sup>8</sup> cells/test.

Super Bright 436 can be excited with the violet laser line (405 nm) and emits at 436 nm. We recommend using a 450/50

bandpass filter, or equivalent. Please make sure that your instrument is capable of detecting this fluorochrome.

When using two or more Super Bright dye-conjugated antibodies in a staining panel, it is recommended to use Super Bright Complete Staining Buffer (Product # SB-4401) to minimize any non-specific polymer interactions. Please refer to the datasheet for Super Bright Staining Buffer for more information.


Excitation: 405 nm; Emission: 436 nm; Laser: Violet Laser

Super Bright Polymer Dyes are sold under license from Becton, Dickinson and Company.

## Product Images For CD9 Monoclonal Antibody (eBioSN4 (SN4 C3-3A2)), Super Bright™ 436, eBioscience™

### CD9 Antibody (62-0098-41) in Flow

Normal human peripheral blood cells were stained with Mouse IgG1 kappa Isotype Control, Super Bright 436 (Product # 62-4714-82) (blue histogram) or CD9 Monoclonal Antibody, Super Bright 436 (purple histogram). Cells in the monocyte gate were used for analysis.



[View more figures on thermofisher.com](#)

## 4 References

### Flow Cytometry (4)

Cancers	Year
<b>Extracellular Vesicle Membrane Protein Profiling and Targeted Mass Spectrometry Unveil CD59 and Tetraspanin 9 as Novel Plasma Biomarkers for Detection of Colorectal Cancer.</b>	2022

"Published figure using CD9 monoclonal antibody (Product # 62-0098-42) in Flow Cytometry"

Authors: Dash S,Wu CC,Wu CC,Chiang SF,Lu YT,Yeh CY,You JF,Chu LJ,Yeh TS,Yu JS

Cells	Year
<b>Anti-Human CD9 Fab Fragment Antibody Blocks the Extracellular Vesicle-Mediated Increase in Malignancy of Colon Cancer Cells.</b>	2022

"Published figure using CD9 monoclonal antibody (Product # 62-0098-42) in Flow Cytometry"

Authors: Santos MF,Rappa G,Fontana S,Karbanová J,Aalam F,Tai D,Li Z,Pucci M,Alessandro R,Morimoto C,Corbeil D,Lorico A

[View more Flow references on thermofisher.com](#)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.