

NR5A1 Monoclonal Antibody (N1665)

Product Details	
Size	100 µL
Species Reactivity	Human, Mouse, Rat
Published Species	Rat, Human, Mouse
Host/Isotype	Mouse / IgG1
Class	Monoclonal
Type	Antibody
Clone	N1665
Conjugate	Unconjugated
Immunogen	BALB/c mouse immunized with E.coli-expressed recombinant human SF-1 (218-461aa).
Form	Liquid
Concentration	1 mg/mL
Purification	Protein A
Storage buffer	physiological saline
Contains	0.1% sodium azide
Storage conditions	Maintain refrigerated at 2-8°C for up to 1 month. For long term storage store at -20°C
RRID	AB_2532209

Applications	Tested Dilution	Publications
Western Blot (WB)	3 µg/mL	-
Immunohistochemistry (IHC)	-	10 Publications
Immunohistochemistry (Paraffin) (IHC (P))	10 µg/mL	2 Publications
Immunohistochemistry (PFA fixed) (IHC (PFA))	-	1 Publication
Immunohistochemistry (Frozen) (IHC (F))	-	1 Publication
Immunocytochemistry (ICC/IF)	-	3 Publications
ELISA (ELISA)	0.1 µg/mL	-
Immunoprecipitation (IP)	Assay-dependent	-
Miscellaneous PubMed (Misc)	-	1 Publication


Product Specific Information

This antibody specifically recognizes human SF-1 and cross reacts with mouse and rat SF-1.

Product Images For NR5A1 Monoclonal Antibody (N1665)

NR5A1 Antibody (434200) in WB

Western blot was performed using NR5A1 Monoclonal Antibody (Product # 434200) and a 50 kDa band corresponding to NR5A1 was observed in the cell line and tissues tested. Modified whole cell extracts (1% SDS) (30 µg lysate) of Hep G2 (Lane 1), Hek-293 (Lane 2), tissue extracts of Mouse Ovary (Lane 3), Mouse Heart (Lane 4) and Mouse Prostate (Lane 5) were electrophoresed using NuPAGE™ 4-12% Bis-Tris Protein Gel (Product # NP0322BOX). Resolved proteins were then transferred onto a nitrocellulose membrane (Product # IB23001) by iBlot® 2 Dry Blotting System (Product # IB21001). The blot was probed with the primary antibody (3 µg/ml) and detected by chemiluminescence with Goat anti-Mouse IgG (H+L) Superclonal™ Recombinant Secondary Antibody, HRP (Product # A28177, 1:4000 dilution) using the iBright FL 1000 (Product # A32752). Chemiluminescent detection was performed using SuperSignal™ West Dura Extended Duration Substrate (Product # 34076). Hek-293 cell line, Heart and Prostate tissues have been reported to have low to negative expression of NR5A1. (Note: A band at ~25 kDa was observed in mouse tissues corresponding to circulating IgG).



[View more figures on thermofisher.com](#)

Immunohistochemistry (10)

Clinical endocrinology Pre- and postoperative ⁶⁸ Ga-DOTATOC positron emission tomography for hormone-secreting pituitary neuroendocrine tumours. "434200 was used in Immunohistochemistry to show that corticotroph tumours had a significantly lower uptake compared to the pituitary gland but without a distinct increased tumour uptake the clinical postoperative value is limited." Authors: Tjörnstrand A,Casar-Borota O,Heurling K,Schöll M,Gjertsson P,Ragnarsson O,Filipsson Nyström H	Year 2021 Species Human Dilution 1:100
Neuropathology and applied neurobiology Gonadotroph tumours with a low SF-1 labelling index are more likely to recur and are associated with enrichment of the PI3K-AKT pathway. "Published figure using NR5A1 monoclonal antibody (Product # 434200) in Immunohistochemistry" Authors: Hickman RA,Bruce JN,Otten M,Khandji AG,Flowers XE,Siegelin M,Lopes B,Faust PL,Freda PU	Year 2021

View more IHC references on thermofisher.com

Immunohistochemistry (Paraffin) (2)

Endocrine pathology Oncogene-Induced Senescence in Pituitary Adenomas--an Immunohistochemical Study. "434200 was used in immunohistochemistry - paraffin section to report the expression of senescence-associated lysosomal beta-galactosidase, p16, and p21 in different types of pituitary adenomas" Authors: Manojlovic-Gacic E,Skender-Gazibara M,Popovic V,Soldatovic I,Boricic N,Raicevic S,Pekic S,Doknic M,Miljic D,Alafuzoff I,Pontén F,Casar-Borota O	Year 2016 Species Human Dilution 1:200
Endocrinology Steroidogenic factor 1 promotes aggressive growth of castration-resistant prostate cancer cells by stimulating steroid synthesis and cell proliferation. "Published figure using NR5A1 monoclonal antibody (Product # 434200) in Immunohistochemistry" Authors: Lewis SR,Hedman CJ,Ziegler T,Ricke WA,Jorgensen JS	Year 2014 Species Human

More applications with references on thermofisher.com

- IHC (PFA) (1)
- IHC (F) (1)
- ICC/IF (3)
- Misc (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.