


Phospho-c-Abl (Tyr245) Polyclonal Antibody

Product Details	
Size	100 µL
Species Reactivity	Human
Published Species	Tag
Host/Isotype	Rabbit / IgG
Class	Polyclonal
Type	Antibody
Conjugate	Unconjugated
Immunogen	synthesized phosphopeptide derived from a region of human c-Abl that contains tyrosine 245
Form	Liquid
Purification	Antigen affinity chromatography
Storage buffer	Dulbecco's PBS, pH 7.3, with 1mg/mL BSA
Contains	0.05% sodium azide
Storage conditions	-20°C
RRID	AB_2533616


Applications	Tested Dilution	Publications
Western Blot (WB)	1:1,000	1 Publication
Immunocytochemistry (ICC/IF)	1:250	-

Product Images For Phospho-c-Abl (Tyr245) Polyclonal Antibody




Phospho-c-Abl (Tyr245) Antibody (44-250) in WB

Peptide Competition: Fibroblasts transfected with oncogenic DSH3-Abl were incubated with 0.50 µg/mL c-Abl (pY245) antibody, following prior incubation with: no peptide (1), the non-phosphopeptide corresponding to the immunogen (2), a generic phospho



Phospho-c-Abl (Tyr245) Antibody (44-250)

Detection of altered subcellular localization of the target protein by cell treatment demonstrates antibody specificity. Immunofluorescence analysis of Phospho-c-Abl (Tyr245) using Phospho-c-Abl (Tyr245) polyclonal antibody (Product # 44-250), shows change in localization of Phospho-c-Abl (Tyr245) from nuclear to both nuclear and cytoplasmic in HeLa cells upon treatment with curcumin. {TM}



Phospho-c-Abl (Tyr245) Antibody (44-250) in ICC/IF

Immunofluorescence analysis of Phospho-c-Abl (Tyr245) Polyclonal Antibody was performed using 70% confluent log phase HeLa cells treated with 4 micromolar Curcumin for 4h. The cells were fixed with 4% paraformaldehyde for 10 minutes, permeabilized with 0.1% Triton X-100 for 10 minutes, and blocked with 1% BSA for 1 hour at room temperature. The cells were labeled with Phospho-c-Abl (Tyr245) Rabbit Polyclonal Antibody (Product # 44-250) at 1:250 dilution in 0.1% BSA and incubated for 3 hours at room temperature and then labeled with Goat anti-Rabbit IgG (Heavy Chain) Superclonal Secondary Antibody, Alexa Fluor® 488 conjugate (Product # A27034) at a dilution of 1:2000 for 45 minutes at room temperature (Panel a: green). Nuclei (Panel b: blue) were stained with SlowFade® Gold Antifade Mountant with DAPI (Product # S36938). F-actin (Panel c: red) was stained with Rhodamine Phalloidin (Product # R415, 1:300). Panel d represents the merged image showing nuclear and cytoplasmic localization. Panel e shows the untreated cells with nuclear localization. Panel e shows the no primary antibody control. The images were captured at 60X magnification.

1 Reference

Western Blot (1)

The Journal of biological chemistry

Src family kinases phosphorylate the Bcr-Abl SH3-SH2 region and modulate Bcr-Abl transforming activity.

Authors: Meyn MA,Wilson MB,Abdi FA,Fahey N,Schiavone AP,Wu J,Hochrein JM,Engen JR,Smithgall TE

Year
2006

Species
Tag

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (i) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (ii) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (iii) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (iv) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.