

IL-33R (ST2) Monoclonal Antibody (RMST2-2), Super Bright™ 436, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Host/Isotype	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), Super Bright™ 436, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	RMST2-2
Conjugate	Super Bright™ 436
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2717013

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	1 Publication
Flow Cytometry (Flow)	1 µg/test	2 Publications

Product Specific Information

Description: The RMST2-2 monoclonal antibody reacts with ST2, also known as IL-33 receptor (IL-33R) or interleukin 1 receptor-like 1. ST2 is a member of the IL-1 receptor family. In the membrane-bound form, it consists of three extra-cellular immunoglobulin domains and an intracellular toll-interleukin-1 receptor domain. ST2 forms a dimer with IL-1R accessory protein in a ligand-dependent manner. The IL-33/ST2 interaction induces the production of TH2 cytokines. ST2 also has a soluble isoform lacking transmembrane and intracellular toll-interleukin-1 receptor domains. It is believed that the soluble form functions as a decoy receptor that can block membrane bound IL-33/ST2 interaction. ST2 is expressed by TH2 lymphocytes, mast cells, eosinophils, basophils, innate lymphocytes, smooth muscle cells, and endothelial cells and is involved in host defense, allergy, and inflammation. The IL-33/ST2 interaction has also been shown to be atheroprotective.

Applications Reported: This RMST2-2 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This RMST2-2 antibody has been tested by flow cytometric analysis of mouse bone marrow-derived mast cells. This can be used at less than or equal to 1.0 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Super Bright 436 can be excited with the violet laser line (405 nm) and emits at 436 nm. We recommend using a 450/50 bandpass


filter, or equivalent. Please make sure that your instrument is capable of detecting this fluorochrome.

When using two or more Super Bright dye-conjugated antibodies in a staining panel, it is recommended to use Super Bright Complete Staining Buffer (Product # SB-4401) to minimize any non-specific polymer interactions. Please refer to the datasheet for Super Bright Staining Buffer for more information.

Excitation: 405 nm; Emission: 436 nm; Laser: Violet Laser

Super Bright Polymer Dyes are sold under license from Becton, Dickinson and Company.

Product Images For IL-33R (ST2) Monoclonal Antibody (RMST2-2), Super Bright™ 436, eBioscience™



IL-33R (ST2) Antibody (62-9335-82) in Flow

C57BL/6 mouse bone marrow-derived mast cells were stained with FceR1 Monoclonal Antibody, APC (Product # 17-5898-82) and 0.5 µg of Rat IgG2a kappa Isotype Control, Super Bright 436 (Product # 62-4321-82) (left) or 0.5 µg of IL-33R (ST2) Monoclonal Antibody, Super Bright 436 (right). Total viable cells were used for analysis, as determined by Fixable Viability Dye eFluor 506 (Product # 65-0866-18).

[View more figures on thermofisher.com](https://www.thermofisher.com)

Immunohistochemistry (1)

Human reproduction open

A 3D endometrial organotypic model simulating the acute inflammatory decidualisation initiation phase with epithelial induction of the key endometrial receptivity marker, integrin V3.

"Published figure using IL-33R (ST2) monoclonal antibody (Product # 62-9335-82) in Immunohistochemistry"

Authors: Fraser R,Smith R,Lin CJ

Species
Not Applicable

Dilution
Not Cited

Year
2022

Flow Cytometry (2)

Cell reports

TNFR2 Signaling Enhances ILC2 Survival, Function, and Induction of Airway Hyperreactivity.

"Published figure using IL-33R (ST2) monoclonal antibody (Product # 62-9335-82) in Flow Cytometry"

Authors: Hurrell BP,Galle-Treger L,Jahani PS,Howard E,Helou DG,Banie H,Soroosh P,Akbari O

Species
Not Applicable

Dilution
Not Cited

Year
2019

Nature communications

Costimulation of type-2 innate lymphoid cells by GITR promotes effector function and ameliorates type 2 diabetes.

"Published figure using IL-33R (ST2) monoclonal antibody (Product # 62-9335-82) in Flow Cytometry"

Authors: Galle-Treger L,Sankaranarayanan I,Hurrell BP,Howard E,Lo R,Maazi H,Lewis G,Banie H,Epstein AL,Hu P,Rehan VK,Gilliland FD,Allyayee H,Soroosh P,Sharpe AH,Akbari O

Species
Not Applicable

Dilution
Not Cited

Year
2019

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.