.

TCR V alpha 2 Monoclonal Antibody (B20.1), APC-eFluor™ 780, eBioscience™

Product Details	
Size	25 µg
Species Reactivity	Mouse
Published Species	Mouse
Host/Isotype	Rat / IgG2a, lambda
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), APC-eFluor™ 780, eBioscience™
Class	Monoclonal
Туре	Antibody
Clone	B20.1
Conjugate	APC-eFluor™ 780
Excitation/Emission Max	756/785 nm
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_11041384

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.25 μg/test	3 Publications

Product Specific Information

Description: The B20.1 monoclonal antibody reacts with mouse T-cell receptor (TCR) V alpha 2 chains. This antibody recognizes the majority of the TCR V alpha 2 subfamily in mice carrying the a, b and c haplotypes. The antibody also reacts with the products of T cell receptor, V delta 8 due to the high degree of homology.

Applications Reported: This B20.1 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This B20.1 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.25 μ g per test. A test is defined as the amount (μ g) of antibody that will stain a cell sample in a final volume of 100 μ L. Cell number should be determined empirically but can range from 10^5 to 10^8 cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

APC-eFluor 780 emits at 780 nm and is excited with the Red laser (633 nm). Please make sure that your instrument is capable of detecting this fluorochome.

Light sensitivity: This tandem is sensitive to photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (Product # 00-8222) (100 μ L cell sample + 100 μ L IC Fixation Buffer) or 1step Fix/Lyse Solution (Product # 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency/compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 633-647 nm; Emission: 780 nm; Laser: Red Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For TCR V alpha 2 Monoclonal Antibody (B20.1), APC-eFluor™ 780, eBioscience™



TCR V alpha 2 Antibody (47-5812-80) in Flow

Staining of BALB/c splenocytes with Anti-Mouse CD4 and CD8 FITC (Product # 11-0042-82 and Product # 11-0081-82, respectively) and 0.125 µg of Rat IgG2a K Isotype Control APC-eFluor® 780 (Product # 47-4321-82) (left) or 0.125 µg of Anti-Mouse V alpha 2 TCR APC-eFluor® 780 (right). Total viable cells were used for analysis.

View more figures on thermofisher.com

A 3 References	
Flow Cytometry (3)	
Cell reports	Year 2018
Repeated Antigen Exposure Extends the Durability of Influenza-Specific	Species Mouse
Lung-Resident Memory CD8 ⁺ T Cells and Heterosubtypic Immunity.	
"47-5812 was used in Flow cytometry/Cell sorting to demonstrate that, relative to single virus exposure, repeated antigen exposure dramatically alters the dynamics of influenza-specific lung-resident primary memory CD8+ T cell populations."	
Authors: Van Braeckel-Budimir N,Varga SM,Badovinac VP,Harty JT	
Immunology	Year
Macrophages transfer antigens to dendritic cells by releasing exosomes	2016
containing dead-cell-associated antigens partially through a ceramide-	Species
dependent pathway to enhance CD4(+) T-cell responses.	Mouse
"Published figure using TCR V alpha 2 monoclonal antibody (Product # 47-5812-80) in Flow Cytometry"	
Authors: Xu Y.Liu Y.Yang C.Kang L.Wang M.Hu J.He H.Song W.Tang H	

View more Flow references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set for hin the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regress nuthorization. Product specifications regress authorization. Product specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regressent that any Product will conform to such model or sample (numished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. No OTHER WARRANTES, EXPRESS OR INPED, ARE ORANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTES OF MERCHANTABILITY, FITNESS FOR ANY PARTICURTS DURING PRODUCTS DURING THE WARRANTES, EXPRESS OR INPERIOR SEAL TO FUNCTOR CONCOMPTICES AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (III) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER', SEAL TO FUNCTOR THE WARRANTES OF THE VARRANTES OF OR DEVENT OF FORCE MAJEURE, (III) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER', (III) USE OF THE PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (III) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER', (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation or animals.

2