

# CD11c Monoclonal Antibody (N418), eFluor™ 450, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Mouse, Human
Host/Isotype	Armenian hamster / IgG
Recommended Isotype Control	Armenian Hamster IgG Isotype Control (eBio299Arm), eFluor™ 450, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	N418
Conjugate	eFluor™ 450
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_1548654

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	12 Publications
Immunohistochemistry (Frozen) (IHC (F))	-	2 Publications
Immunocytochemistry (ICC/IF)	-	6 Publications
Flow Cytometry (Flow)	0.125 µg/test	122 Publications
Miscellaneous PubMed (Misc)	-	1 Publication

## Product Specific Information

**Description:** The N418 monoclonal antibody reacts with mouse CD11c, the integrin alphaX. CD11c non-covalently associates with beta2 integrin to form the CD11c/CD18 heterodimer. CD11c is expressed by dendritic cells, a subset of Intestinal Intraepithelial Lymphocytes (IEL) and some activated T cells. CD11c/CD18 binds to CD54, iC3b and fibrinogen and plays a role in leukocyte adhesive interactions. N418 binds to CD11c on splenic dendritic cells in the T-dependent areas of mouse spleen and precipitates a 150, 90 kDa heterodimer.

**Applications Reported:** This N418 antibody has been reported for use in flow cytometric analysis.


**Applications Tested:** This N418 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.125 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10<sup>5</sup> to 10<sup>8</sup> cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

eFluor® 450 is an alternative to Pacific Blue®. eFluor® 450 emits at 445 nm and is excited with the Violet laser (405 nm). Please make sure that your instrument is capable of detecting this fluorochoime.

Excitation: 405 nm; Emission: 445 nm; Laser: Violet Laser.

Filtration: 0.2 µm post-manufacturing filtered.

## Product Images For CD11c Monoclonal Antibody (N418), eFluor™ 450, eBioscience™



### CD11c Antibody (48-0114-82) in Flow

Staining of BALB/c splenocytes with Anti-Human/Mouse CD45R (B220) APC (Product # 17-0452-82) and 0.06 µg of Armenian Hamster IgG Isotype Control eFluor® 450 (Product # 48-4888-82) (left) or 0.06 µg of Anti-Mouse CD11c eFluor® 450 (right). Total viable cells were used for analysis.

[View more figures on thermofisher.com](https://www.thermofisher.com)

## Immunohistochemistry (12)

EMBO molecular medicine

### Glufosinate constrains synchronous and metachronous metastasis by promoting anti-tumor macrophages.

"Published figure using CD11c monoclonal antibody (Product # 48-0114-82) in Immunohistochemistry"

Authors: Menga A, Serra M, Todisco S, Riera-Domingo C, Ammarah U, Ehling M, Palmieri EM, Di Noia MA, Gissi R, Favia M, Pierri CL, Porporato PE, Castegna A, Mazzone M

**Species**  
Not Applicable

**Dilution**  
Not Cited

**Year**  
2020

International journal of molecular medicine

### Identification of different macrophage subpopulations with distinct activities in a mouse model of oxygen-induced retinopathy.

"Published figure using CD11c monoclonal antibody (Product # 48-0114-82) in Immunofluorescence"

Authors: Zhu Y, Zhang L, Lu Q, Gao Y, Cai Y, Sui A, Su T, Shen X, Xie B

**Species**  
Not Applicable

**Dilution**  
Not Cited

**Year**  
2017

[View more IHC references on thermofisher.com](#)

## Immunohistochemistry (Frozen) (2)

The Journal of experimental medicine

### Essential roles of DC-derived IL-15 as a mediator of inflammatory responses in vivo.

"Published figure using CD11c monoclonal antibody (Product # 48-0114-82) in Immunohistochemistry"

Authors: Ohteki T, Tada H, Ishida K, Sato T, Maki C, Yamada T, Hamuro J, Koyasu S

**Species**  
Not Applicable

**Dilution**  
Not Cited

**Year**  
2006

International immunology

### The existence of CD11c+ sentinel and F4/80+ interstitial dendritic cells in dental pulp and their dynamics and functional properties.

Authors: Zhang J, Kawashima N, Suda H, Nakano Y, Takano Y, Azuma M

**Species**  
Not Applicable

**Dilution**  
Not Cited

**Year**  
2006

## More applications with references on thermofisher.com

ICC/IF (6)

Flow (122)

Misc (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.