

CD90.2 (Thy-1.2) Monoclonal Antibody (53-2.1), eFluor 450, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Fish, Mouse
Host/Isotype	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), eFluor 450, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	53-2.1
Conjugate	eFluor® 450
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.1% gelatin
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_1272200

Applications	Tested Dilution	Publications
Immunofluorescence (IF)	-	1 Publication
Flow Cytometry (Flow)	0.015 µg/test	18 Publications
Miscellaneous PubMed (Misc)	-	1 Publication

Product Specific Information

Description: The 53-2.1 monoclonal antibody reacts with mouse CD90.2 also known as Thy-1.2, a GPI-linked membrane molecule. CD90.2 is expressed by mouse thymocytes and mature T cells as well as neurons in CD90.2-expressing mouse strains. These strains include BALB/c, CBA, C3H, C57BL/6, C58/, SJL and others. Cells from CD90.1-expressing strains including PL and AKR do not stain with 53-2.1. CD90 is involved in regulation of adhesion and signal transduction by T cells.

Applications Reported: This 53-2.1 antibody has been reported for use in flow cytometric analysis.


Applications Tested: This 53-2.1 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.015 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

eFluor® 450 is an alternative to Pacific Blue®. eFluor® 450 emits at 445 nm and is excited with the Violet laser (405 nm). Please make sure that your instrument is capable of detecting this fluorochrome.

Excitation: 405 nm; Emission: 445 nm; Laser: Violet Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For CD90.2 (Thy-1.2) Monoclonal Antibody (53-2.1), eFluor 450, eBioscience™



CD90.2 (Thy-1.2) Antibody (48-0902-82) in Flow

Staining of C57BL/6 splenocytes with Anti-Human/Mouse CD45R (B220) APC (Product # 17-0452-82) and 0.015 µg of Rat IgG2a kappa Isotype Control eFluor® 450 (Product # 48-4321-82) (left) or 0.0075 µg of Anti-Mouse CD90.2 (Thy-1.2) eFluor® 450 (Product # 48-0902-82) (right). Total viable cells were used for analysis.

[View more figures on thermofisher.com](http://thermofisher.com)

20 References

Immunofluorescence (1)

Nature

Single-cell transcriptomics reconstructs fate conversion from fibroblast to cardiomyocyte.

"Published figure using CD90.2 (Thy-1.2) monoclonal antibody (Product # 48-0902-82) in Immunofluorescence"

Authors: Liu Z,Wang L,Welch JD,Ma H,Zhou Y,Vaseghi HR,Yu S,Wall JB,Alimohamadi S,Zheng M,Yin C,Shen W,Prins JF,Liu J,Qian L

Species

Not Applicable

Dilution

Not Cited

Year

2017

Flow Cytometry (18)

Immunity

Nuclear export of the NF-B inhibitor IB is required for proper B cell and secondary lymphoid tissue formation.

"Published figure using CD90.2 (Thy-1.2) monoclonal antibody (Product # 48-0902-82) in Flow Cytometry"

Authors: Wuerzberger-Davis SM,Chen Y,Yang DT,Kearns JD,Bates PW,Lynch C,Ladell NC,Yu M,Podd A,Zeng H,Huang TT,Wen R,Hoffmann A,Wang D,Miyamoto S

Species

Not Applicable

Dilution

Not Cited

Year

2011

Molecular therapy. Nucleic acids

Lipidoid Nanoparticles Containing PD-L1 siRNA Delivered In Vivo Enter Kupffer Cells and Enhance NK and CD8(+) T Cell-mediated Hepatic Antiviral Immunity.

"48-0902 was used in Flow cytometry/Cell sorting to demonstrate that PD-L1 knockdown on KCs is central in determining the outcome of liver viral infections, and they represent a new class of gene therapy."

Authors: Dolina JS,Sung SS,Novobrantseva TI,Nguyen TM,Hahn YS

Species

Mouse

Dilution

Not Cited

Year

2013

[View more Flow references on thermofisher.com](#)

Miscellaneous PubMed (1)

Journal of immunology (Baltimore, Md. : 1950)

Intrarectal immunization and IgA antibody-secreting cell homing to the small intestine.

"48-0902 was used in Magnetic cell separation to investigate the organ distribution and the homing molecule expression of IgA Ab-secreting cells induced by intrarectal immunisation with a particulate Ag."

Authors: Agnello D,Denimal D,Lavaux A,Blondeau-Germe L,Lu B,Gerard NP,Gerard C,Pothier P

Species

Mouse

Dilution

Not Cited

Year

2013

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.