

CD137 (4-1BB) Monoclonal Antibody (4B4 (4B4-1)), Super Bright™ 600, eBioscience™

| Product Details | |
|-----------------------------|--|
| Size | 100 Tests |
| Species Reactivity | Human |
| Host/Isotype | Mouse / IgG1, kappa |
| Recommended Isotype Control | Mouse IgG1 kappa Isotype Control (P3.6.2.8.1), Super Bright™ 600, eBioscience™ |
| Class | Monoclonal |
| Type | Antibody |
| Clone | 4B4 (4B4-1) |
| Conjugate | Super Bright™ 600 |
| Excitation/Emission Max | 414/601 nm |
| Form | Liquid |
| Concentration | 5 µL/Test |
| Purification | Affinity chromatography |
| Storage buffer | PBS, pH 7.2, with BSA |
| Contains | 0.09% sodium azide |
| Storage conditions | 4° C, store in dark, DO NOT FREEZE! |
| RRID | AB_2717053 |

| Applications | Tested Dilution | Publications |
|-----------------------|--------------------|---------------|
| Flow Cytometry (Flow) | 5 µL (0.5 µg)/test | 1 Publication |

Product Specific Information

Description: This 4B4 (4B4-1) monoclonal antibody reacts with human CD137 (also known as 4-1BB or TNFRSF9), which is an inducible member of the TNFR family of costimulatory molecules expressed on T cells, natural killer cells, dendritic cells, granulocytes, and mast cells. Involved in recruiting TNFR-associated factors (TRAF) 1 and 2, CD137 signaling plays a role in T cell activation, maintaining the survival of activated and CD8 memory T cells, as well as suppressing myelopoiesis and dendritic cell development. Stimulation of this receptor has also been shown to promote expansion of CD4+CD25+ T regulatory cells *in vivo*. The ligand for CD137, 4-1BBL, is found on activated macrophages, mature B cells, hematopoietic stem cells, and myeloid progenitor cells.

Applications Reported: This 4B4 (4B4-1) antibody has been reported for use in flow cytometric analysis.

Applications Tested: This 4B4 antibody has been tested by flow cytometric analysis of normal human peripheral blood cells. This may be used at less than or equal to 5 µL (0.5 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells /test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Super Bright 600 is a tandem dye that can be excited with the violet laser line (405 nm) and emits at 600 nm. We recommend using a 610/20 bandpass filter. Please make sure that your instrument is capable of detecting this fluorochrome.

When using two or more Super Bright dye-conjugated antibodies in a staining panel, it is recommended to use Super Bright Complete Staining Buffer (Product # SB-4401) to minimize any non-specific polymer interactions. Please refer to the datasheet for Super Bright Staining Buffer for more information.


Light sensitivity: This tandem dye is sensitive to photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (Product # 00-8222) (100 µL of cell sample + 100 µL of IC Fixation Buffer) or 1-step Fix/Lyse Solution (Product # 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency/compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 405 nm; Emission: 600 nm; Laser: Violet Laser

Super Bright Polymer Dyes are sold under license from Becton, Dickinson and Company.

Product Images For CD137 (4-1BB) Monoclonal Antibody (4B4 (4B4-1)), Super Bright™ 600, eBioscience™



CD137 (4-1BB) Antibody (63-1379-42) in Flow
Normal human peripheral blood cells were stimulated for 72 hours with Con A (Product # 00-4978-93) and then stained with CD25 Monoclonal Antibody, PE (Product # 12-0259-42) and Mouse IgG1 kappa Isotype Control, Super Bright 600 (Product # 63-4714-82) (left) or CD137 Monoclonal Antibody, Super Bright 600 (right). Total viable cells were used for analysis.

1 Reference

Flow Cytometry (1)

| | |
|--|--------------|
| Oncoimmunology | Year 2022 |
| Neoantigens retention in patient derived xenograft models mediates autologous T cells activation in ovarian cancer. | |
| "Published figure using CD137 (4-1BB) monoclonal antibody (Product # 63-1379-42) in Flow Cytometry" | |
| Authors: Want MY, Konstorum A, Huang RY, Jain V, Matsueda S, Tsuji T, Lugade A, Odunsi K, Koya R, Battaglia S | |

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.