

IL-13 Monoclonal Antibody (eBio13A), PE-eFluor 610, eBioscience™

| Product Details | |
|-----------------------------|---|
| Size | 100 µg |
| Species | Mouse |
| Published Species | Artificial Control, Mouse, Human |
| Expression System | Rat / IgG1, kappa |
| Recommended Isotype Control | Rat IgG1 kappa Isotype Control (eBRG1), PE-eFluor 610, eBioscience™ |
| Class | Monoclonal |
| Type | Antibody |
| Clone | eBio13A |
| Conjugate | PE-eFluor® 610 |
| Form | Liquid |
| Concentration | 0.2 mg/mL |
| Purification | Affinity chromatography |
| Storage buffer | PBS, pH 7.2 |
| Contains | 0.09% sodium azide |
| Storage Conditions | 4° C, store in dark, DO NOT FREEZE! |
| RRID | AB_2574654 |

| Applications | Tested Dilution | Publications |
|-----------------------|-----------------|-----------------|
| Flow Cytometry (Flow) | 1 µg/test | 11 Publications |

Product Specific Information

Description: The eBio13A antibody reacts with mouse IL-13. IL-13 is a cytokine produced mainly by Th2 cells, but also by antigen-primed CD8 T cells. IL-13 has a strong involvement in allergic inflammation and parasitic clearing. In cancer models it has been shown to have either inhibitory or stimulatory activity depending on the tumor. In humans, IL-13 is found to play a role in isotype switching in B cells. IL-13 is implicating in down modulating macrophage activity, through the reduction of pro-inflammatory cytokines (IL-1, IL-6, IL-8, IL-10, IL-12)

Applications Reported: This eBio13A antibody has been reported for use in intracellular staining followed by flow cytometric analysis.

Applications Tested: This eBio13A antibody has been tested by intracellular staining and flow cytometric analysis of Th2-polarized mouse splenocytes. This can be used at less than or equal to 1 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

PE-eFluor® 610 can be excited with laser lines from 488-561 nm and emits at 607 nm. We recommend using a 610/20 band pass filter (equivalent to PE-Texas Red®). Please make sure that your instrument is capable of detecting this fluorochrome.


Light sensitivity: This tandem dye is sensitive to photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (cat. 00-8222) (100 μ L of cell sample + 100 μ L of IC Fixation Buffer) or 1-step Fix/Lyse Solution (cat. 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency /compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 488-561 nm; Emission: 607 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 μ m post-manufacturing filtered.

Product Images For IL-13 Monoclonal Antibody (eBio13A), PE-eFluor 610, eBioscience™



IL-13 Antibody (61-7133-82) in Flow

CD4+ BALB/c splenocytes were stimulated for 6 days with plate-bound Anti-Mouse CD3e Functional Grade Purified (Product # 16-0031-82), soluble Anti-Mouse CD28 Functional Grade Purified (Product # 16-0281-82), Mouse IL-2 Recombinant Protein (Product # 14-8021-64), and Mouse IL-4 Recombinant Protein (Product # 14-8041-80). Cells were then either non-restimulated (left) or restimulated with Cell Stimulation Cocktail (plus protein transport inhibitors) (Product # 00-4975-03) for 5 hours (right). Following restimulation, cells were fixed and permeabilized using the Intracellular Fixation and Permeabilization Buffer Set (Product # 88-8824-00) and then stained with Anti-Mouse CD4 FITC (Product # 11-0042-82) and 0.5 μ g of Anti-Mouse IL-13 PE-eFluor 610. Viable cells, as determined by Fixable Viability Dye eFluor® 450 (Product # 65-0863-14), were used for analysis.

[View more figures on thermofisher.com](https://www.thermofisher.com)

11 References

Flow Cytometry (11)

Nature communications

Arf1-mediated lipid metabolism sustains cancer cells and its ablation induces anti-tumor immune responses in mice.

"Published figure using IL-13 monoclonal antibody (Product # 61-7133-82) in Flow Cytometry"

Authors: Wang G,Xu J,Zhao J,Yin W,Liu D,Chen W,Hou SX

Species

Not Applicable

Dilution

Not Cited

Year

2020

Nature communications

Costimulation of type-2 innate lymphoid cells by GITR promotes effector function and ameliorates type 2 diabetes.

"Published figure using IL-13 monoclonal antibody (Product # 61-7133-82) in Flow Cytometry"

Authors: Galle-Treger L,Sankaranarayanan I,Hurrell BP,Howard E,Lo R,Maazi H,Lewis G,Banie H,Epstein AL,Hu P,Rehan VK,Gilliland FD,Allayee H,Soroosh P,Sharpe AH,Akbari O

Species

Artificial Control

Dilution

Not Cited

Year

2019

[View more Flow references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.