

Gata-3 Monoclonal Antibody (TWAJ), PE-eFluor 610, eBioscience™

Product Details	
Size	100 Tests
Species Reactivity	Human, Mouse, Pig, Rhesus monkey
Host/Isotope	Rat / IgG2b, kappa
Recommended Isotype Control	Rat IgG2b kappa Isotype Control (eB149/10H5), PE-eFluor 610, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	TWAJ
Conjugate	PE-eFluor® 610
Form	Liquid
Concentration	5 µL/Test
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with 0.2% BSA
Contains	0.09% sodium azide
Storage Conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2574686

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	5 µL (0.03 µg)/test	5 Publications

Product Specific Information

Description: The monoclonal antibody TWAJ recognizes mouse and human Gata-3, a member of the Gata family of transcription factors. Gata-3 is a T cell-specific transcription factor important for thymic development and Th2 differentiation. Expression during embryonic development is found in the central nervous system, skin, mammary glands and kidney. During development, the expression of Gata-3 is essential as homozygous knock-out of Gata-3 is embryonic lethal. The Gata-3 is also essential for T cell commitment and survival. In the thymus, expression is found mainly on the CD4 single positive cells. During Th2 differentiation, Gata-3 binds to the IL-4 promoter as well as represses the expression of T-bet, thus inhibiting Th1 differentiation.

Alternative splice variants have been reported especially in the MCF7 cell line. The TWAJ Human/Mouse Gata-3 antibody will recognize both forms (50 and 45 kDa) of the protein.

Staining with the TWAJ Human/Mouse Gata-3 antibody requires the use of the Foxp3/Transcription Factor Staining Buffer Set.(cat 00-5523)

Crossreactivity in rhesus monkeys has been published.

Applications Reported: This TWAJ antibody has been reported for use in intracellular staining followed by flow cytometric analysis.

Applications Tested: This TWAJ antibody has been pre-titrated and tested by intracellular staining and flow cytometric analysis of mouse thymocytes using the Foxp3/Transcription Factor Staining Buffer Set (cat. 00-5523) and protocol. Please refer to Best Protocols: Protocol B: One step protocol for (nuclear) intracellular proteins located under the Resources Tab online. This can be used at 5 µL (0.03 µg) per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100

µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test.

PE-eFluor® 610 can be excited with laser lines from 488-561 nm and emits at 607 nm. We recommend using a 610/20 band pass filter (equivalent to PE-Texas Red®). Please make sure that your instrument is capable of detecting this fluorochrome.


Light sensitivity: This tandem dye is sensitive to photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (cat. 00-8222) (100 µL of cell sample + 100 µL of IC Fixation Buffer) or 1-step Fix/Lyse Solution (cat. 00-5333) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency /compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 488-561 nm; Emission: 607 nm; Laser: Blue Laser, Green Laser, Yellow-Green Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For Gata-3 Monoclonal Antibody (TWAJ), PE-eFluor 610, eBioscience™



Gata-3 Antibody (61-9966-42) in Flow

C57Bl/6 thymocytes were surface stained with Anti-Mouse CD4 FITC (Product # 11-0042-82) and Anti-Mouse CD8a APC (Product # 17-0081-82) followed by intracellular staining with Rat IgG2b K Isotype Control PE-eFluor® 610 (Product # 61-4031-80) (blue histogram) or Anti-Human/Mouse Gata-3 PE-eFluor® 610 (purple histogram) using the Foxp3/Transcription Factor Staining Buffer Set (Product # 00-5523-00) and protocol. Cells in the CD4 single positive (left) or CD8 single positive (right) gates were used for analysis.

[View more figures on thermofisher.com](http://thermofisher.com)

5 References

Flow Cytometry (5)

Wellcome open research

Characterisation of innate lymphoid cell populations at different sites in mice with defective T cell immunity.

"Published figure using Gata-3 monoclonal antibody (Product # 61-9966-42) in Flow Cytometry"

Authors: Dutton EE,Camelo A,Sleeman M,Herbst R,Carlesso G,Belz GT,Withers DR

Species
Not Applicable

Dilution
Not Cited

Year
2019

Nature

Stability and function of regulatory T cells expressing the transcription factor T-bet.

"Published figure using Gata-3 monoclonal antibody (Product # 61-9966-42) in Flow Cytometry"

Authors: Levine AG,Mendoza A,Hemmers S,Molledo B,Niec RE,Schizas M,Hoyos BE,Putintseva EV,Chaudhry A,Dikiy S,Fujisawa S,Chudakov DM,Treuting PM,Rudensky AY

Species
Not Applicable

Dilution
Not Cited

Year
2017

[View more Flow references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.