

CD90.1 (Thy-1.1) Monoclonal Antibody (HIS51), Super Bright™ 436, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse, Rat
Host/Isotype	Mouse / IgG2a, kappa
Recommended Isotype Control	Mouse IgG2a kappa Isotype Control (eBM2a), Super Bright™ 436, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	HIS51
Conjugate	Super Bright™ 436
Excitation/Emission Max	413/431 nm
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2744782

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	1 Publication
Immunocytochemistry (ICC/IF)	-	1 Publication
Flow Cytometry (Flow)	0.25 µg/test	16 Publications

Product Specific Information

Description: The HIS51 monoclonal antibody reacts with rat CD90 and cross-reacts with mouse CD90.1, a GPI-linked membrane molecule. In the rat, CD90 is expressed by hematopoietic stem cells, immature B cells, thymocytes, recent thymic emigrants, neurons, inflamed endothelia and other cell types. In the CD90.1-expressing mouse strains, PL and AKR, CD90 is expressed by early hematopoietic cells in the bone marrow, thymocytes and mature T cells. ^{^M}

Applications Reported: This HIS51 antibody has been reported for use in flow cytometric analysis. ^{^M}

Applications Tested: This HIS51 antibody has been tested by flow cytometric analysis of rat splenocytes. This may be used at less than or equal to 0.25 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest. ^{^M}

Super Bright 436 can be excited with the violet laser line (405 nm) and emits at 436 nm. We recommend using a 450/50 bandpass filter, or equivalent. Please make sure that your instrument is capable of detecting this fluorochrome. ^{^M}

When using two or more Super Bright dye-conjugated antibodies in a staining panel, it is recommended to use Super Bright Complete Staining Buffer (Product # SB-4401) to minimize any non-specific polymer interactions. Please refer to the datasheet

for Super Bright Staining Buffer for more information.™


™

Excitation: 405 nm; Emission: 436 nm; Laser: Violet Laser.™

™

Super Bright Polymer Dyes are sold under license from Becton, Dickinson and Company.

Product Images For CD90.1 (Thy-1.1) Monoclonal Antibody (HIS51), Super Bright™ 436, eBioscience™



CD90.1 (Thy-1.1) Antibody (62-0900-82) in Flow

Wistar rat splenocytes were stained with CD3 Monoclonal Antibody, APC (Product # 17-0030-82) and 0.125 µg of Mouse IgG2a kappa Isotype Control, Super Bright 436 (Product # 62-4724-82) (left) or 0.125 µg of CD90.1 Monoclonal Antibody, Super Bright 436 (right). Total viable cells were used for analysis, as determined by 7-AAD (Product # 00-6993-50).

[View more figures on thermofisher.com](http://thermofisher.com)

18 References

Immunohistochemistry (1)

Stem cell research & therapy

Bone marrow-derived mesenchymal stem cells combined with gonadotropin therapy restore postnatal oogenesis of chemo-ablated ovaries in rats via enhancing very small embryonic-like stem cells.

"Published figure using CD90.1 (Thy-1.1) monoclonal antibody (Product # 62-0900-82) in Immunohistochemistry"

Authors: Ebrahim N, Al Saihati HA, Shaman A, Dessouky AA, Farid AS, Hussien NI, Mostafa O, Seleem Y, Sabry D, Saad AS, Emam HT, Hassouna A, Badr OAM, Saffaf BA, Forsyth NR, Salim RF

Year
2021

Immunocytochemistry (1)

Frontiers in endocrinology

Pituispheres Contain Genetic Variants Characteristic to Pituitary Adenoma Tumor Tissue.

"Published figure using CD90.1 (Thy-1.1) monoclonal antibody (Product # 62-0900-82) in Immunocytochemistry"

Authors: Peculis R, Mandrika I, Petrovska R, Dortane R, Megnis K, Nazarovs J, Balcere I, Stukens J, Konrade I, Pirags V, Klovins J, Rovite V

Year
2021

Flow Cytometry (16)

Heliyon

Single-cell transcriptomics reveals variable trajectories of CSPCs in the progression of osteoarthritis.

"Published figure using CD90.1 (Thy-1.1) monoclonal antibody (Product # 62-0900-82) in Flow Cytometry"

Authors: Qi L, Wang J, Chen X, Ding Y, Ling B, Wang W, Xu J, Xue Z

Year
2022

Neural regeneration research

Sustained release of exosomes loaded into polydopamine-modified chitin conduits promotes peripheral nerve regeneration in rats.

"Published figure using CD90.1 (Thy-1.1) monoclonal antibody (Product # 62-0900-82) in Flow Cytometry"

Authors: Li C, Liu SY, Zhang M, Pi W, Wang B, Li QC, Lu CF, Zhang PX

Year
2022

[View more Flow references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.