

CD163 Monoclonal Antibody (TNKUPJ), Super Bright™ 702, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Host/Isotype	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), Super Bright™ 702, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	TNKUPJ
Conjugate	Super Bright™ 702
Excitation/Emission Max	413/702 nm
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2784887

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	2 Publications
Flow Cytometry (Flow)	0.25 µg/test	10 Publications

Product Specific Information

Description: This TNKUPJ monoclonal antibody recognizes mouse CD163. CD163 is a 130 kDa surface receptor expressed by certain subsets of tissue macrophages, including splenic red pulp macrophages, Kupffer cells, intestinal lamina propria macrophages and a small fraction of peritoneal macrophages. In contrast to human blood monocytes, mouse monocytes do not express CD163. Also, unlike human CD163, mouse CD163 is not as readily induced by M2 polarizing cytokines, and it is not a good marker of M2 macrophages. No common cell lines of monocytic or macrophage origin express mouse CD163. In humans, CD163 has been shown to be proteolytically cleaved and shed from the cell surface, and it acts as a soluble anti-inflammatory factor.

This TNKUPJ antibody will detect CD163 on fixed and permeabilized cells allowing for staining of the intracellular pool of this receptor. Although CD163 is relatively stable to collagenase digestion, aggressive tissue dissociation protocols might potentially decrease the amount of surface CD163. In these cases intracellular detection is recommended.

Applications Reported: This TNKUPJ antibody has been reported for use in flow cytometric analysis.

Applications Tested: This TNKUPJ antibody has been tested by flow cytometric analysis of mouse splenocytes. This may be used at less than or equal to 0.25 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Super Bright 702 is a tandem dye that can be excited with the violet laser line (405 nm) and emits at 702 nm. We recommend using a 710/50 bandpass filter. Please make sure that your instrument is capable of detecting this fluorochrome.

When using two or more Super Bright dye-conjugated antibodies in a staining panel, it is recommended to use Super Bright Complete Staining Buffer (Product # SB-4401) to minimize any non-specific polymer interactions. Please refer to the datasheet for Super Bright Staining Buffer for more information.


Light sensitivity: This tandem dye is sensitive to photo-induced oxidation. Please protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (Product # 00-8222-49) (100 μ L of cell sample + 100 μ L of IC Fixation Buffer) or 1-step Fix/Lyse Solution (Product # 00-5333-57) for up to 3 days in the dark at 4°C with minimal impact on brightness and FRET efficiency/compensation. Some generalizations regarding fluorophore performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 405 nm; Emission: 702 nm; Laser: Violet Laser

Super Bright Polymer Dyes are sold under license from Becton, Dickinson and Company.

Product Images For CD163 Monoclonal Antibody (TNKUPJ), Super Bright™ 702, eBioscience™



CD163 Antibody (67-1631-82) in Flow

BALB/c mouse splenocytes were stained with F4/80 Monoclonal Antibody, eFluor 450 (Product # 48-4801-82) and 0.125 μ g of Rat IgG2a kappa Isotype Control, Super Bright 702 (Product # 67-4321-82) (left) or 0.125 μ g of CD163 Monoclonal Antibody, Super Bright 702 (right). Total cells were used for analysis.

[View more figures on thermofisher.com](https://www.thermofisher.com)

Immunohistochemistry (2)

eLife

The regional distribution of resident immune cells shapes distinct immunological environments along the murine epididymis.

"Published figure using CD163 monoclonal antibody (Product # 67-1631-82) in Immunohistochemistry"

Authors: Pleuger C, Ai D, Hoppe ML, Winter LT, Bohnert D, Karl D, Guenther S, Eelman S, Kantores C, Fijak M, Ravens S, Middendorff R, Mayer JU, Loveland KL, Hedger M, Bhushan S, Meinhardt A

Year
2022

Nature materials

Tumour-associated macrophages drive stromal cell-dependent collagen crosslinking and stiffening to promote breast cancer aggression.

"Published figure using CD163 monoclonal antibody (Product # 67-1631-82) in Immunohistochemistry"

Authors: Maller O, Drain AP, Barrett AS, Borgquist S, Ruffell B, Zakharevich I, Pham TT, Gruosso T, Kuasne H, Lakins JN, Acerbi I, Barnes JM, Nemkov T, Chauhan A, Gruenberg J, Nasir A, Bjarnadottir O, Werb Z, Kabos P, Chen YY, Hwang ES, Park M, Coussens LM, Nelson AC, Hansen KC, Weaver VM

Year
2021

Flow Cytometry (10)

Cellular and molecular gastroenterology and hepatology

Shp2 Deficiency in Kupffer Cells and Hepatocytes Aggravates Hepatocarcinogenesis by Recruiting Non-Kupffer Macrophages.

"Published figure using CD163 monoclonal antibody (Product # 67-1631-82) in Flow Cytometry"

Authors: Du L, Ji Y, Xin B, Zhang J, Lu LC, Glass CK, Feng GS

Year
2023

EMBO reports

Pericyte stem cells induce Ly6G⁺ cell accumulation and immunotherapy resistance in pancreatic cancer.

"Published figure using CD163 monoclonal antibody (Product # 67-1631-82) in Flow Cytometry"

Authors: Wu Z, Thierry K, Bachy S, Zhang X, Gamradt P, Hernandez-Vargas H, Mikaelian I, Tonon L, Pommier R, Zhao Y, Bertolino P, Hennino A

Year
2023

[View more Flow references on thermofisher.com](#)

More applications with references on thermofisher.com

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.