

F4/80 Monoclonal Antibody (BM8), eFluor™ 506, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Published Species	Hamster, Mouse, Human
Host/Isotype	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), eFluor™ 506, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	BM8
Conjugate	eFluor™ 506
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2637190

Applications	Tested Dilution	Publications
Immunohistochemistry (IHC)	-	124 Publications
Immunohistochemistry (Paraffin) (IHC (P))	-	2 Publications
Immunohistochemistry (PFA fixed) (IHC (PFA))	-	2 Publications
Immunohistochemistry (Frozen) (IHC (F))	-	4 Publications
Immunocytochemistry (ICC/IF)	-	35 Publications
Flow Cytometry (Flow)	0.125 µg/test	108 Publications
Miscellaneous PubMed (Misc)	-	1 Publication

Product Specific Information

Description: The BM8 monoclonal antibody reacts with mouse F4/80 antigen, an approximately 160 kDa surface receptor. It belongs to the EGF-TM7 family of proteins. As such it contains seven EGF-like domains on its extracellular N-terminus, seven transmembrane spanning sequences, and an intracellular C-terminal domain showing homology to other TM7 superfamily members. The F4/80 antigen is expressed by a majority of mature macrophages and is one of the best markers for this population of cells. However, other cell types, such as peritoneal eosinophils, Langerhans cells, and some other dendritic cell subtypes, have been reported to express this antigen as well. Expression of F4/80 commences during early myeloid development in vivo and can be upregulated on BM cells stimulated in vitro with M-CSF. Some populations of macrophages, especially in the lymphoid microenvironment, may be devoid of F4/80.

Applications Reported: This BM8 antibody has been reported for use in flow cytometric analysis.


Applications Tested: This BM8 antibody has been tested by flow cytometric analysis of mouse resident peritoneal exudate cells. This can be used at less than or equal to 0.125 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

eFluor® 506 can be excited with the violet laser line (405 nm) and emits at 506 nm. We recommend using a 510/20 band pass filter, or equivalent. Please make sure that your instrument is capable of detecting this fluorochrome.

Excitation: 405 nm; Emission: 506 nm; Laser: Violet Laser.

Filtration: 0.2 µm post-manufacturing filtered.

Product Images For F4/80 Monoclonal Antibody (BM8), eFluor™ 506, eBioscience™



F4/80 Antibody (69-4801-82) in Flow

Staining of mouse resident peritoneal exudate cells with Anti-Mouse CD11b PerCP-Cyanine5-5 (Product # 45-0112-82) and 0.06 µg of Anti-Mouse F4/80 Antigen eFluor® 506 (right). Total viable cells were used for analysis.

[View more figures on thermofisher.com](https://www.thermofisher.com)

Immunohistochemistry (124)

Histochemistry and cell biology

Potential functions of embryonic cardiac macrophages in angiogenesis, lymphangiogenesis and extracellular matrix remodeling.

"Published figure using F4/80 monoclonal antibody (Product # 69-4801-82) in Immunohistochemistry"

Authors: Gula G,Rumiski S,Niderla-Bieliska J,Jasiska A,Kiernozek E,Jankowska-Steifer E,Flaht-Zabost A,Ratajska A

Species
Not Applicable

Dilution
Not Cited

Year
2021

Frontiers in immunology

Vitamin D in Acute Campylobacteriosis-Results From an Intervention Study Applying a Clinical *Campylobacter jejuni* Induced Enterocolitis Model.

"Published figure using F4/80 monoclonal antibody (Product # 69-4801-82) in Immunohistochemistry"

Authors: Mousavi S,Lobo de Sá FD,Schulzke JD,Bücker R,Bereswill S,Heimesaat MM

Species
Not Applicable

Dilution
Not Cited

Year
2020

[View more IHC references on thermofisher.com](#)

Immunohistochemistry (Paraffin) (2)

Frontiers in immunology

Murine Fecal Microbiota Transplantation Alleviates Intestinal and Systemic Immune Responses in *Campylobacter jejuni* Infected Mice Harboring a Human Gut Microbiota.

"Published figure using F4/80 monoclonal antibody (Product # 69-4801-82) in Immunohistochemistry"

Authors: Heimesaat MM,Mrazek K,Bereswill S

Species
Not Applicable

Dilution
Not Cited

Year
2020

Experimental and therapeutic medicine

Anti-inflammatory effects of *Fagopyrum cymosum* administered as a potential drug for ulcerative colitis.

"Published figure using F4/80 monoclonal antibody (Product # 69-4801-82) in Immunohistochemistry (Paraffin)"

Authors: Ge F,Zhu S,Liu L,Yan J, Ji Y,Sun Z

Species
Not Applicable

Dilution
Not Cited

Year
2017

More applications with references on thermofisher.com

IHC (PFA) (2)

IHC (F) (4)

ICC/IF (35)

Flow (108)

Misc (1)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.