

CD170 (Siglec F) Monoclonal Antibody (1RNM44N), Super Bright™ 436, eBioscience™

Product Details	
Size	100 µg
Species Reactivity	Mouse
Host/Isotype	Rat / IgG2a, kappa
Recommended Isotype Control	Rat IgG2a kappa Isotype Control (eBR2a), Super Bright™ 436, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	1RNM44N
Conjugate	Super Bright™ 436
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2664259

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.125 µg/test	4 Publications

Product Specific Information

Description: This 1RNM44N monoclonal antibody recognizes mouse CD170, also known as Siglec F. Siglec F is a cell surface lectin belonging to the Ig superfamily that binds glycoconjugates containing sialic acids that are commonly found on various cell types. The cytoplasmic domain of Siglec F contains an immunoreceptor tyrosine-based inhibitory motif (ITIM) that initiates intracellular signaling upon ligand binding. Siglec F is expressed mostly on eosinophils and alveolar macrophages and lower levels of this receptor have also been reported on immature myelomonocytic cells. Mouse Siglec F is a functional ortholog of human Siglec 8, however, unlike human Siglec 8, mouse Siglec F is not expressed on mast cells.

This 1RNM44N antibody will recognize a formaldehyde-fixed epitope.

Applications Reported: This 1RNM44N antibody has been reported for use in flow cytometric analysis.

Applications Tested: This 1RNM44N antibody has been tested by flow cytometric analysis of thioglycolate-elicited peritoneal macrophages. This may be used at less than or equal to 0.125 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells /test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.


Super Bright 436 can be excited with the violet laser line (405 nm) and emits at 436 nm. We recommend using a 450/50 bandpass filter, or equivalent. Please make sure that your instrument is capable of detecting this fluorochrome.

When using two or more Super Bright dye-conjugated antibodies in a staining panel, it is recommended to use Super Bright Complete Staining Buffer (Product # SB-4401) to minimize any non-specific polymer interactions. Please refer to the datasheet for Super Bright Staining Buffer for more information.

Excitation: 405 nm; Emission: 436 nm; Laser: Violet Laser

Super Bright Polymer Dyes are sold under license from Becton, Dickinson and Company.

Product Images For CD170 (Siglec F) Monoclonal Antibody (1RNM44N), Super Bright™ 436, eBioscience™



CD170 (Siglec F) Antibody (62-1702-82) in Flow

Staining of BALB/c mouse thioglycolate-elicited peritoneal exudate cells with Anti-Mouse F4/80 APC (Product # 17-4801-82) and 0.06 µg of Rat IgG2a kappa Isotype Control Super Bright 436 (Product # 62-4321-82) (left) or 0.06 µg of Anti-Mouse CD170 (Siglec F) Super Bright 436 (right). Viable cells were used for analysis.

[View more figures on thermofisher.com](#)

4 References

Flow Cytometry (4)

JCI insight

Arf6 exacerbates allergic asthma through cell-to-cell transmission of ASC inflammasomes.

"Published figure using CD170 (Siglec F) monoclonal antibody (Product # 62-1702-82) in Flow Cytometry"

Authors: Lee S, Ishitsuka A, Kuroki T, Lin YH, Shibuya A, Hongu T, Funakoshi Y, Kanaho Y, Nagata K, Kawaguchi A

Year
2021

Nature communications

Eosinophils improve cardiac function after myocardial infarction.

"Published figure using CD170 (Siglec F) monoclonal antibody (Product # 62-1702-82) in Flow Cytometry"

Authors: Liu J, Yang C, Liu T, Deng Z, Fang W, Zhang X, Li J, Huang Q, Liu C, Wang Y, Yang D, Sukhova GK, Lindholt JS, Diederichsen A, Rasmussen LM, Li D, Newton G, Luscinskas FW, Liu L, Libby P, Wang J, Guo J, Shi GP

Year
2020

[View more Flow references on thermofisher.com](#)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.