

Fluorescein/Oregon Green Monoclonal Antibody (4-4-20)

Product Details	
Size	500 µg
Species Reactivity	Chemical
Host/Isotype	Mouse
Class	Monoclonal
Type	Antibody
Clone	4-4-20
Conjugate	Unconjugated
Immunogen	fluorescein/Oregon Green®
Form	Lyophilized
Purification	purified
Storage buffer	0.1M sodium phosphate, pH 8, with 1.5% BSA
Contains	0.01% thimerosal
Storage conditions	4° C
RRID	AB_2536201

Applications	Tested Dilution	Publications
Western Blot (WB)	-	2 Publications
Immunohistochemistry (IHC)	Assay-dependent	1 Publication
Immunohistochemistry (Paraffin) (IHC (P))	-	1 Publication
Immunocytochemistry (ICC/IF)	Assay-dependent	3 Publications
Flow Cytometry (Flow)	Assay-dependent	1 Publication
ELISA (ELISA)	-	4 Publications
Blocking Assay (BLOCK)	-	3 Publications
Miscellaneous PubMed (Misc)	-	13 Publications


Product Specific Information

Storage and reconstitution: a stock solution can be made by dissolving the powder in 0.5 mL of deionized water to yield an antibody concentration of 1 mg/mL. When stored desiccated at 4°C or -20°C, the lyophilized product is stable for at least six months. Stock solutions are stable for at least three months when stored at 4°C. For longer storage of solutions, divide into aliquots and freeze at -20°C.

Product Images For Fluorescein/Oregon Green Monoclonal Antibody (4-4-20)



Fluorescein/Oregon Green Antibody (A-6421) in ICC/IF

α -Satellite probes to chromosomes 1, 15 and 17 were labeled by nick translation with biotin-11-dUTP, ChromaTide Texas Red-12-dUTP (C7631) and ChromaTide Oregon Green 488-5-dUTP, respectively. Following simultaneous hybridization of all three probes, the biotinylated chromosome 1 probe was detected with HRP-streptavidin conjugate and Alexa Fluor 546 tyramide (TSA Kit #23, Prod # T20933). HRP activity from this first TSA detection step was then quenched by treatment with 1% hydrogen peroxide for 30 minutes. Lastly, the Oregon Green 488 dye-labeled chromosome 17 probe was detected with anti-fluorescein/Oregon Green antibody (Prod # A6421) followed by HRP-conjugated goat anti-mouse IgG antibody and Alexa Fluor 594 tyramide (TSA Kit #5, Prod # T20915). HRP activity from this second TSA detection step was then quenched by treatment with 1% hydrogen peroxide for 30 minutes. The Texas Red dye-labeled chromosome 15 probe was then detected with rabbit anti-Texas Red antibody (Prod # A6399) followed by HRP-conjugated goat anti-rabbit IgG antibody and Alexa Fluor 488 tyramide (TSA Kit #12, Prod # T20922). After counterstaining with Hoechst 33258 (Prod # H1398, H3569, H21491), the images were acquired using filters appropriate for DAPI, FITC, TRITC and Texas Red dyes.



Fluorescein/Oregon Green Antibody (A-6421) in IHC

Simultaneous detection of expression of five genes in a whole-mount *Drosophila* embryo by fluorescence in situ hybridization (FISH) with five RNA probes. Red: *sog* labeled using aminoallyl UTP (Prod # A21663, A32765) and Alexa Fluor® 647 succinimidyl ester (Prod # A20006, A20106). Green: *ind* labeled with DNP, followed by rabbit anti-dinitrophenyl-KLH IgG antibody (Prod # A6430) pre-labeled with the Zenon® Alexa Fluor® 555 Rabbit IgG Labeling Kit (Prod # Z25305). Blue: *en* labeled with biotin and detected with HRP-streptavidin and Alexa Fluor® 405 tyramide (TSA™ Kit #39, T30952). Yellow: *wg* labeled with digoxigenin and detected with sheep anti-digoxigenin IgG antibody and Alexa Fluor® 594 Donkey Anti-Sheep IgG antibody (Prod # A11016). Magenta: *msh* labeled with fluorescein and detected with mouse anti-fluorescein/Oregon Green® IgG_{2a} antibody (Prod # A6421) and Alexa Fluor® 488 Goat Anti-Mouse IgG antibody (Prod # A11001, A11029). Image contributed by Dave Kosman and Ethan Bier, University of California, San Diego.



Fluorescein/Oregon Green Antibody (A-6421)

Detection of a mouse monoclonal antibody using the Amplex® Red ELISA Kit #1, with the horseradish peroxidase conjugate of goat anti-mouse IgG antibody (Prod # A22170). The wells of a microplate were first coated with an excess of a fluorescein conjugate of bovine serum albumin (BSA) and then blocked with PBS-BSA. The indicated amounts of anti-fluorescein/Oregon Green® mouse monoclonal 4-4-20 antibody (Prod # A6421) were then applied in 100 μ L volumes and incubated for one hour. The wells were washed and then assayed using the reagents and protocol provided in this kit. The reactions were incubated for 50 minutes and then measured both A) for fluorescence (excitation/emission of 530/590 nm) and B) for absorbance (576 nm). The data points represent the average of three reactions. For the fluorescence plot, a background of 280 (arbitrary units) has been subtracted from each reading; for the absorption plot, a background of 0.040 has been subtracted from each reading.

28 References

Western Blot (2)

American journal of physiology. Renal physiology

The reactive nitrogen species peroxynitrite is a potent inhibitor of renal Na-K-ATPase activity.

"A-6421 was used in western blot to examine the direct effects of peroxynitrite on Na-K-ATPase function"

Authors: Reifenberger MS, Arnett KL, Gatto C, Milanick MA

Species
Not Applicable

Dilution
1:5000

Year
2008

Biology of the cell

Analysis of rates of receptor-mediated endocytosis and exocytosis of a fluorescent hapten-protein conjugate in murine macrophage: implications for antigen processing.

"A-6421 was used in western blot to investigate the effect of receptor-mediated endocytosis upon the processing of the hapten-protein within murine peritoneal macrophage"

Authors: Weaver DJ, Voss EW

Species
Not Applicable

Dilution
Not Cited

Year
1998

Immunohistochemistry (1)

Proceedings of the National Academy of Sciences of the United States of America

Antibody caging of a nuclear-targeting signal.

"A-6421 was used in immunohistochemistry to develop a technique to reversibly mask a peptide-targeting signal"

Authors: Halleck MS, Rechsteiner M

Species
Not Applicable

Dilution
Not Cited

Year
1990

Immunohistochemistry (Paraffin) (1)

American journal of physiology. Endocrinology and metabolism

The vascular endothelial cell mediates insulin transport into skeletal muscle.

"A-6421 was used in immunohistochemistry - paraffin section to determine mediation of insulin transport into skeletal muscle via the vascular endothelial cell"

Authors: Wang H, Liu Z, Li G, Barrett EJ

Species
Not Applicable

Dilution
1:100

Year
2006

More applications with references on thermofisher.com

ICC/IF (3)

Flow (1)

ELISA (4)

BLOCK (3)

Misc (13)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.