

CD48 Monoclonal Antibody (HM48-1), Super Bright™ 600, eBioscience™

Product Details	
Size	25 µg
Species Reactivity	Mouse
Published Species	Mouse
Host/Isotype	Armenian hamster / IgG
Recommended Isotype Control	Armenian Hamster IgG Isotype Control (eBio299Arm), Super Bright™ 600, eBioscience™
Class	Monoclonal
Type	Antibody
Clone	HM48-1
Conjugate	Super Bright™ 600
Excitation/Emission Max	414/601 nm
Form	Liquid
Concentration	0.2 mg/mL
Purification	Affinity chromatography
Storage buffer	PBS, pH 7.2, with BSA
Contains	0.09% sodium azide
Storage conditions	4° C, store in dark, DO NOT FREEZE!
RRID	AB_2734993

Applications	Tested Dilution	Publications
Flow Cytometry (Flow)	0.5 µg/test	4 Publications

Product Specific Information

Description: The HM48-1 monoclonal antibody reacts with the mouse CD48 antigen; also known as BCM1, Blast-1 (human), and OX-45 (rat). CD48, a member of the SLAM family and Ig superfamily, is a 45 kDa GPI-linked glycoprotein expressed on the majority of hematopoietic cells. Recent publications have reported differential expression of members of the SLAM family including CD48, CD150, and CD244 among functionally distinct bone marrow hematopoietic progenitors providing a useful tool for prediction of the primitiveness of hematopoietic progenitors based on the expression of these SLAM family members. Hematopoietic stem cells (HSC) are highly purified as CD150(+)/CD244(-)/CD48(-) cells while non-self-renewing multipotent hematopoietic progenitors (MPP) are CD244(+)/CD150(-)/CD48(-) and the most restricted progenitors are CD48(+)/CD244(+)/CD150(-). CD48 plays a critical role in adhesion and T cell activation. In the mouse, the primary counter-receptors for CD48 are CD2 and CD244. HM48-1 is reported to modulate in vitro and in vivo CD48 functions including blocking the CD48/CD2 and CD48/CD244 interactions, inhibiting the proliferative response of mitogen-activated spleen cells, providing a costimulation signal for T cells activated in vitro through their TCR, and prolonging cardiac allograft survival in vivo.

Applications Reported: This HM48-1 antibody has been reported for use in flow cytometric analysis.

Applications Tested: This HM48-1 antibody has been tested by flow cytometric analysis of mouse splenocytes. This can be used at less than or equal to 0.5 µg per test. A test is defined as the amount (µg) of antibody that will stain a cell sample in a final volume of 100 µL. Cell number should be determined empirically but can range from 10⁵ to 10⁸ cells/test. It is recommended that the antibody be carefully titrated for optimal performance in the assay of interest.

Super Bright 600 is a tandem dye that can be excited with the violet laser line (405 nm) and emits at 600 nm. We recommend using a 610/20 bandpass filter. Please make sure that your instrument is capable of detecting this fluorochrome.

When using two or more Super Bright dye-conjugated antibodies in a staining panel, it is recommended to use Super Bright Complete Staining Buffer (Product # SB-4401) to minimize any non-specific polymer interactions. Please refer to the datasheet for Super Bright Staining Buffer for more information.


Light sensitivity: This tandem dye is sensitive to photo-induced oxidation. Protect this vial and stained samples from light.

Fixation: Samples can be stored in IC Fixation Buffer (Product # 00-8222) (100 μ L of cell sample + 100 μ L of IC Fixation Buffer) or 1-step Fix/Lyse Solution (Product # 00-5333) for up to 3 days in the dark at 2-8°C with minimal impact on brightness and FRET efficiency/compensation. Some generalizations regarding fluorochrome performance after fixation can be made, but clone specific performance should be determined empirically.

Excitation: 405 nm; Emission: 600 nm; Laser: Violet Laser

Super Bright Polymer Dyes are sold under license from Becton, Dickinson and Company.

Product Images For CD48 Monoclonal Antibody (HM48-1), Super Bright™ 600, eBioscience™



CD48 Antibody (63-0481-80) in Flow

Swiss Webster mouse splenocytes were stained with 0.25 μ g of Armenian Hamster IgG Isotype Control, Super Bright 600 (Product # 63-4888-82) (blue histogram) or 0.25 μ g of CD48 Monoclonal Antibody, Super Bright 600 (purple histogram). Cells in the lymphocyte gate were used for analysis.

[View more figures on thermofisher.com](https://www.thermofisher.com)

4 References

Flow Cytometry (4)

Science advances

Conditionally pathogenic genetic variants of a hematopoietic disease-suppressing enhancer.

"Published figure using CD48 monoclonal antibody (Product # 63-0481-82) in Flow Cytometry"

Authors: Soukup AA, Matson DR, Liu P, Johnson KD, Bresnick EH

Year
2021

Nature communications

MAEA is an E3 ubiquitin ligase promoting autophagy and maintenance of haematopoietic stem cells.

"Published figure using CD48 monoclonal antibody (Product # 63-0481-82) in Flow Cytometry"

Authors: Wei Q, Pinho S, Dong S, Pierce H, Li H, Nakahara F, Xu J, Xu C, Boulais PE, Zhang D, Maryanovich M, Cuervo AM, Frenette PS

Year
2021

[View more Flow references on thermofisher.com](#)

For Research Use Only. Not for use in diagnostic procedures. Not for resale without express authorization. Products are warranted to operate or perform substantially in conformance with published Product specifications in effect at the time of sale, as set forth in the Production documentation, specifications and/or accompanying package inserts ("Documentation"). No claim of suitability for use in applications regulated by FDA is made. The warranty provided herein is valid only when used by properly trained individuals. Unless otherwise stated in the Documentation, this warranty is limited to one year from date of shipment when the Product is subjected to normal, proper and intended usage. This warranty does not extend to anyone other than the Buyer. Any model or sample furnished to Buyer is merely illustrative of the general type and quality of goods and does not represent that any Product will conform to such model or sample. NO OTHER WARRANTIES, EXPRESS OR IMPLIED, ARE GRANTED INCLUDING WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR ANY PARTICULAR PURPOSE, OR NON-INFRINGEMENT. BUYER'S EXCLUSIVE REMEDY FOR NON-CONFORMING PRODUCTS DURING THE WARRANTY PERIOD IS LIMITED TO REPAIR, REPLACEMENT OF OR REFUND FOR THE NON-CONFORMING PRODUCT(S) AT SELLER'S SOLE OPTION. THERE IS NO OBLIGATION TO REPAIR, REPLACE OR REFUND FOR PRODUCTS AS THE RESULT OF (I) ACCIDENT, DISASTER OR EVENT OF FORCE MAJEURE, (II) MISUSE, FAULT OR NEGLIGENCE OF OR BY BUYER, (III) USE OF THE PRODUCTS IN A MANNER FOR WHICH THEY WERE NOT DESIGNED, OR (IV) IMPROPER STORAGE AND HANDLING OF THE PRODUCTS. Unless otherwise expressly stated on the Product or in the documentation accompanying the Product, the Product is intended for research only and is not to be used for any other purpose, including without limitation, unauthorized commercial uses, in vitro diagnostic uses, ex vivo or in vivo therapeutic uses, or any type of consumption by or application to human or animals.